

# Chip Inductor

AWCM Series - ISO9001 | ISO14001 | IATF16949




- RF  
Circuit
- Unshield
- Wire  
Wound
- Ceramic
- High  
Q

## Part Numbering

|       |             |              |                         |                    |           |               |
|-------|-------------|--------------|-------------------------|--------------------|-----------|---------------|
| A     | WCM         | 00           | 161008                  | 10N                | J         | 00            |
| Grade | Series Name | Control Code | Dimensions Code<br>(mm) | Inductance<br>(nH) | Tolerance | Internal Code |
|       |             |              | 120707 1.19x0.64x0.66   | 2N2 2.2            | B ±0.1nH  |               |
|       |             |              | 161008 1.6x1.02x0.82    | 10N 10             | C ±0.2nH  |               |
|       |             |              |                         | R10 100            | D ±0.5nH  |               |
|       |             |              |                         |                    | G ±2%     |               |
|       |             |              |                         |                    | H ±3%     |               |
|       |             |              |                         |                    | J ±5%     |               |


## AWCM00120707 Type

### Dimensions



unit:mm

### Recommended Land Pattern



unit:mm

### Electrical Characteristics


| Part No.           | Inductance (nH) | L/Q Test Freq. (MHz) | Q Min. | SRF (MHz)Min. | RDC (Ω)Max. | Irms (mA)Max. | Tolerance            |
|--------------------|-----------------|----------------------|--------|---------------|-------------|---------------|----------------------|
| AWCM001207071N5□00 | 1.5             | 100/250              | 10     | 18000         | 0.03        | 1000          | ±0.1nH,±0.2nH,±0.5nH |
| AWCM001207072N4□00 | 2.4             | 100/250              | 20     | 15000         | 0.05        | 850           | ±0.1nH,±0.2nH,±0.5nH |
| AWCM001207072N5□00 | 2.5             | 100/250              | 20     | 15000         | 0.05        | 850           | ±0.1nH,±0.2nH,±0.5nH |
| AWCM001207072N7□00 | 2.7             | 100/250              | 20     | 15000         | 0.05        | 850           | ±0.1nH,±0.2nH,±0.5nH |
| AWCM001207072N9□00 | 2.9             | 100/250              | 20     | 15000         | 0.07        | 750           | ±0.1nH,±0.2nH,±0.5nH |
| AWCM001207073N9□00 | 3.9             | 100/250              | 25     | 10000         | 0.07        | 750           | 3,5                  |
| AWCM001207074N1□00 | 4.1             | 100/250              | 25     | 10000         | 0.07        | 750           | 3,5                  |
| AWCM001207074N3□00 | 4.3             | 100/250              | 25     | 10000         | 0.07        | 750           | 3,5                  |
| AWCM001207074N7□00 | 4.7             | 100/250              | 25     | 8000          | 0.07        | 750           | 3,5                  |
| AWCM001207075N1□00 | 5.1             | 100/250              | 25     | 8000          | 0.12        | 600           | 3,5                  |
| AWCM001207075N8□00 | 5.8             | 100/250              | 25     | 8000          | 0.12        | 700           | 3,5                  |
| AWCM001207076N2□00 | 6.2             | 100/250              | 25     | 8000          | 0.09        | 700           | 3,5                  |
| AWCM001207076N8□00 | 6.8             | 100/250              | 25     | 6000          | 0.09        | 700           | 3,5                  |
| AWCM001207077N3□00 | 7.3             | 100/250              | 25     | 6000          | 0.13        | 570           | 3,5                  |
| AWCM001207077N5□00 | 7.5             | 100/250              | 25     | 6000          | 0.13        | 570           | 3,5                  |
| AWCM001207078N2□00 | 8.2             | 100/250              | 25     | 5500          | 0.14        | 540           | 3,5                  |
| AWCM001207078N7□00 | 8.7             | 100/250              | 25     | 5500          | 0.14        | 540           | 3,5                  |
| AWCM001207079N1□00 | 9.1             | 100/250              | 25     | 5500          | 0.14        | 540           | 3,5                  |
| AWCM001207079N5□00 | 10              | 100/250              | 25     | 5500          | 0.14        | 540           | 3,5                  |
| AWCM0012070710N□00 | 10              | 100/250              | 25     | 5500          | 0.17        | 500           | 2,3,5                |
| AWCM0012070711N□00 | 11              | 100/250              | 30     | 5500          | 0.14        | 500           | 2,3,5                |
| AWCM0012070712N□00 | 12              | 100/250              | 30     | 5500          | 0.14        | 500           | 2,3,5                |
| AWCM0012070713N□00 | 13              | 100/250              | 25     | 5000          | 0.21        | 430           | 2,3,5                |
| AWCM0012070715N□00 | 15              | 100/250              | 30     | 5000          | 0.16        | 460           | 2,3,5                |
| AWCM0012070716N□00 | 16              | 100/250              | 25     | 4500          | 0.24        | 370           | 2,3,5                |
| AWCM0012070718N□00 | 18              | 100/250              | 25     | 4500          | 0.27        | 370           | 2,3,5                |
| AWCM0012070719N□00 | 19              | 100/250              | 25     | 4500          | 0.27        | 370           | 2,3,5                |
| AWCM0012070720N□00 | 20              | 100/250              | 25     | 4000          | 0.27        | 370           | 2,3,5                |
| AWCM0012070722N□00 | 22              | 100/250              | 25     | 4000          | 0.3         | 310           | 2,3,5                |
| AWCM0012070723N□00 | 23              | 100/250              | 25     | 3800          | 0.3         | 310           | 2,3,5                |
| AWCM0012070724N□00 | 24              | 100/250              | 25     | 3500          | 0.52        | 280           | 2,3,5                |
| AWCM0012070727N□00 | 27              | 100/250              | 25     | 3500          | 0.52        | 280           | 2,3,5                |

Note: □-tolerance B=±0.1nH / C=±0.2nH / D=±0.5nH / H=±3% / J=±5% / G=±2%

1. Operating temperature range - 40°C ~ 125°C(Including self - temperature rise)
2. Irms for a 15°C temperature rise from 25°C ambient.
3. L/Q Test OSC @200mV.
4. Inductance would be correct Chilisin standard piece.
5. Offset value : -0.556nH


## AWCM00120707 Type

### ■ Dimensions



unit:mm

### ■ Recommended Land Pattern



unit:mm

### ■ Electrical Characteristics



| Part No.           | Inductance<br>(nH) | L/Q Test<br>Freq.<br>(MHz) | Q<br>Min. | SRF<br>(MHz)Min. | RDC<br>(Ω)Max. | Irms<br>(mA)Max. | Tolerance |
|--------------------|--------------------|----------------------------|-----------|------------------|----------------|------------------|-----------|
| AWCM0012070730N□00 | 30                 | 100/250                    | 25        | 3300             | 0.58           | 270              | 2,3,5     |
| AWCM0012070733N□00 | 33                 | 100/250                    | 25        | 3200             | 0.63           | 260              | 2,3,5     |
| AWCM0012070736N□00 | 36                 | 100/250                    | 25        | 3100             | 0.63           | 260              | 2,3,5     |
| AWCM0012070739N□00 | 39                 | 100/250                    | 25        | 3000             | 0.7            | 250              | 2,3,5     |
| AWCM0012070740N□00 | 40                 | 100/250                    | 25        | 3000             | 0.7            | 250              | 2,3,5     |
| AWCM0012070747N□00 | 47                 | 100/200                    | 25        | 2900             | 1.08           | 210              | 2,3,5     |
| AWCM0012070751N□00 | 51                 | 100/200                    | 25        | 2850             | 1.08           | 210              | 2,3,5     |
| AWCM0012070756N□00 | 56                 | 100/200                    | 25        | 2800             | 1.17           | 200              | 2,3,5     |
| AWCM0012070762N□00 | 62                 | 100/200                    | 20        | 2600             | 1.82           | 145              | 2,3,5     |
| AWCM0012070768N□00 | 68                 | 100/200                    | 20        | 2500             | 1.96           | 140              | 2,3,5     |
| AWCM0012070772N□00 | 72                 | 100/150                    | 20        | 2500             | 2.1            | 135              | 2,5       |
| AWCM0012070775N□00 | 75                 | 100/150                    | 20        | 2400             | 2.1            | 135              | 2,5       |
| AWCM0012070782N□00 | 82                 | 100/150                    | 20        | 2300             | 2.24           | 130              | 2,5       |
| AWCM0012070791N□00 | 91                 | 100/150                    | 20        | 2100             | 2.38           | 125              | 2,5       |
| AWCM00120707R10□00 | 100                | 100/150                    | 20        | 1500             | 2.52           | 120              | 2,5       |
| AWCM00120707R12□00 | 120                | 100/150                    | 20        | 1000             | 2.66           | 110              | 2,5       |

Note: □-tolerance B=±0.1nH / C=±0.2nH / D=±0.5nH / H=±3% / J=±5% / G=±2%

1. Operating temperature range - 40°C ~ 125°C(Including self - temperature rise)
2. Irms for a 15°C temperature rise from 25°C ambient.
3. L/Q Test OSC @200mV.
4. Inductance would be correct Chilisin standard piece.
5. Offset value : -0.556nH


## AWCM00120707 Type

### Characteristics Graph




## AWCM00161008 Type

### Dimensions



unit:mm

### Recommended Land Pattern



unit:mm

### Electrical Characteristics

| Part No.           | Inductance (nH) | L/Q Test Freq. (MHz) | Q Min. | SRF (MHz)Min. | RDC (Ω)Max. | Irms (mA)Max. | Tolerance            |
|--------------------|-----------------|----------------------|--------|---------------|-------------|---------------|----------------------|
| AWCM001610082N2□00 | 2.2             | 100/250              | 16     | 6000          | 0.049       | 700           | ±0.1nH,±0.2nH,±0.5nH |
| AWCM001610083N6□00 | 3.6             | 100/250              | 25     | 6000          | 0.059       | 850           | 3,5                  |
| AWCM001610083N9□00 | 3.9             | 100/250              | 35     | 6000          | 0.059       | 850           | 3,5                  |
| AWCM001610084N3□00 | 4.3             | 100/250              | 35     | 6000          | 0.059       | 850           | 3,5                  |
| AWCM001610084N7□00 | 4.7             | 100/250              | 35     | 6000          | 0.059       | 850           | 3,5                  |
| AWCM001610085N6□00 | 5.6             | 100/250              | 35     | 6000          | 0.082       | 750           | 3,5                  |
| AWCM001610086N2□00 | 6.2             | 100/250              | 35     | 6000          | 0.082       | 750           | 3,5                  |
| AWCM001610086N8□00 | 6.8             | 100/250              | 35     | 6000          | 0.082       | 750           | 3,5                  |
| AWCM001610087N5□00 | 7.5             | 100/250              | 35     | 6000          | 0.082       | 750           | 3,5                  |
| AWCM001610088N2□00 | 8.2             | 100/250              | 35     | 6000          | 0.11        | 650           | 3,5                  |
| AWCM001610088N7□00 | 8.7             | 100/250              | 35     | 6000          | 0.11        | 650           | 3,5                  |
| AWCM001610089N1□00 | 9.1             | 100/250              | 35     | 6000          | 0.11        | 650           | 3,5                  |
| AWCM001610089N5□00 | 9.5             | 100/250              | 35     | 6000          | 0.11        | 650           | 3,5                  |
| AWCM0016100810N□00 | 10              | 100/250              | 35     | 6000          | 0.11        | 650           | 2,5                  |
| AWCM0016100811N□00 | 11              | 100/250              | 35     | 6000          | 0.11        | 650           | 2,5                  |
| AWCM0016100812N□00 | 12              | 100/250              | 35     | 6000          | 0.13        | 600           | 2,5                  |
| AWCM0016100813N□00 | 13              | 100/250              | 35     | 6000          | 0.13        | 600           | 2,5                  |
| AWCM0016100815N□00 | 15              | 100/250              | 40     | 6000          | 0.13        | 600           | 2,5                  |
| AWCM0016100816N□00 | 16              | 100/250              | 40     | 5500          | 0.16        | 550           | 2,5                  |
| AWCM0016100818N□00 | 18              | 100/250              | 40     | 5500          | 0.16        | 550           | 2,5                  |
| AWCM0016100820N□00 | 20              | 100/250              | 40     | 4900          | 0.16        | 550           | 2,5                  |
| AWCM0016100822N□00 | 22              | 100/250              | 40     | 4600          | 0.17        | 500           | 2,5                  |
| AWCM0016100824N□00 | 24              | 100/250              | 40     | 3800          | 0.21        | 500           | 2,5                  |
| AWCM0016100827N□00 | 27              | 100/250              | 40     | 3700          | 0.21        | 440           | 2,5                  |
| AWCM0016100830N□00 | 30              | 100/250              | 40     | 3300          | 0.23        | 420           | 2,5                  |
| AWCM0016100833N□00 | 33              | 100/250              | 40     | 3200          | 0.23        | 420           | 2,5                  |
| AWCM0016100836N□00 | 36              | 100/250              | 40     | 2900          | 0.26        | 400           | 2,5                  |
| AWCM0016100839N□00 | 39              | 100/250              | 40     | 2800          | 0.26        | 400           | 2,5                  |
| AWCM0016100843N□00 | 43              | 100/200              | 40     | 2700          | 0.29        | 380           | 2,5                  |
| AWCM0016100847N□00 | 47              | 100/200              | 38     | 2600          | 0.29        | 380           | 2,5                  |
| AWCM0016100851N□00 | 51              | 100/200              | 38     | 2500          | 0.33        | 370           | 2,5                  |
| AWCM0016100856N□00 | 56              | 100/200              | 38     | 2400          | 0.35        | 360           | 2,5                  |

Note: When ordering, please specify tolerance code. Tolerance: B=±0.1 / C=±0.2 / D=±0.5 / G=±2% / H=±3% / J=±5%

1. Operating temperature range - 40°C ~ 125°C(Including self - temperature rise)

2. Irms for a 15°C temperature rise from 25°C ambient.

3. Measure Equipment:

L & Q: Agilent E4991A+Agilent HP16197A


SRF: Agilent HP8753D/Agilent HP8722ES

RDC:Chroma 16502

Irms: HP4284A+HP42841A/HP4285A+HP42841A


## AWCM00161008 Type

### ■ Dimensions



unit:mm

### ■ Recommended Land Pattern



unit:mm

### ■ Electrical Characteristics

| Part No.           | Inductance<br>(nH) | L/Q Test<br>Freq.<br>(MHz) | Q<br>Min. | SRF<br>(MHz)Min. | RDC<br>(Ω)Max. | Irms<br>(mA)Max. | Tolerance |
|--------------------|--------------------|----------------------------|-----------|------------------|----------------|------------------|-----------|
| AWCM0016100862N□00 | 62                 | 100/200                    | 38        | 2300             | 0.51           | 280              | 2,5       |
| AWCM0016100868N□00 | 68                 | 100/200                    | 38        | 2200             | 0.38           | 340              | 2,5       |
| AWCM0016100872N□00 | 72                 | 100/150                    | 34        | 2100             | 0.56           | 270              | 2,5       |
| AWCM0016100875N□00 | 75                 | 100/150                    | 34        | 2050             | 0.56           | 270              | 2,5       |
| AWCM0016100882N□00 | 82                 | 100/150                    | 34        | 2000             | 0.6            | 250              | 2,5       |
| AWCM0016100891N□00 | 91                 | 100/150                    | 34        | 1900             | 0.64           | 230              | 2,5       |
| AWCM00161008R10□00 | 100                | 100/150                    | 34        | 1800             | 0.68           | 220              | 2,5       |
| AWCM00161008R11□00 | 110                | 100/150                    | 32        | 1700             | 1.2            | 200              | 2,5       |
| AWCM00161008R12□00 | 120                | 100/150                    | 32        | 1600             | 1.3            | 180              | 2,5       |
| AWCM00161008R13□00 | 130                | 100/150                    | 32        | 1450             | 1.4            | 170              | 2,5       |
| AWCM00161008R15□00 | 150                | 100/150                    | 32        | 1400             | 1.5            | 160              | 2,5       |
| AWCM00161008R16□00 | 160                | 100/150                    | 32        | 1350             | 2.1            | 150              | 2,5       |
| AWCM00161008R18□00 | 180                | 100/100                    | 25        | 1300             | 2.2            | 140              | 2,5       |
| AWCM00161008R20□00 | 200                | 100/100                    | 25        | 1250             | 2.4            | 120              | 2,5       |
| AWCM00161008R22□00 | 220                | 100/100                    | 25        | 1200             | 2.5            | 120              | 2,5       |
| AWCM00161008R27□00 | 270                | 100/100                    | 30        | 960              | 3.4            | 110              | 2,5       |
| AWCM00161008R33□00 | 330                | 100/100                    | 30        | 800              | 5.5            | 85               | 2,5       |
| AWCM00161008R39□00 | 390                | 100/100                    | 30        | 800              | 6.2            | 80               | 2,5       |
| AWCM00161008R47□00 | 470                | 100/100                    | 30        | 700              | 7              | 75               | 2,5       |

**Note:** When ordering, please specify tolerance code. Tolerance: B=±0.1 / C=±0.2 / D=±0.5 / G=±2% / H=±3% / J=±5%

1. Operating temperature range - 40°C ~ 125°C(Including self - temperature rise)

2. Irms for a 15°C temperature rise from 25°C ambient.

3. Measure Equipment:

L & Q: Agilent E4991A+Agilent HP16197A



SRF: Agilent HP8753D/Agilent HP8722ES

RDC:Chroma 16502

Irms: HP4284A+HP42841A/HP4285A+HP42841A

## AWCM00161008 Type


### Characteristics Graph



## ■ Packaging

### Tape Dimensions

Figure 1



### Tape Material






Figure 2



### Reel Dimensions



### Dimensions in mm

| TYPE         | Fig. | Tape Dimensions |      |      |   |   |     |      |  | Reel Dimensions |        |        |         | Quantity<br>PCS / Reel |
|--------------|------|-----------------|------|------|---|---|-----|------|--|-----------------|--------|--------|---------|------------------------|
|              |      | A               | B    | T    | W | P | F   | K    |  | A               | B      | C      | D       |                        |
| AWCM00120707 | 1    | 0.67            | 1.23 | 0.75 | 8 | 2 | 3.5 | 0.59 |  | 178±1           | 60±0.5 | 12±0.5 | 1.5±0.5 | 4000                   |
| AWCM00161008 | 2    | 1.20            | 1.8  | 1.05 | 8 | 4 | 3.5 | -    |  | 178             | 60     | 12     | 1.5     | 4000                   |

### For More Information:

Americas - [prodinfo\\_power\\_americas@yageo.com](mailto:prodinfo_power_americas@yageo.com) | Europe - [prodinfo\\_power\\_emea@yageo.com](mailto:prodinfo_power_emea@yageo.com) | Asia - [prodinfo\\_power\\_asia@yageo.com](mailto:prodinfo_power_asia@yageo.com)

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2022. Pulse Electronics, Inc. All rights reserved.



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Pulse:

|                                    |                                    |                                    |                                    |
|------------------------------------|------------------------------------|------------------------------------|------------------------------------|
| <a href="#">AWCM0011060510NG00</a> | <a href="#">AWCM0011060510NH00</a> | <a href="#">AWCM0011060510NJ00</a> | <a href="#">AWCM0011060511NG00</a> |
| <a href="#">AWCM0011060511NH00</a> | <a href="#">AWCM0011060511NJ00</a> | <a href="#">AWCM0011060512NG00</a> | <a href="#">AWCM0011060512NH00</a> |
| <a href="#">AWCM0011060512NJ00</a> | <a href="#">AWCM0011060513NG00</a> | <a href="#">AWCM0011060513NH00</a> | <a href="#">AWCM0011060513NJ00</a> |
| <a href="#">AWCM0011060515NG00</a> | <a href="#">AWCM0011060515NH00</a> | <a href="#">AWCM0011060515NJ00</a> | <a href="#">AWCM0011060516NG00</a> |
| <a href="#">AWCM0011060516NH00</a> | <a href="#">AWCM0011060516NJ00</a> | <a href="#">AWCM0011060518NG00</a> | <a href="#">AWCM0011060518NH00</a> |
| <a href="#">AWCM0011060518NJ00</a> | <a href="#">AWCM0011060519NG00</a> | <a href="#">AWCM0011060519NH00</a> | <a href="#">AWCM0011060519NJ00</a> |
| <a href="#">AWCM001106051N5B00</a> | <a href="#">AWCM001106051N5C00</a> | <a href="#">AWCM001106051N5D00</a> | <a href="#">AWCM0011060520NG00</a> |
| <a href="#">AWCM0011060520NH00</a> | <a href="#">AWCM0011060520NJ00</a> | <a href="#">AWCM0011060522NG00</a> | <a href="#">AWCM0011060522NH00</a> |
| <a href="#">AWCM0011060522NJ00</a> | <a href="#">AWCM0011060523NG00</a> | <a href="#">AWCM0011060523NH00</a> | <a href="#">AWCM0011060523NJ00</a> |
| <a href="#">AWCM0011060524NG00</a> | <a href="#">AWCM0011060524NH00</a> | <a href="#">AWCM0011060524NJ00</a> | <a href="#">AWCM0011060527NG00</a> |
| <a href="#">AWCM0011060527NH00</a> | <a href="#">AWCM0011060527NJ00</a> | <a href="#">AWCM001106052N4B00</a> | <a href="#">AWCM001106052N4C00</a> |
| <a href="#">AWCM001106052N4D00</a> | <a href="#">AWCM001106052N5B00</a> | <a href="#">AWCM001106052N5C00</a> | <a href="#">AWCM001106052N5D00</a> |
| <a href="#">AWCM001106052N7B00</a> | <a href="#">AWCM001106052N7C00</a> | <a href="#">AWCM001106052N7D00</a> | <a href="#">AWCM001106052N9B00</a> |
| <a href="#">AWCM001106052N9C00</a> | <a href="#">AWCM001106052N9D00</a> | <a href="#">AWCM0011060530NG00</a> | <a href="#">AWCM0011060530NH00</a> |
| <a href="#">AWCM0011060530NJ00</a> | <a href="#">AWCM0011060533NG00</a> | <a href="#">AWCM0011060533NH00</a> | <a href="#">AWCM0011060533NJ00</a> |
| <a href="#">AWCM0011060536NG00</a> | <a href="#">AWCM0011060536NH00</a> | <a href="#">AWCM0011060536NJ00</a> | <a href="#">AWCM0011060539NG00</a> |
| <a href="#">AWCM0011060539NH00</a> | <a href="#">AWCM0011060539NJ00</a> | <a href="#">AWCM001106053N9H00</a> | <a href="#">AWCM001106053N9J00</a> |
| <a href="#">AWCM0011060540NG00</a> | <a href="#">AWCM0011060540NH00</a> | <a href="#">AWCM0011060540NJ00</a> | <a href="#">AWCM0011060547NG00</a> |
| <a href="#">AWCM0011060547NH00</a> | <a href="#">AWCM0011060547NJ00</a> | <a href="#">AWCM001106054N1H00</a> | <a href="#">AWCM001106054N1J00</a> |
| <a href="#">AWCM001106054N3H00</a> | <a href="#">AWCM001106054N3J00</a> | <a href="#">AWCM001106054N7H00</a> | <a href="#">AWCM001106054N7J00</a> |
| <a href="#">AWCM0011060551NG00</a> | <a href="#">AWCM0011060551NH00</a> | <a href="#">AWCM0011060551NJ00</a> | <a href="#">AWCM0011060556NG00</a> |
| <a href="#">AWCM0011060556NH00</a> | <a href="#">AWCM0011060556NJ00</a> | <a href="#">AWCM001106055N1H00</a> | <a href="#">AWCM001106055N1J00</a> |
| <a href="#">AWCM001106055N8H00</a> | <a href="#">AWCM001106055N8J00</a> | <a href="#">AWCM0011060562NG00</a> | <a href="#">AWCM0011060562NH00</a> |
| <a href="#">AWCM0011060562NJ00</a> | <a href="#">AWCM0011060568NG00</a> | <a href="#">AWCM0011060568NH00</a> | <a href="#">AWCM0011060568NJ00</a> |
| <a href="#">AWCM001106056N2H00</a> | <a href="#">AWCM001106056N2J00</a> | <a href="#">AWCM001106056N8H00</a> | <a href="#">AWCM001106056N8J00</a> |