

Description: 1608 Diplexer
PART NUMBER: DPX1608LKE7R2460A
Features:

- Compact Size
- Low loss
- High Soldering Heat Resistance

Applications:

- WLAN
- WiFi6E
- WiFi7

ELECTRICAL SPECIFICATIONS
Low-Band

Item	Frequency Range (MHz)	Min.	Typ.	Max.
Insertion loss (dB)	2400~2500	-	0.66	0.8
Return loss (dB)	2400~2500	10	15.0	-
Attenuation (dB)	30~1000	8	14.3	-
	4800~7125	33	38.3	-
	7200~7500	33	38.9	-
	7700~7950	33	44.1	-
	7500~12000	15	22.5	-

High-Band

Item	Frequency Range (MHz)	Min.	Typ.	Max.
Insertion loss (dB)	5150~7125	-	0.88	1.2
Return loss (dB)	5150~7125	10	-	-
Attenuation (dB)	100~1000	35	60.9	-
	1000~2300	35	45.8	-
	2400~2500	35	45.3	-
	2700~3500	20	23.9	-
	9600~14250	25	28.5	-
	14700~21375	10	19.2	-

In the effort to improve our products, we reserve the right to make changes judged to be necessary.

CONFIDENTIAL AND PROPRIETARY INFORMATION

This document contains confidential and proprietary information of Pulse Electronics, Inc. (Pulse) and is protected by copyright, trade secret and other state and federal laws. Its receipt or possession does not convey any rights to reproduce, disclose its contents, or to manufacture, use or sell anything it may describe. Reproduction, disclosure or use without specific written authorization of Pulse is strictly forbidden.

For more information:

Pulse Worldwide Headquarters
 15255 Innovation Drive #100
 San Diego, CA 92128
 USA
 Tel: 1-858-674-8100

Pulse/Larsen Antennas
 18110 SE 34th St Bldg 2 Suite 250
 Vancouver, WA 98683
 USA
 Tel: 1-360-944-7551

Europe Headquarters
 Pulse GmbH & Do, KG
 Zeppelinstrasse 15
 Herrenberg, Germany
 Tel: 49 7032 7806 0

Pulse (Suzhou) Wireless Products Co, Inc.
 99 Huo Ju Road(#29 Bldg,4th Phase
 Suzhou New District
 Jiangsu Province, Suzhou 215009 PR China
 Tel: 86 512 6807 9998



Description: 1608 Diplexer
PART NUMBER: DPX1608LKE7R2460A
ELECTRICAL SPECIFICATIONS
Common

Item	Frequency Range (MHz)	Min.	Typ.	Max.
Return loss (dB)	2400~2500	10	15.0	-
	5150~7125	10	-	-

Isolation

Item	Frequency Range (MHz)	Min.	Typ.	Max.
HB to LB (dB)	2400~2500	35	45.9	-
	4800~7125	33	40.6	-
	10300~14250	-	21.3	-
	15450~20000	-	17.9	-

*Impedance for high-band = Match to client's chipset

Operating Temperature Range : -40~85°C


Power Capacity : 3W max.

Description: 1608 Diplexer

PART NUMBER: DPX1608LKE7R2460A

MECHANICAL DIMENSION

Outline




Dimension

L	W	T	a
1.60±0.10	0.80±0.10	0.70 max.	0.20±0.10
b	c	g	p
0.20±0.15	0.15±0.10	0.30±0.10	0.50±0.05

NOTE : Dimensions in mm.

Termination

Top View




Terminal name


Function

1	High band
2	GND
3	Low band
4	GND
5	Common
6	GND

Reference design of EVB



Unit : mm



*Line width should be designed to match 50Ω characteristic impedance, depending on PCB material and thickness.

In the effort to improve our products, we reserve the right to make changes judged to be necessary.


CONFIDENTIAL AND PROPRIETARY INFORMATION

This document contains confidential and proprietary information of Pulse Electronics, Inc. (Pulse) and is protected by copyright, trade secret and other state and federal laws. Its receipt or possession does not convey any rights to reproduce, disclose its contents, or to manufacture, use or sell anything it may describe. Reproduction, disclosure or use without specific written authorization of Pulse is strictly forbidden.

Description: 1608 Diplexer

PART NUMBER: DPX1608LKE7R2460A

MEASURING DIAGRAM




Test Instrument :

Agilent E5071C Network Analyzer or equivalent.

*Impedance for high-band=Match to client's chipset

ELECTRICAL PERFORMANCES

Tr1 S21 Log Mag 10.00dB/ Ref 0.000dB [F3]
 Tr2 S31 Log Mag 10.00dB/ Ref 0.000dB [F3]
 Tr3 S11 Log Mag 10.00dB/ Ref 0.000dB [F3]
 Tr4 S23 Log Mag 10.00dB/ Ref 0.000dB [F3]



In the effort to improve our products, we reserve the right to make changes judged to be necessary.

CONFIDENTIAL AND PROPRIETARY INFORMATION



This document contains confidential and proprietary information of Pulse Electronics, Inc. (Pulse) and is protected by copyright, trade secret and other state and federal laws. Its receipt or possession does not convey any rights to reproduce, disclose its contents, or to manufacture, use or sell anything it may describe. Reproduction, disclosure or use without specific written authorization of Pulse is strictly forbidden.

Description: 1608 Diplexer

PART NUMBER: DPX1608LKE7R2460A


PACKING SPECIFICATION

Peel-off force



The force for peeling of cover tape is 10 grams in the arrow direction.


Dimension (Unit: mm)



TYPE	A	B	C	D	E	F
8 mm	178±1	60+0.5 -0	-	13±0.2	9±0.5	12±0.5
12 mm	178±0.3	60±0.2	19.3±0.1	13.5±0.1	13.6±0.1	-

Taping quantity

SERIES	5824 5724	5320 5220	4532	4516	3225	3216 2520	2012 1608	1005 0605
PCS/Reel	5000	3000	1000	2000	2500	3000	4000	10000



In the effort to improve our products, we reserve the right to make changes judged to be necessary.

CONFIDENTIAL AND PROPRIETARY INFORMATION

This document contains confidential and proprietary information of Pulse Electronics, Inc. (Pulse) and is protected by copyright, trade secret and other state and federal laws. Its receipt or possession does not convey any rights to reproduce, disclose its contents, or to manufacture, use or sell anything it may describe. Reproduction, disclosure or use without specific written authorization of Pulse is strictly forbidden.

Description: 1608 Diplexer**PART NUMBER:** DPX1608LKE7R2460A**REVISION HISTORY**

Revision	Date	Description
Version 1	Oct. 28, 2022	- New issue

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pulse:](#)

[DPX1608LKE7R2460A](#)