



Product: [8744](#)

Electronic, 9 Pr #22 Sol TC, PVC Ins, PVC Jkt, CMG

[Request Sample](#)

Product Description

Electronic, 9 Pair 22AWG (Solid) Tinned Copper, PVC Insulation, PVC Outer Jacket, CMG

Technical Specifications

Product Overview

Suitable Applications:	telephone cables; low voltage analog signals (4-20ma, 0-10v, ...); low voltage control (24v, ...); voice communications
------------------------	---

Construction Details

Conductor				
Element	No. of Elements	Size	Stranding	Material
Pair(s)	9	22 AWG	Solid	TC - Tinned Copper

Insulation			
Element	Material	Nom. Thickness	Color Code
Pair(s)	PVC - Polyvinyl Chloride	0.010 in (0.25 mm)	Black & Red, Black & White, Black & Green, Black & Blue, Black & Yellow, Black & Brown, Black & Orange, Red & White, Red & Green

Outer Jacket		
Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.035 in (0.89 mm)	0.350 in (8.89 mm)
Overall Cable Diameter (Nominal):		0.350 in (8.89 mm)

Electrical Characteristics

Electricals			
Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Current
Pair(s)	16.5 Ohm/1000ft (54.1 Ohm/km)	30 pF/ft (98 pF/m)	1.4 Amps per Conductor at 20°C

Voltage	
UL Voltage Rating	
300 V (CMG), 150 V (UL AWM 2576)	

Mechanical Characteristics

Temperature	
UL Temperature	Operating
80°C (UL AWM 2576)	-20°C to +80°C
Max. Pull Tension:	140 lbs (64 kg)
Bulk Cable Weight:	71 lbs/1000ft (110 kg/km)

Standards and Compliance

Flammability / Reaction to Fire:	UL1685 FT4 Loading
NEC / UL Compliance:	Article 800, CMG
AWM Compliance:	AMW 2576

CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.353 Revision Date: 12-22-2023
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
8744 0601000	Chrome	Reel	1,000 ft	612825214946	C

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[8744 0601000](#)