



Product: [8791](#)

Electronic, 3 C #18 Str TC, PVC Ins, OA TC Srv, PVC Jkt

[Request Sample](#)

Product Description

Electronic, 3 Conductor 18AWG (7x26) Tinned Copper, PVC Insulation, Overall Tinned Copper Serve Shield, PVC Outer Jacket

Technical Specifications

Product Overview

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage control (24v, ...); line level audio; voice communications; panel wiring
------------------------	---

Construction Details

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	3	18 AWG	7x26	TC - Tinned Copper

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PVC - Polyvinyl Chloride	0.022 in (0.56 mm)	0.090 in (2.3 mm)	Black, Red, White

Shield Type	Material	Coverage
Spiral Serve / Screen	Tinned Copper (TC)	80%

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.028 in (0.71 mm)	0.260 in (6.60 mm)
Overall Cable Diameter (Nominal):		0.260 in (6.60 mm)

Electrical Characteristics

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Max. Current
Conductor(s)	7.06 Ohm/1000ft	47 pF/ft (150 pF/m)	84 pF/ft (280 pF/m)	8 Amps per Conductor at 30°C

Voltage Rating
450 V

Mechanical Characteristics

Temperature
Operating
-30°C to +75°C

Bend Radius	
Stationary Min.	Installation Min.
2.6 in (66 mm)	2.6 in (66 mm)

Max. Pull Tension:	85 lbs (39 kg)
Bulk Cable Weight:	42 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.504 Revision Date: 02-03-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
8791 060500	Chrome	Reel	500 ft	612825216490	C
8791 0601000	Chrome	Reel	1,000 ft	612825216483	C
8791 060U1000	Chrome	UnReel	1,000 ft	612825216476	
8791 0605000	Chrome	Reel	5,000 ft	612825216506	C Z

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[8791 060500](#) [8791 060U1000](#) [8791 0601000](#) [8791 0605000](#)