


SMT Power Inductors

Molded powder - PA/PM2242-2243-2244.XXXNLT series




- Ⓟ **Height:** 10.0mm Max
- Ⓟ **Footprint:** 12.2mm x 11.3mm Max
- Ⓟ **Current Rating:** up to 40 Apk
- Ⓟ **Inductance Range:** 0.28 uH to 15 uH
- Ⓟ **Rated Voltage between Terminals:** 50V
- Ⓟ High current, low DCR, and high efficiency
- Ⓟ Minimized acoustic noise and minimized leakage flux noise
- Ⓟ Available in Commercial (PA224X) and Automotive (PM224X) grades

Electrical Specifications @ 25°C, Operating Temperature Range -55°C to +155°C


| Part Number | | Inductance ⁶ 100KHz, 0.1V uH±20% | Rated ³ Current A | DC Resistance MAX. mΩ | Saturation ² Current A | K Factor for Core Loss |
|--------------------------------|---|---|------------------------------------|-----------------------------|--------------------------------------|------------------------------|
| Commerical (-55°C to 125°C) | Automotive ^{4,5} (-55°C to 155°C) | | | | | |
| PA2242.281NLT | PM2242.281NLT | 0.28 | 35.0 | 1.60 | 58.0 | 114.6 |
| PA2242.561NLT | PM2242.561NLT | 0.56 | 32.0 | 2.75 | 39.0 | 72.9 |
| PA2242.821NLT | PM2242.821NLT | 0.82 | 25.0 | 4.10 | 32.0 | 53.5 |
| PA2242.901NLT | PM2242.901NLT | 0.90 | 24.0 | 4.20 | 31.0 | 53.5 |
| PA2242.102NLT | PM2242.102NLT | 1.00 | 23.0 | 4.95 | 30.0 | 52.2 |
| PA2242.152NLT | PM2242.152NLT | 1.50 | 18.0 | 6.60 | 25.0 | 42.2 |
| PA2243.681NLT | PM2243.681NLT | 0.68 | 34.0 | 1.50 | 50.0 | 53.5 |
| PA2243.102NLT | PM2243.102NLT | 1.00 | 28.5 | 2.32 | 44.0 | 52.3 |
| PA2243.122NLT | PM2243.122NLT | 1.20 | 26.5 | 2.64 | 40.0 | 42.2 |
| PA2243.152NLT | PM2243.152NLT | 1.50 | 24.5 | 3.30 | 36.0 | 42.2 |
| PA2243.222NLT | PM2243.222NLT | 2.20 | 20.0 | 4.84 | 30.0 | 34.9 |
| PA2243.332NLT | PM2243.332NLT | 3.30 | 16.8 | 7.70 | 25.0 | 29.7 |
| PA2243.472NLT | PM2243.472NLT | 4.70 | 14.0 | 10.72 | 22.0 | 22.9 |
| PA2244.102NLT | PM2244.102NLT | 1.00 | 40.0 | 1.20 | 42.0 | 53.5 |
| PA2244.152NLT | PM2244.152NLT | 1.50 | 35.5 | 1.76 | 31.0 | 42.3 |
| PA2244.222NLT | PM2244.222NLT | 2.20 | 32.0 | 2.80 | 29.0 | 34.9 |
| PA2244.332NLT | PM2244.332NLT | 3.30 | 25.0 | 4.10 | 23.4 | 27.9 |
| PA2244.472NLT | PM2244.472NLT | 4.70 | 24.0 | 5.70 | 21.4 | 23.6 |
| PA2244.562NLT | PM2244.562NLT | 5.60 | 21.2 | 7.20 | 19.6 | 21.2 |
| PA2244.682NLT | PM2244.682NLT | 6.80 | 18.5 | 8.90 | 18.5 | 19.1 |
| PA2244.822NLT | PM2244.822NLT | 8.20 | 17.1 | 12.40 | 16.3 | 16.0 |
| PA2244.103NLT | PM2244.103NLT | 10.0 | 15.5 | 13.75 | 14.6 | 13.6 |
| PA2244.153NLT | PM2244.153NLT | 15.0 | 13.8 | 19.30 | 12.5 | 11.9 |

Notes:


1. Actual temperature of the component during system operation (ambient plus temperature rise) must be within the standard operating range.
2. The saturation current is the current at which the initial inductance is guaranteed to drop by no more than 40%. The typical inductance at a specified current can be found on the typical performance curves.
3. The rated current is the DC current required to raise the component temperature by approximately 40 °C. Take note that the components' performance varies depending on the system condition. It is suggested that the component be tested at the system level, to verify the temperature rise of the component during system operation.
4. The part temperature (ambient+temp rise) should not exceed 125 °C under worst case operating conditions. Circuit design, PCB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application.
5. PM224X.XXXNL series are AEC-Q200 certified and IATF 16949 compliance, but the resistance to solvents test is waived. The inductance and mechanical dimensions will do 100% test in mass production due to the Cpk <1.33.
6. Special Characteristics  for PM224X.XXXNL.

Mechanical

PA/PM224X.XXXNLT



FINAL LAYOUT




SUGGESTED PAD LAYOUT

| Series | A | B | C | D | E | F | L | G | H |
|------------------|----------|----------|---------|-------------------------------------|---------|---------|-----------|-----------|-----------|
| PA/PM2242.XXXNLT | 11.9±0.3 | 11.0±0.3 | 2.9±0.2 | 9.0±0.5 | 2.4±0.2 | 4.4±0.3 | 10.5(REF) | 3.7(REF) | 11.0(REF) |
| PA/PM2243.XXXNLT | 11.9±0.3 | 11.0±0.3 | 5.7±0.3 | 9.0 ^{+1.0} _{-0.5} | 2.4±0.2 | 4.4±0.3 | 10.5(REF) | 3.7(REF) | 11.0(REF) |
| PA/PM2244.XXXNLT | 11.9±0.3 | 11.0±0.3 | 9.7±0.3 | 9.0(REF) | 2.4±0.2 | 4.4±0.3 | 10.5(REF) | 3.7 (REF) | 11.0(REF) |

All Dimensions in mm.

TAPE & REEL INFO




SURFACE MOUNTING TYPE, REEL/TAPE LIST

| PART NUMBER | REEL SIZE (mm) | | TAPE SIZE (mm) | | | QTY |
|------------------|----------------|------|----------------|----|----------------|------|
| | A | G | P ₁ | W | K ₀ | |
| PA/PM2242.XXXNLT | Ø330 | 24.4 | 16 | 24 | 3.4 | 1000 |
| PA/PM2243.XXXNLT | Ø330 | 24.4 | 16 | 24 | 6.3 | 500 |
| PA/PM2244.XXXNLT | Ø330 | 24.4 | 16 | 24 | 10.3 | 300 |

CORE LOSS vs FLUX DENSITY

CORE LOSS vs FLUX DENSITY

PA/PM2242.XXXNLT




$$Bp-p = K \cdot L(uH) \cdot \Delta I(A)$$

SMT Power Inductors

Molded powder - PA/PM2242-2243-2244.XXXNLT series


CORE LOSS vs FLUX DENSITY

PA/PM2243.XXXNLT



$$Bp-p = K \cdot L(uH) \cdot \Delta I(A)$$

PA/PM2244.XXXNLT



$$Bp-p = K \cdot L(uH) \cdot \Delta I(A)$$

Americas - prodinfo_power_americas@yageo.com | Europe - prodinfo_power_emea@yageo.com | Asia - prodinfo_power_asia@yageo.com

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2023. Pulse Electronics, Inc. All rights reserved.

YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pulse:

[PA2242.561NLT](#) [PA2242.821NLT](#) [PA2242.152NLT](#) [PA2242.102NLT](#) [PA2242.281NLT](#) [PA2242.901NLT](#)