



Product: [88241](#)

Analog Video, RG59, #23 Solid BCCS, 95% BC Braid, FEP Jacket, CMP



Product Description

23 AWG Solid .023" bare copper-covered steel conductor, plenum, FEP insulation, bare copper braid shield (95% coverage), FEP jacket.

Technical Specifications

Product Overview

Suitable Applications:	Standard analog video
------------------------	-----------------------

Construction Details

RG Type:	59
----------	----

Conductor

No. of Elements	Size	Stranding	Nom. Diameter	Material
1	23 AWG	Solid	0.023 in	BCCS - Bare Copper Covered Steel

Insulation

Material	Nom. Insulation Diameter	Color Code
FEP - Fluorinated Ethylene Propylene	0.132 in (3.35 mm)	Clear

Outer Shield

Outer Shield Type	Material	Coverage
Braid	Bare Copper (BC)	95%

Outer Jacket

Material	Nom. Diameter
FEP - Fluorinated Ethylene Propylene	0.19 in (4.8 mm)

Overall Cable Diameter (Nominal):	0.19 in (4.8 mm)
-----------------------------------	------------------

Electrical Characteristics

Attenuation

Frequency	Nom. Attenuation
1 MHz	0.5 dB/100ft
10 MHz	1 dB/100ft
50 MHz	2.3 dB/100ft
100 MHz	3.3 dB/100ft
200 MHz	5.2 dB/100ft
400 MHz	8.4 dB/100ft
700 MHz	11.6 dB/100ft
900 MHz	13.8 dB/100ft
1000 MHz	14.8 dB/100ft

Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
49 Ohm/1000ft (160 Ohm/km)	2.6 Ohm/1000ft (8.5 Ohm/km)	19.5 pF/ft (64.0 pF/m)	75 Ohm	70%

Voltage

UL Voltage Rating	Voltage Rating
300 V RMS	1700 V RMS

Mechanical Characteristics

Temperature

Operating
-70°C To +200°C

Bend Radius

Stationary Min.	Installation Min.
2.5 in (64 mm)	2.5 in (64 mm)

Max. Pull Tension:	70 lbs (32 kg)
Bulk Cable Weight:	37 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Outdoor, Burial
Flammability / Reaction to Fire:	NFPA 262, FT6, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMP
CEC / C(UL) Compliance:	CMP
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Non-Plenum Number:	8241

Product Notes

Notes:	PF_88241 1)# Elements@Conductor1:-In Stibo it was Blank and now changed to 1. 2)Size@Conductor1 :-In Stibo it was 23 now changed to 23AWG. 3)Color@Color Chart1 01 :- In stibo it was Blank now Changed to Clear. 4)Coverage@OuterShield1 1 - in stibo it was 95% Now changed to 97%. 5)Cable Diameter (Nominal)- In Stibo it was Blank Now Changed to 0.19 in. 6)Bulk Cable Weight - in stibo it was 36 lbs/1000 ft Now changed to 37 lbs/1000 ft.
--------	---

History

Update and Revision:	Revision Number: 0.459 Revision Date: 04-04-2023
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
88241 010500	Black	Reel	500 ft	612825216957	C
88241 0101000	Black	Reel	1,000 ft	612825216933	C

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[88241 010500](#) [88241 0101000](#)