



**Part Number: 88761**

Single-Pair, (1 pr) 22 AWG (7x30) TC, FEP/FEP, Foil Shld, CMP

[Request Sample](#)

## Product Description

One 22 AWG pair stranded (7x30) tinned copper conductors, twisted pair, FEP insulation, overall Beldfoil® shield (100% coverage), FEP jacket.

## Technical Specifications

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	No. of Pairs
22	7x30	TC - Tinned Copper	1

Conductor Count:	2
Total Number of Pairs:	1
Conductor Size:	22 AWG

#### Insulation

Material	Nominal Wall Thickness
FEP - Fluorinated Ethylene Propylene	0.0065 in

#### Color Chart

Number	Color
1	Black & Red

#### Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum/Polyester	Beldfoil®	100 %	TC - Tinned Copper	22	Stranded mm

#### Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
FEP - Fluorinated Ethylene Propylene	0.116 in	0.014 in

### Construction and Dimensions

#### Cabling

Lay Direction	Twists
Left Hand	8 twist/ft

### Electrical Characteristics

#### Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
15 Ohm/1000ft	12 Ohm/1000ft

#### Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
35 pF/ft	67 pF/ft

#### Inductance

Nominal Inductance
0.16 µH/ft

#### Impedance

Nominal Characteristic Impedance
42 Ohm

#### Current

Element	Max. Recommended Current [A]
10C temperature rise	2.8 Amps per conductor @ 25°C ambient

#### Voltage

UL Voltage Rating
300 V RMS

#### Temperature Range

Operating Temp Range:	-70°C To +200°C
-----------------------	-----------------

#### Mechanical Characteristics

Bulk Cable Weight:	13 lbs/1000ft
Max Recommended Pulling Tension:	27 lbs
Min Bend Radius/Minor Axis:	1.25 in

#### Standards

NEC Articles:	800
NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CMP
CPR Euroclass:	Eca

#### Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

#### Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes

#### Flammability, LS0H, Toxicity Testing

UL Flammability:	NFPA 262
CSA Flammability:	FT6
UL voltage rating:	300 V RMS

#### Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

#### Part Number

Non-Plenum Number:	8761
--------------------	------

#### Variants

Item #	Color	Footnote
88761 002100	Red	C
88761 0021000	Red	C
88761 002500	Red	C

88761 0025000	Red	
88761 002U1000	Red	

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.