

89272 Twinax - 78 Ohm Twinax


 For more Information  
 please call

1-800-Belden1

**General Description:**

78 ohm, 20 AWG stranded (7x28) .038" tinned copper conductors, plenum, FEP Teflon® insulation, tinned copper braid shield (93% coverage), FEP Teflon® jacket.

**Physical Characteristics (Overall)****Conductor****AWG:**

# Pairs	AWG	Stranding	Conductor Material	Dia. (in.)
1	20	7x28	TC - Tinned Copper	.038

Total Number of Conductors: 2

**Insulation****Insulation Material:**

Insulation Trade Name	Insulation Material	Wall Thickness (in.)	Dia. (in.)
Teflon®	FEP - Fluorinated Ethylene Propylene	0.018	0.074

**Outer Shield****Outer Shield Material:**

Type	Outer Shield Material	Coverage (%)
Braid	TC - Tinned Copper	93

**Outer Jacket****Outer Jacket Material:**

Outer Jacket Trade Name	Outer Jacket Material	Nom. Wall Thickness (in.)
Teflon®	FEP - Fluorinated Ethylene Propylene	0.014

**Overall Cable**

Overall Nominal Diameter: 0.198 in.

**Pair****Pair Color Code Chart:**

Number	Color
1	Clear & Blue

**Mechanical Characteristics (Overall)**

Operating Temperature Range: -70°C To +200°C

Bulk Cable Weight: 34 lbs/1000 ft.

Max. Recommended Pulling Tension: 68 lbs.

Min. Bend Radius/Minor Axis: 2 in.

**Applicable Specifications and Agency Compliance (Overall)****Applicable Standards & Environmental Programs**

NEC/(UL) Specification: CMP

CEC/C(UL) Specification: CMP

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: No

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS):	Yes
---------------------------------	-----

EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
---------------------------------------	------------

EU Directive 2002/96/EC (WEEE):	Yes
---------------------------------	-----

EU Directive 2003/11/EC (BFR):	Yes
--------------------------------	-----

CA Prop 65 (CJ for Wire & Cable):	Yes
-----------------------------------	-----

MII Order #39 (China RoHS):	Yes
-----------------------------	-----

**Flame Test**

UL Flame Test:	NFPA 262
----------------	----------

CSA Flame Test:	FT6
-----------------	-----

**Suitability**

Suitability - Indoor:	Yes
-----------------------	-----

Suitability - Outdoor:	Yes
------------------------	-----

Suitability - Aerial:	Yes
-----------------------	-----

Suitability - Burial:	Yes
-----------------------	-----

**Plenum/Non-Plenum**

Plenum (Y/N):	Yes
---------------	-----

Non-Plenum Number:	9272
--------------------	------

**Electrical Characteristics (Overall)****Nom. Characteristic Impedance:**

Impedance (Ohm)

78

**Nom. Inductance:**

Inductance (µH/ft)

0.200

**Nom. Capacitance Conductor to Conductor:**

Capacitance (pF/ft)

18.4

**Nominal Velocity of Propagation:**

VP (%)

69.5

**Nominal Delay:**

Delay (ns/ft)

1.46

**Nom. Conductor DC Resistance:**

DCR @ 20°C (Ohm/1000 ft)

9.5

**Nominal Outer Shield DC Resistance:**

DCR @ 20°C (Ohm/1000 ft)

3.9

**Nom. Attenuation:**

Freq. (MHz) Attenuation (dB/100 ft.)

1 0.6

10 2.1

50 5.0

100 7.5

200 11.0

400 16.0

**Max. Operating Voltage - UL:**

**Voltage**

300 V RMS

**Max. Operating Voltage - Non-UL:****Voltage**

600 V RMS

**Notes (Overall)**

**Notes:** Teflon® is a registered trademark of E. I. duPont de Nemours and Co. used under license by Belden, Inc. Suitable for aerial applications when supported by a messenger wire.

**Put Ups and Colors:**

Item #	Putup	Ship Weight	Color	Notes	Item Desc
89272 0061000	1,000 FT	38.000 LB	BLUE, LIGHT	C	2#20 FEP BRD FEP 78 OHM
89272 006500	500 FT	19.000 LB	BLUE, LIGHT	C	2#20 FEP BRD FEP 78 OHM

**Notes:**

C = CRATE REEL PUT-UP.

Revision Number: 2    Revision Date: 10-16-2012

© 2019 Belden, Inc.  
 All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[89272 0061000](#) [89272 006500](#)