


Surface Mount Ceramic Chip Capacitors – Low Profile MLCC

Outline Drawing



Dimensions – Millimeters (Inches)

EIA Size Code	Metric Size Code	L Length	W Width	B Bandwidth	S Separation
0805	2012	2.0 (.079) ± 0.2 (.008)	1.25 (.049) ± 0.2 (.008)	0.5 (.02) ± 0.25 (.010)	-
1206	3216	3.2 (.126) ± 0.2 (.008)	1.6 (.063) ± 0.2 (.008)	0.5 (.02) ± 0.25 (.010)	-

See Capacitance Value Table for thickness dimension.

Capacitance Values - X5R Dielectric

Capacitance Value (μF)	KEMET Part Number	Voltage	Capacitance Tolerance	Thickness	Qty 7" Reel
4.7	C0805L475(1)9PAC	6.3	±10%, ±20%	0.85 (.033) ± 0.1 (.004)	4,000
10.0	C0805L106(1)9PAC	6.3	±10%, ±20%	0.85 (.033) ± 0.1 (.004)	4,000
10.0	C0805L106(1)8PAC	10	±10%, ±20%	0.85 (.033) ± 0.1 (.004)	4,000
1.0	C1206L105(1)3PAC	25	±10%, ±20%	0.78 (.031) ± 0.1 (.004)	4,000
4.7	C1206L475(1)4PAC	16	±10%, ±20%	0.90 (.035) ± 0.1 (.004)	4,000


(1) To complete KEMET part number insert K for ±10% or M for ±20% capacitance tolerance.

Capacitance Values - X7R Dielectric

Capacitance Value (μF)	KEMET Part Number	Voltage	Capacitance Tolerance	Thickness	Qty 7" Reel
1.0	C0805L105(1)8RAC	10	±10%, ±20%	0.78 (.031) ± 0.1 (.004)	4,000

(1) To complete KEMET part number insert K for ±10% or M for ±20% capacitance tolerance.

Capacitor Ordering Information



Electrical Parameters - X5R Dielectric

As detailed in the KEMET Surface Mount Catalog F3102 for X5R, with following specific requirements based on room temperature (25°C) parameters:

- Operating Range: -55°C to +85°C, with no-bias capacitance shift limited to $\pm 15\%$ over that range.
- Insulation Resistance (IR) measured after 2 minutes at rated voltage @ 25°C: Limit is 500 megohm microfarads or 10000M Ω , whichever is less.
- Capacitance and Dissipation Factor (DF) measured at the following conditions. DF Limit is 10%. 1 kHz and 1 Vrms.

Electrical Parameters - X7R Dielectric

As detailed in the KEMET Surface Mount Catalog F3102 for X7R, with following specific requirements based on room temperature (25°C) parameters:

- Operating Range: -55°C to +125°C, with no-bias capacitance shift limited to $\pm 15\%$ over that range.
- Insulation Resistance (IR) measured after 2 minutes at rated voltage @ 25°C: Limit is 500 megohm microfarads or 10000M Ω , whichever is less.
- Capacitance and Dissipation Factor (DF) measured at the following conditions. DF Limit is 5%. 1 kHz and 1 Vrms.

Soldering Process

These components are suitable for reflow only. All parts incorporate the standard KEMET barrier layer of pure nickel, with an overplate of pure tin to provide excellent solderability as well as resistance to leaching.

Marking

These chips will be supplied unmarked.

In general, the information in the KEMET Surface Mount catalog F3102 applies to these capacitors. The information in this bulletin supplements that in the catalog.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

KEMET:

[C0805L475K9PACTU](#) [C0805L106K9PACTU](#) [C0805L105K8RACTU](#) [C1206L475K4PACTU](#) [C1206L105K3PACTU](#)
[C0805L106K8PACTU](#) [C1206L475K3PACTU](#) [C0805L106M8PAC](#) [C0805L105M8RAC](#) [C1206L105M3PAC](#)
[C1206L475M4PAC](#) [C0805L226M9PAC7800](#) [C0805L106M9PAC7800](#)