



Product: [89418](#)

Electronic, 4 C #18 Str TC, FEP Ins, OS, FEP Jkt, CMP

Request Sample

**Product Description**

High Temperature Electronic, 4 Conductor 18AWG (19x30) Tinned Copper, FEP Insulation, Overall Beldfoil® Shield, FEP Outer Jacket, CMP

**Technical Specifications**

Product Overview

Suitable Applications:	extreme high/low temperature environments; chemical resistant; outdoor and burial applications; low voltage analog signals (4-20ma, 0-10v, ...); low voltage control (24v, ...); line level audio; voice communications; panel wiring
------------------------	---

Construction Details

Conductor				
Element	No. of Elements	Size	Stranding	Material
Conductor(s)	4	18 AWG	19x30	TC - Tinned Copper

Insulation				
Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	FEP - Fluorinated Ethylene Propylene	0.007 in (0.18 mm)	0.057 in (1.4 mm)	Black, White, Red, Green

Outer Shield			
Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	20 AWG (19x32) TC

Outer Jacket		
Material	Nom. Thickness	Nom. Diameter
FEP - Fluorinated Ethylene Propylene	0.014 in (0.36 mm)	0.173 in (4.39 mm)

Overall Cable Diameter (Nominal):	0.173 in (4.39 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals					
Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Velocity of Prop.	Max. Current
Conductor(s)	7.06 Ohm/1000ft	30 pF/ft (98 pF/m)	57 pF/ft (190 pF/m)	69%	13.6 Amps per Conductor at 30°C

Voltage	
UL Voltage Rating	
300 V (CMP)	

Mechanical Characteristics

Temperature	
UL Temperature	Operating
150°C	-20°C to +150°C

Bend Radius	
Stationary Min.	Installation Min.
1.7 in (43 mm)	1.7 in (43 mm)

Max. Pull Tension:	114 lbs (51.7 kg)
Bulk Cable Weight:	36 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance, Oil Resistance, Burial
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	NFPA 262, UL 910 (Plenum), IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMP
CEC / C(UL) Compliance:	CMP
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Non-Plenum Number:	9418

Product Notes

Notes:	Chemical Resistance: Gasoline
--------	-------------------------------

History

Update and Revision:	Revision Number: 0.528 Revision Date: 02-03-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
89418 002100	Red	Reel	100 ft	612825220930	C
89418 002500	Red	Reel	500 ft	612825220954	C
89418 0021000	Red	Reel	1,000 ft	612825220947	C
89418 0025000	Red	Reel	5,000 ft	612825220961	C Z

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[89418 002500](#) [89418 0021000](#) [89418 002100](#) [89418 0025000](#)