



Product: [9116SB](#)

75 Ohm SDI Coax, RG-6, 18 AWG Solid BCCS, Foil + 60% AL Braid, LSZH Jkt, CMG-LS, ABS Certified

Product Description

75 Ohm SDI Coax, RG-6, 18 AWG Solid Bare Copper Conductor Covered Steel, PE Insulation, Foil + 60% Aluminum Braid Shield, LSZH Jacket, CMG-LS, Shipboard ABS Type Approved

Technical Specifications

Product Overview

Suitable Applications:	Digital Video, HD-SDI 1080p, ABS approved for marine shipboard and offshore use
------------------------	---

Construction Details

Series Type:	6
--------------	---

Conductor

No. of Elements	Size	Stranding	Nom. Diameter	Material
1	18 AWG	Solid	0.04 in	BCCS - Bare Copper Covered Steel

Insulation

Material	Nom. Insulation Diameter	Color Code
PE - Polyethylene (Foam)	0.18 in (4.6 mm)	White

Table Notes:	Gas Injected
--------------	--------------

Outer Shield

Layer	Outer Shield Type	Material	Material Trade Name	Coverage
1	Tape	Tri-Laminate (Alum+Poly+Alum)	Duobond® II	100%
2	Braid	Aluminum		57%

Outer Jacket

Material	Nom. Diameter
PO - Polyolefin	0.274 in (6.96 mm)

Overall Cable Diameter (Nominal):	0.274 in (6.96 mm)
-----------------------------------	--------------------

Electrical Characteristics

Return Loss (RL)

Frequency	Min. Structural Return Loss
5-1000 MHz	20 dB
1000-2250 MHz	15 dB
2250-3000 MHz	10 dB

Attenuation

Frequency	Max. Attenuation
5 MHz	0.67 dB/100ft
55 MHz	1.6 dB/100ft
211 MHz	2.87 dB/100ft
270 MHz	3.24 dB/100ft
300 MHz	3.43 dB/100ft

350 MHz	3.72 dB/100ft
400 MHz	4 dB/100ft
450 MHz	4.26 dB/100ft
5500 MHz	4.71 dB/100ft
750 MHz	5.59 dB/100ft
870 MHz	6 dB/100ft
1000 MHz	6.54 dB/100ft
1450 MHz	8.3 dB/100ft
1800 MHz	9.3 dB/100ft
2250 MHz	10.6 dB/100ft
3000 MHz	11.9 dB/100ft

Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
28 Ohm/1000ft (92 Ohm/km)	9 Ohm/1000ft (30 Ohm/km)	16.2 pF/ft (53.1 pF/m)	75 Ohm	83%

Voltage

UL Voltage Rating
300 V RMS

Mechanical Characteristics

Temperature

UL Temperature	Operating
75°C	-20°C To +75°C

Bend Radius

Stationary Min.	Installation Min.
2.75 in (69.9 mm)	2.75 in (69.9 mm)

Max. Pull Tension:	126 lbs (57.2 kg)
Bulk Cable Weight:	28 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Outdoor, Sunlight Resistance
Flammability / Reaction to Fire:	UL1685 FT4 Loading, Limited Smoke, FT4, 1202, IEC 60332-1-2, IEC 60332-3-22
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMG-LS
CEC / C(UL) Compliance:	CMG-LS
IEEE Compliance:	Std. 45 clause 23
Marine Compliance:	ABS Type Approval Certificate 19-HS1852547-PDA
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.492 Revision Date: 04-29-2024
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
9116SB 0101000	Black	Reel	1,000 ft	612825224556	C

© 2024 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[9116SB 0101000](#)