



Product: [9161](#)

Electronic, 8 Pr #18 Str TC, PVC Ins, PVC Jkt, CMG

[Request Sample](#)

Product Description

Electronic, 8 Pair 18AWG (16x30) Tinned Copper, PVC Insulation, PVC Outer Jacket, CMG

Technical Specifications

Product Overview

|                        |   |
|------------------------|---|
| Suitable Applications: | low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; computer communication; panel wiring |
|------------------------|---|

Construction Details

Conductor

| Element | No. of Elements | Size   | Stranding | Material           |
|---------|-----------------|--------|-----------|--------------------|
| Pair(s) | 8               | 18 AWG | 16x30     | TC - Tinned Copper |

Insulation

| Element | Material                 | Nom. Thickness     | Nom. Insulation Diameter | Color Code  |
|---------|--------------------------|--------------------|--------------------------|---|
| Pair(s) | PVC - Polyvinyl Chloride | 0.013 in (0.33 mm) | 0.073 in (1.9 mm)        | Black & Red, Black & White, Black & Green, Black & Blue, Black & Yellow, Black & Brown, Black & Orange, Red & White |

Outer Jacket

| Material                 | Nom. Thickness     | Nom. Diameter      |
|--------------------------|--------------------|--------------------|
| PVC - Polyvinyl Chloride | 0.037 in (0.94 mm) | 0.485 in (12.3 mm) |

|                                   |                    |
|-----------------------------------|--------------------|
| Overall Cable Diameter (Nominal): | 0.485 in (12.3 mm) |
|-----------------------------------|--------------------|

Electrical Characteristics

Electricals

| Element | Nom. Conductor DCR | Nom. Capacitance Cond-to-Cond | Max. Current                   |
|---------|--------------------|-------------------------------|--------------------------------|
| Pair(s) | 7.2 Ohm/1000ft     | 25.5 pF/ft (83.7 pF/m)        | 3.5 Amps per Conductor at 20°C |

Voltage

| UL Voltage Rating                |
|----------------------------------|
| 300 V (CMG), 300 V (UL AWM 2464) |

Mechanical Characteristics

Temperature

| UL Temperature | Operating      |
|----------------|----------------|
| 80°C           | -20°C to +80°C |

Bend Radius

| Stationary Min. | Installation Min. |
|-----------------|-------------------|
| 4.9 in (120 mm) | 4.9 in (120 mm)   |

|                    |                      |
|--------------------|----------------------|
| Max. Pull Tension: | 332.8 lbs (151.0 kg) |
| Bulk Cable Weight: | 142 lbs/1000ft       |

Standards and Compliance

|                                  |  |
|----------------------------------|--|
| Environmental Suitability:       | Indoor   |
| Sustainability:                  | CA Prop 65   |
| Flammability / Reaction to Fire: | UL 1685 FT4 Loading, FT4   |
| CPR Compliance:                  | CPR Euroclass: Eca   |
| NEC / UL Compliance:             | Article 800, CMG   |
| AWM Compliance:                  | AWM 2464   |
| CEC / C(UL) Compliance:          | CMG  |
| European Directive Compliance:   | EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE) |
| UK Regulation Compliance:        | UKCA Mark  |
| APAC Compliance:                 | China RoHS II (GB/T 26572-2011)  |

History

|                      |  |
|----------------------|--|
| Update and Revision: | Revision Number: 0.537 Revision Date: 12-22-2023 |
|----------------------|--|

Part Numbers

Variants

| Item #       | Color  | Putup Type | Length   | UPC          | Footnote |
|--------------|--------|------------|----------|--------------|----------|
| 9161 060100  | Chrome | Reel       | 100 ft   | 612825224990 | C        |
| 9161 0601000 | Chrome | Reel       | 1,000 ft | 612825225003 | C        |

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[9161 060100](#) [9161 060500](#) [9161 0601000](#)