


Metal Film Resistors

Professional Type

Miniature Style [MF0 Series]



INTRODUCTION


The MF0 Series Metal Film Professional Resistors are manufactured using a vacuum sputtering system to deposit multiple layers of mixed metal alloys and passivative materials onto a carefully treated high grade ceramic substrate. After a helical groove has been cut in the resistive layer; tinned connecting leads of electrolytic copper are welded to the end-caps. The resistors are coated with layers of blue color lacquer.

FEATURES

Power Rating	0.4W, 0.6W
Resistance Tolerance	$\pm 0.5\%$, $\pm 1\%$, $\pm 2\%$, $\pm 5\%$,
T.C.R.	$\pm 50\text{ppm}/^{\circ}\text{C}$, $\pm 100\text{ppm}/^{\circ}\text{C}$

DERATING CURVE

For resistors operated in ambient temperatures above 70°C , power rating must be derated in accordance with the curve below.



DIMENSIONS



Unit: mm

STYLE	DIMENSION			
Miniature	L	øD	H	ød
MF0204	3.4 ± 0.3	1.9 ± 0.2	28 ± 2.0	0.45 ± 0.05
MF0207	6.3 ± 0.5	2.4 ± 0.2	28 ± 2.0	0.55 ± 0.05

Note:

ELECTRICAL CHARACTERISTICS

STYLE	MF0204	MF0207
Power Rating at 70°C	0.4W	0.6W
Maximum Working Voltage	250V	350V
Maximum Overload Voltage	500V	700V
Voltage Proof on Insulation	300V	500V
Resistance Range	1Ω - 4M7Ω & 0Ω for E24 & E96 series value	
Operating Temp. Range	-55°C to +155°C	
Temperature Coefficient	±50ppm/°C , ±100ppm/°C	

Note: Special value is available on request

ENVIRONMENTAL CHARACTERISTICS

PERFORMANCE TEST	TEST METHOD		APPRAISE
Short Time Overload	IEC 60115-1 4.13	2.5 times RCWV for 5 sec. (Not more than maximum Overload Voltage)	±0.25%+0.05Ω
Voltage Proof on Insulation	IEC 60115-1 4.7	In V-Block for 60 sec., test voltage as above table	No Breakdown
Temperature Coefficient	IEC 60115-1 4.8	Between -55°C to +155°C	By type
Insulation Resistance	IEC 60115-1 4.6	in V-block for 60 Sec.	>10,000MΩ
Solderability	IEC 60115-1 4.17	245±5°C for 3±0.5 Sec.	95% Min. coverage
Solvent Resistance of Marking	IEC 60115-1 4.30	IPA for 5±0.5 Min. with ultrasonic	No deterioration of coatings and markings
Robustness of Terminations	IEC 60115-1 4.16	Direct load for 10 Sec. in the direction of the terminal leads	≥2.5kg (24.5N)
Periodic-pulse Overload	IEC 60115-1 4.39	4 times RCWV 10,000 cycles (1 Sec. on, 25 Sec. off)	±1.0%+0.05Ω
Damp Heat Steady State	IEC 60115-1 4.24	40±2°C, 90-95% RH for 56 days, loaded with 0.1 times RCWV	±1.5%+0.05Ω
Endurance at 70°C	IEC 60115-1 4.25	70±2°C at RCWV (or Umax., Whichever less) for 1,000 Hr. (1.5Hr: on, 0.5Hr: Off)	±1.5%+0.05Ω
Temperature Cycling	IEC 60115-1 4.19	-55°C ⇄ Room Temp. ⇄ +155°C ⇄ Room Temp. (5 cycles)	±0.75%+0.05Ω
Resistance to Soldering Heat	IEC 60115-1 4.18	260±3°C for 10±1 Sec., immersed to a point 3±0.5mm from the body	±0.25%+0.05Ω

Note: RCWV(Rated Continuous Working Voltage) = $\sqrt{\text{Power Rating} \times \text{Resistance Value}}$ or Max. working voltage listed above, whichever less.

Revision: 2020

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Yageo:

[MF0207FTE52-4K75](#) [MF0207FTE52-560K](#) [MF0207FTE52-15R](#) [MF0207FTE52-2K1](#) [MF0204FTE52-16K9](#)
[MF0204FTE52-154R](#) [MF0204FTE52-430R](#) [MF0204FTE52-470R](#) [MF0204FTE52-200R](#) [MF0207FTE52-1M8](#)
[MF0207FTE52-4M7](#) [MF0204FTE52-15R](#) [MF0204FTE52-2K4](#) [MF0204FTE52-300R](#) [MF0204FTE52-330K](#)
[MF0204FTE52-2K61](#) [MF0204FTE52-270R](#) [MF0204FTE52-1K21](#) [MF0204FTE52-680R](#) [MF0204FTE52-100R](#)
[MF0204FTE52-1K6](#) [MF0204FTE52-7R5](#) [MF0204FTE52-178R](#) [MF0204FTE52-1K18](#) [MF0204FTE52-20K](#)
[MF0204FTE52-7K68](#) [MF0204FTE52-42R2](#) [MF0204FTE52-6K04](#) [MF0207FTE52-4M64](#) [MF0204FTE52-11K5](#)
[MF0204FTE52-392K](#) [MF0204FTE52-56R2](#) [MF0204FTE52-10K2](#) [MF0204FTE52-383K](#) [MF0204FTE52-226K](#)
[MF0204FTE52-215K](#) [MF0204FTE52-8K66](#) [MF0204FTE52-11K3](#) [MF0204FTE52-5R62](#) [MF0204FTE52-2K8](#)
[MF0204FTE52-294K](#) [MF0204FTE52-3K65](#) [MF0204FTE52-40K2](#) [MF0204FTE52-1K82](#) [MF0204FTE52-26K7](#)
[MF0204FTE52-604R](#) [MF0204FTE52-715R](#) [MF0204FTE52-1K07](#) [MF0204FTE52-1K3](#) [MF0204FTE52-365K](#)
[MF0204FTE52-680K](#) [MF0204FTE52-2K67](#) [MF0204FTE52-2K](#) [MF0204FTE52-3K32](#) [MF0204FTE52-249K](#)
[MF0204FTE52-38K3](#) [MF0204FTE52-1K47](#) [MF0207FTE52-1M02](#) [MF0204FTE52-1K96](#) [MF0204FTE52-4K53](#)
[MF0207FTE52-2M49](#) [MF0204FTE52-12K7](#) [MF0204FTE52-698K](#) [MF0204FTE52-8K06](#) [MF0204FTE52-100K](#)
[MF0204FTE52-3K48](#) [MF0204FTE52-4K75](#) [MF0204FTE52-51K1](#) [MF0204FTE52-562R](#) [MF0204FTE52-1M5](#)
[MF0204FTE52-14K7](#) [MF0204FTE52-909K](#) [MF0204FTE52-1M](#) [MF0204FTE52-15K](#) [MF0204FTE52-12R](#)
[MF0204FTE52-3K16](#) [MF0204FTE52-174K](#) [MF0204FTE52-34K8](#) [MF0204FTE52-316R](#) [MF0204FTE52-464R](#)
[MF0204FTE52-2K7](#) [MF0204FTE52-4K22](#) [MF0204FTE52-130R](#) [MF0204FTE52-10K7](#) [MF0204FTE52-1K58](#)
[MF0204FTE52-24K9](#) [MF0204FTE52-143K](#) [MF0204FTE52-10K5](#) [MF0204FTE52-274K](#) [MF0204FTE52-332K](#)
[MF0204FTE52-82K5](#) [MF0204FTE52-19K6](#) [MF0204FTE52-28R7](#) [MF0204FTE52-240R](#) [MF0204FTE52-51R](#)
[MF0204FTE52-787R](#) [MF0204FTE52-220K](#) [MF0204FTE52-121R](#) [MF0204FTE52-4K42](#) [MF0204FTE52-12K1](#)