




No. x QTY.	REVISION DESCRIPTION	APP.	CHK.	DSGN.	Mo - D - Yr	Decision Change #
△ x 1	Design change.	N. K.		I. I.	3-19-'98	DC 98-0757
△ x						
△ x						
△ x						
△ x						

This is the English version drawing, please note all Japanese text has been removed. Please consult factory for latest revision.





**CONTACT & MOUNTING SCREW HOLE PATTERN**  
(Pattern shown looking down through top of socket)




**Performance**

- Insulation Resistance  
1,000Mohm min. at DC100V
- Dielectric Withstanding Voltage  
For 1 minute at AC100V
- Contact Resistance  
30mohm max. at 10mA and 20mV max. Initial Number
- Operation Temperature  
40deg. C +150deg. C
- Contact Force  
20g - 80g Per Pin
- Operation Force  
1.2Kg/Max.
- Life Span  
10,000 Times (Mechanical)



Full Stroke Condition Drawing(S-FREE)  
This Device Can Be Pressed On The Hatched (XXXX) Areas Shown In The Drawing Above



ITEM	DESCRIPTION	QTY.	MATERIAL	CONTENT	PART IDENT
8	Coil Spring K1012	4	SUS DIA. 0.20	KS SANGYO No. 1012	Commercial
7	-C	16			
6	Contact 2088 -B	16	BeCu t0.20	Ni-Au PL (CLASS BF)	AB-05839
5	-A	16			
4	IC234-0484-034 #LV	1	PES (GF)	BLACK	AB-06993
3	IC234-0484-039 #LB	1	PC1 (GF)	BLACK	AB-08728
2	IC234-0484-034* #IN-B	1	PES (GF)	BLACK	AB-06991
1	IC234-0484-034 #IN-A	1	PES (GF)	BLACK	AB-06990

Ordering Code

Type Name	Positioning Pin
IC234-0484-039N	Without
IC234-0484-039P	With

DU-2207		YAMAICHI ELECTRONICS USA, INC.	
TOLERANCES: ±0.3		(CLASS) QFP-P0.5-48P	
Unless otherwise specified		(TITLE) IC234-0484-039-*	
SCALE 2/1	APP. APP. CHK. DRW. DSGN.	(DRW. NO.)	Sheet No. REV.
DIMENSION	3-18-'02 3-15-'02 3-15-'02 3-14-'02	YEU-A0222	B
3RD. ANGLE PROJECTION	H. Watanabe / I. Muro / A. Querubin / A. Querubin		

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Yamaichi Electronics:](#)

[IC234-0484-039N](#)