

MXC-6300/6310/6320 Series

3rd Generation Intel® Core™ i7/i5/i3/Celeron® PGA Processor-based Expandable Fanless Embedded Computer

Features

- Supports 3rd generation Intel® Core™ i7/i5/i3/Celeron® processor + QM77 chipset
- 2 x DDR3 SO-DIMM sockets, supporting up to 16 GB memory
- 1 PCI + 2 PCIe x8 slots or 1 PCI + 1 PCIe x16 for MXC-6300 series; 1 PCI + 1 PCIe x16 for MXC-6310 series, 3 PCI + 1 PCIe x16 for MXC-6320 series
- 3 independent displays: 2 DisplayPort + 1 DVI-I
- 6 external USB ports (4 USB 3.0 + 2 USB 2.0) + 1 internal USB 2.0
- 2 Intel® GbE ports with teaming function, Intel® iAMT 8.0
- 2 CFast sockets, internal SATA III for 2 x 2.5" HDD/SSD installation, SATA 6Gb/s and RAID 0,1 support
- Rugged, up to -20°C to 55/60°C fanless operation (w/ industrial SSD/CFast)



Introduction

The Matrix MXC-6300/6310/6320 series is a high-performance fanless embedded computer integrating a 3rd generation Intel® Core™ i7/ i5/i3 processor and QM77 chipset to provide powerful computing and superior graphic performance. Graphic-intensive and computing-oriented applications including image and vision measurement, machine automation, maritime automation, surveillance and high-resolution medical imaging all benefit.

Increased PCI & PCI express (Gen2) expansion slots allow installation of a variety of PCI, PCIe x8 or PCIe x16 add-on cards, meeting the needs of application platform development environments. In addition, the MXC-6300/6310/6320 series offers 2 DisplayPort and one DVI-I port for three independent display support connections, four USB 3.0 and two USB 2.0 ports, and 2 GbE LAN ports with teaming function. The two 2.5" onboard SATA III ports with high speed SATA 6 Gb/s and RAID 0, 1 ensure all data in the RAID array is fully backed up. Built-in 16 CH isolated DIO provides overall industrial control.

Delivering high quality, durable and compact construction, the MXC-6300/6310/6320 series leverages a reliable fanless and cable-free configuration, optimal thermal dissipation, and easy installation for flexible and user-friendly system development and application implementation in harsh environments.

Applications

- **Factory Automation / Machine Vision**
- **Intelligent Transportation Systems / Surveillance**
- **Maritime Automation**
- **High Resolution Medical Imaging**

Software Support

- **Win10/ Win7/Embedded standard 7/WES 2009**
- **Linux (by request)**


Ordering Information

- **MXC-6301/ 6302/ 6303/ 6305**
Intel® Core™ i7/i5/i3/Celeron®, w/ 1 PCI + 2 PCIe x8 or 1 PCIe x16 slots
- **MXC-6311/ 6312/ 6313/ 6315**
Intel® Core™ i7/i5/i3/Celeron®, w/ 1 PCI + 1 PCIe x16 slots
- **MXC-6321/ 6322/ 6323/ 6325**
Intel® Core™ i7/i5/i3/Celeron®, w/ 3 PCI + 1 PCIe x16 slots

Optional Accessories

- **Optional Fan Kit**
Fan kit for MXC-6300/ 6320
Fan kit for MXC-6310
- **8/ 16 GB DDR3 Upgrade**
Upgrade to 8/ 16 GB DDR3 memory
- **HDD/ SSD/ CFast storage**
Factory-installed and test
- **160 W AC-DC Adapter**
160 W industrial grade AC-DC adapter
- **Wireless Kit Option**
WiFi/ BT/ 3G/ 4G LTE/ LoRa wireless kit (w/ Antenna)
- **Extended Temperature Option**
Optional screening to extended temperature of i7 CPU to -20 to 55°C; i5/i3/Celeron® CPU to -20 to 60°C

Product Illustration




Specifications

Model Name	MXC-6301D/6311D/6321D	MXC-6302D/6312D/6322D	MXC-6303D/6313D/6323D	MXC-6305D/6315D/6325D
System Core				
Processor	Intel® Core™ i7-3610QE, 2.3/3.3 GHz, 6M cache	Intel® Core™ i5-3610ME, 2.7/3.3 GHz, 3 M cache	Intel® Core™ i3-3120ME, 2.4 GHz, 3 M cache	Intel® Celeron 1020E, 2.2 GHz, 2 M cache
Chipset	Intel® Mobile Platform Controller Hub (QM77)			
Video	3 independent display: 2 DisplayPort + 1 DVI-I 1st DP: up to 2560x1600 / 2nd DP: up to 1920x1600 / DVI-I port: up to 1920x1200			
Memory	4 GB DDR3 1600 MHz SODIMM module (Max. capacity 16 GB with 2 SODIMM socket option)			
I/O Interface				
Expansion Slots	1 PCI + 2 PCIe x8 slots or 1 PCI + 1 PCIe x16 (MXC-6300 series), 1 PCI + 1 PCIe x16 (MXC-6310 series), 3 PCI + 1 PCIe x16 (MXC-6320 series)			
Ethernet	2 Intel® GbE ports (Intel® 82579 / I210) Support Teaming function, Intel iAMT 8.0, Wake On LAN			
Serial Ports	2 software-programmable RS-232/422/485 (COM 1&2) with autoflow control, 2 RS-232 (COM 3&4)			
USB	6 external USB ports (4 USB 3.0 + 2 USB 2.0) + 1 internal USB 2.0			
DIO	16-CH DI and 16-CH DO with 1.5KV isolation			
Audio	1 MIC-in and 1 Line-out			
KB/MS	1 PS/2 keyboard and 1 PS/2 mouse			
WDT	Supports a watchdog timer			
Power Supply				
DC Input	Built-in 9-32 VDC wide-range DC input Pluggable connectors with latch (GND, V-, V+), 2-pin remote power on/off switch			
AC Input	Optional 160 W external AC-DC adapter for AC input			
Storage Device				
SATA HDD	2 onboard SATA-III for 2.5" HDD/SSD installation, SATA RAID 0,1 & SATA 6 Gb/s support			
CompactFlash	2 CFast socket (1 external + 1 internal)			
Mechanical				
Optional Fan Module	Optional fan module for dissipating heat generated by PCI/PCIe card, Smart fan control			
Dimensions	MXC-6300/MXC-6320 series: 172.5 (W) x 225 (D) x 213 (H) mm (6.9" x 9" x 8.52"); MXC-6310 series: 154 (W) x 225 (D) x 213 (H) mm (6.16" x 9" x 8.52")			
Weight	MXC-6300/6320 series: 4.3 kg (9.5 lbs); MXC-6310 series: 3.8kg (8.39 lbs)			
Mounting	Wall-mount kit			
Environmental				
Operating Temperature	Standard: 0°C to 50°C (32°F to 122°F) Extended temperature option*: -20°C to 55°C (-4°F to 131°F) (w/industrial SSD or CFast) for MXC-6301D/6311D -20°C to 60°C (-4°F to 140°F) (w/industrial SSD or CFast) for MXC-6302D/6303D/6312D/6313D			
Storage Temperature	-40°C to 85°C (-40°F to 185°F) (excl. HDD/SDD/CFast)			
Humidity	~95% @ 40°C (104°F) (non-condensing)			
Vibration	Operating, 5 Grms, 5-500 Hz, 3 axes (w/ CFast or SSD) Operating, 0.5 Grms, 5-500 Hz, 3 axes (w/ HDD)			
ESD	Contact +/-4 KV and Air +/-8 KV			
Shock	Operating, 50 G, half sine 11 ms duration (w/ CFast or SSD)			
EMC	CE and FCC Class A			
Safety	UL/cUL, CB, KCC			

Versatile Expansion


The MXC-6300 series offer various of expansion slot options for flexible function enhancement and easier system integration.

MXC-6300 (3 Slots)




Recommended expansion slot configuration options for MXC-6300:
1 PCI + 2 PCIe x8 slots or 1 PCI + 1 PCIe x16

MXC-6310 (2 Slots)



MXC-6320 (4 Slots)



Easy-to-install Optional Fan Module



Withdraw the thumbscrew and remove the top cover



Seat the fan module cover and slide into place, the fan connects automatically

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ADLINK Technology:](#)

[MXC-6300 Power Harness,4P](#)