


NuPRO-E330

PICMG® 1.3 Full-Size LGA1156 Intel® Core™ i7/i5/i3/Pentium® Processor-based SHB



Features

- LGA1156 Intel® Core™ i7/i5/i3, Pentium® Dual Core Processor
- Intel® Q57 Express Chipset supports PCI Express 2.0
- Intel® Matrix Storage Technology, supports RAID 0/1/5/10
- Intel® Active Management Technology 6.0
- PCIe Mini Card slot
- 6x COM ports (including 1x RS-232/422/485/485+)

Specifications

Processor & System

CPU	Intel® Core™ i7-860 Processor, 2.80 GHz, 8M Cache, 45nm, 95W TDP, LGA1156, No Graphics (4 cores/8 threads) Intel® Core™ i5-750 Processor, 2.66 GHz, 8M Cache, 45nm, 95W TDP, LGA1156, No Graphics (4 cores/8 threads) Intel® Core™ i5-660 Processor, 3.33 GHz, 4M Cache, 32nm, 73W TDP, LGA1156 (2 cores/4 threads) Intel® Core™ i3-540 Processor, 3.06 GHz, 4M Cache, 32nm, 73W TDP, LGA1156 (2 cores/4 threads) Intel® Pentium® Dual Core G6950 Processor, 2.80 GHz, 3M Cache, 32nm, 73W TDP, LGA1156 (2 cores/4 threads)
Chipset	Intel® Q57 Express Chipset
Memory	2x 240-pin DIMM sockets Dual-channel DDR3 1066/1333 MHz, up to 8 GB
TPM	Infineon® SLB9635 TT1.2
BIOS	AMIBIOS® 32 Mb SPI flash memory
Watchdog Timer	1-255 sec. or min. software programmable, can generate system reset
Hardware Monitor	CPU/System temperature, fan speed and onboard DC voltages
Operating Systems	Windows® XP, Vista 32/64-bit, 7 32/64-bit, Server 2008 Fedora™ 10 Red Hat Enterprise Linux 5

I/O Interfaces

Serial ATA	6x SATA 3 Gb/s ports (4x onboard headers, 2x backplane) Intel® Matrix Storage Technology, supports RAID 0/1/5/10
Expansion Slots	1x PCIe Mini Card slot
USB	9x USB 2.0 ports (1x faceplate, 4x onboard pin headers and 4x via backplane)
KB/MS	1x Mini-DIN for PS/2 keyboard/mouse
Floppy	1x Floppy
Parallel Port	1x LPT
Serial Port	5x RS-232, 1x RS-232/422/485/485+

Audio

Audio Codec Interface	Realtek® ALC262 support by DB-Audio2 daughter board Pin header for High Definition Audio interface
------------------------------	---

Display

Integrated Graphics	Integrated in Core i5-660/i3-540, Pentium G6950 processor
External Graphics	PCI Express x16 or onboard PCI Express Mini Card slot for optional mPCIe-8770

Ethernet

Controller	Intel® 82578DM Gigabit Ethernet PHY Intel® 82574L Gigabit Ethernet Controller
Interface	PCIe x1 bus
iAMT	Supports Intel® AMT 6.0 on 82578DM
Wake On LAN	Support on LAN1

Mechanical and Environmental

Form Factor	Full-Size PICMG® 1.3 System Host Board
Dimensions	338 mm x 126 mm (L x W)
Operating Temp.	0°C to 60°C
Storage Temp.	-20°C to 80°C
Certifications	CE, FCC Class A
Relative Humidity	10% to 90%, non-condensing

Ordering Information

Model Number	Description/Configuration
NuPRO-E330	PICMG® 1.3 Full-Size LGA1156 Intel® Core™ i7/i5/i3/Pentium® Processor-based SHB

Note: CPU, Memory module and Cooler kit are not included.

Optional Accessories

Model Number	Description/Configuration
LGA1156 1U CPU Cooler	LGA1156 1U Thermal Module
LGA1156 2U CPU Cooler	LGA1156 2U Thermal Module
LGA1156 3U CPU Cooler	LGA1156 3U Thermal Module
DB-Audio2	High Definition Audio daughter board with Mic-in/Line-in/Line-out
mPCIe-8770	PCIe 2D VGA Display Card

Packing List

NuPRO-E330	1x Y-cable for PS/2 keyboard/mouse
1x Floppy cable	1x USB 2.0 cable with bracket
1x COM port cable with bracket	1x COM+parallel port cables with bracket
2x SATA data cables	1x dual-plug SATA power cable
Driver DVD	User's manual
2x dual-port COM cables with bracket	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ADLINK Technology:](#)

[NuPRO-E330](#)