

# PCI-9812/9812A/9810

## 4-CH 10/12-Bit 20 MS/s Simultaneous-Sampling Analog Input Cards



### Introduction

ADLINK's PCI-9812, PCI-9810 and PCI-9812A are 4-CH, 10 or 12-bit, 20 MS/s simultaneous-sampling analog input cards. The high-speed analog input channels are single-ended, with hardware programmable input ranges of  $\pm 1\text{ V}$ ,  $\pm 5\text{ V}$  and input impedances of  $50\ \Omega$ ,  $1.25\text{ k}\Omega$  and  $15\text{ M}\Omega$ . The onboard 32 k-sample A/D FIFO can buffer so data throughput is less than 100 Mbytes/s, the FIFO performs as the temporary A/D sample buffer, and as a rule of thumb, no data loss will occur. When four channels operate at 20 MS/s simultaneously, each sample generates two bytes, resulting in 160 Mbytes/s (4 channels \* 20 M \* 2 bytes) throughput, which exceeds the peak 132 Mbyte/s bandwidth of PCI bus. To avoid data loss, the 32 k-sample FIFO is the limitation of sample count. For applications requiring a larger number of samples at full sampling rate, the PCI-9812A features 128 k sample A/D FIFO for storage.

In addition to the onboard 40 MHz time base, users are able to supply the external time base in either sine wave or digital forms. The PCI-9810 and PCI-9812 also feature external digital trigger and programmable analog trigger, thus the conversion start point of multiple cards can be synchronized to external events. The trigger modes include software-trigger, pre-trigger, post-trigger, middle-trigger and delay trigger, further expands the capabilities of these high-speed devices. ADLINK's PCI-9812, PCI-9810 and 9812A deliver cost-effective and reliable data acquisition capabilities and are ideal for vibration testing, image digitizing, ultrasonic measurement, biomedical research, ATE and other high-end industrial, scientific, and military applications.

### Features

- Supports a 32-bit 3.3 V or 5 V PCI bus
- 12-bit A/D resolution (PCI-9812 and PCI-9812A)
- 10-bit A/D resolution (PCI-9810)
- Up to 20 MS/s simultaneous-sampling rate
- >17 MHz -3 dB bandwidth
- 4-CH single-ended inputs
- Bipolar analog input ranges
- User-selectable input impedance of  $50\ \Omega$  or high-input impedance
- Onboard 32 k-sample A/D FIFO (PCI-9810 and PCI-9812)
- Onboard 128 k-sample A/D FIFO (PCI-9812A)
- Analog and digital triggering
- External clock input for customized conversion rate
- Bus-mastering DMA for analog inputs
- 3-CH TTL digital inputs
- Compact, half-size PCB

#### ■ Supported Operating System

- Windows 7/8 x64/x86, Linux

#### ■ Driver and SDK

- LabVIEW, MATLAB, C/C++, Visual Basic, Visual Studio.NET

#### ■ Software Utility

- AD-Logger

### Specifications

#### Analog Input

- Number of channels: 4 single-ended Resolution
  - 12-bit (PCI-9812 and PCI-9812A)
  - 10-bit (PCI-9810)
- Maximum sampling rate: 20 MS/s
- Input signal ranges, impedance and overvoltage protection

| Input Range/Model | Input Impedance       | Overvoltage protection |
|-------------------|-----------------------|------------------------|
| $\pm 1\text{ V}$  | $50\ \Omega$          | $\pm 2\text{ V}$       |
|                   | $15\text{ M}\Omega$   |                        |
| $\pm 5\text{ V}$  | $50\ \Omega$          | $\pm 10\text{ V}$      |
|                   | $1.25\text{ k}\Omega$ |                        |

- Accuracy:  $\pm 1.5\%$  typical
- DNL:  $\pm 0.4\text{ LSB}$  typical,  $\pm 1.0\text{ LSB}$  maximum
- INL:  $\pm 1.9\text{ LSB}$  typical
- Input coupling: DC
- Trigger sources: software, analog and digital trigger (5 V/TTL compatible)
- Trigger modes: software-trigger, pre-trigger, post-trigger, middle-trigger & delay trigger
- FIFO buffer size
  - 32 k samples (PCI-9810 & PCI-9812)
  - 128 k samples (PCI-9812A)
- Data transfers: bus-mastering DMA

#### Triggering

- Analog Trigger
  - Modes: pre-trigger, post-trigger, middle-trigger, delay-trigger
  - Source: CH0, CH1, CH2 and CH3
  - Slope: rising/falling
  - Coupling: DC
  - Trigger sensitivity: 256 steps in full-scale voltage range
- Digital Triggering
  - Modes: pre-trigger, post-trigger, middle-trigger, delay-trigger
  - Source: external digital trigger
  - Slope: rising edge
  - Compatibility: 5 V/TTL
  - Minimum pulse width: 25 ns

#### External Sine Wave Clock

- Input coupling: AC
- Input impedance:  $50\ \Omega$
- Input frequency: 300 kHz to 40 MHz
- Input range: 1.0 to 2.0 Vpp
- Overvoltage protection: 2.5 Vpp

#### External Digital Clock

- Input coupling: DC
- Input impedance:  $50\ \Omega$
- Compatibility: 5 V/TTL
- Input frequency: 20 kHz to 40 MHz
- Overvoltage protection: diode clamping, -0.3 V to +5.3 V

#### Digital Input

- Number of channels: 3
- Compatibility: 5 V/TTL with  $10\text{ k}\Omega$  pull down resistors
- Overvoltage protection: Diode clamping, -0.3 V to +5.3 V
- Data transfers: bus-mastering DMA with A/D samples

#### General Specifications

- I/O connector
  - BNC x 5
  - 10-pin ribbon male
- Operating temperature:  $0^\circ\text{C}$  to  $40^\circ\text{C}$  ( $32^\circ\text{F}$  to  $104^\circ\text{F}$ )
- Storage temperature:  $-20^\circ\text{C}$  to  $70^\circ\text{C}$  ( $-4^\circ\text{F}$  to  $158^\circ\text{F}$ )
- Relative humidity: 10% to 90%, non-condensing
- Power requirements

| Device    | +5 V          |
|-----------|---------------|
| PCI-9812  | 1.4 A typical |
| PCI-9812A |               |
| PCI-9810  | 1 A typical   |

- Dimensions (not including connectors)  
173 mm x 108 mm (6.74" x 4.21")

### Ordering Information

#### ■ PCI-9810

4-CH 10-Bit 20 MS/s Simultaneous-Sampling Analog Input Card with 32 k-Sample A/D FIFO

#### ■ PCI-9812

4-CH 12-Bit 20 MS/s Simultaneous-Sampling Analog Input Card with 32 k-Sample A/D FIFO

#### ■ PCI-9812A

4-CH 12-Bit 20 MS/s Simultaneous-Sampling Analog Input Card with 128 k-Sample A/D FIFO

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ADLINK Technology:](#)

[PCI-9810](#) [PCI-9812A](#) [PCI-9812](#)