

EPS-1132

32-CH Sinking Type Digital Input Module



Features

- 32-CH sinking type digital input
- Quick removable European type connector
- Slave module healthy monitoring
- Wide operation temperature range: -20°C - 60°C
- Compact size: 100 (L) x 100 (H) mm
- IEC-61131 compliant

Ordering Information

- **EPS-1132**
32-CH Sinking Type Digital Input Module

Specifications

■ Power Consumption	2.76W
■ Hot Swap	Yes
■ Operating Temp.	-20-60 °C
■ Digital Input /Output Channel	32
■ Input /Output Type	Sinking
■ Input Current	IEC-61131-2 Type 1/3
■ Input Current Limit	2.3mA
■ Response Time	< 1ms
■ Self-Diagnostic	Power Communication / WDT
■ Connector Type	Phoenix Contact DFMC

EPS-2032

32-CH Sourcing Type Digital Output Module



Features

- 32-CH sourcing type digital output
- Quick removable European type connector
- Slave module healthy monitoring
- Wide operation temperature range: -20°C - 60°C
- Compact size: 100 (L) x 100 (H) mm
- IEC-61131 compliant

Ordering Information

- **EPS-2032**
32-CH Sourcing Type Digital Output Module

Specifications

■ Power Consumption	2.76W
■ Hot Swap	Yes
■ Operating Temp.	-20-60 °C
■ Digital Output Channel	32
■ Output Type	Sourcing
■ Output Current (Single Node)	300mA
■ Output Current (Full node)	1.6A for 8-CH
■ Response Time	4KHz
■ Self-Diagnostic	Power / Communication / WDT
■ Connector Type	Phoenix Contact DFMC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ADLINK Technology:](#)

[EPS-2032](#) [EPS-1132](#)