






| | | | | | | | |
|---|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---|---|---|---|---|---|
| | 1 | 2 | 3 | 4 | 5 | 6 | 7 |
| | <div>DRF03</div> <div>AKA</div> <div>Description1P 250V 3A DINRAIL FILTER</div> <div>Devicerfi filter</div> <div>Current3A 40°C</div> <div>Earthing screw 2.5mm² 0.5Nm strip 8mm</div> <div>Enclosureplastic polyamide UL94-V0</div> <div>Loss0.64W/ph</div> <div>Leakage0.75mA operating</div> <div>Mass0.098kg</div> <div>MountingDin Rail</div> <div>PCBfr4 avlv2 VW-1 600V 105°C</div> <div>Pottingair</div> <div>Power0.7kW</div> <div>ProtectionIP20</div> <div>Resistance71mR/ph</div> <div>Residual1v 5s</div> <div>SCCT5kA</div> <div>Supply230/240V 50/60Hz</div> <div>Terminal screw 2.5mm² 0.5Nm strip 8mm</div> <div>VaristorL-N 275V 6.5kA (500Vdc)</div> <div>Withstand2100Vdc 60s</div> <div>Altitude1000m (3000m w/derating)</div> <div>Bonding25A 50/60Hz</div> <div>Classclass I</div> <div>Environment-25/+85/21</div> <div>FlammabilityULV2 min</div> <div>Humidity93% RH non-condensing</div> <div>Insulation500Vdc ≥3.5MR</div> <div>Materialgroup IIb</div> <div>MTBF22yrs (MIL-HDBK-217F)</div> <div>Overload135% 2hrs 150% 60s</div> <div>Overvoltagecategory II</div> <div>PackagingASTM D7386</div> <div>Pollutiondegree II</div> <div>Shock15g 11mS</div> <div>Spacing≥50mm gap</div> <div>Vibration5-55Hz 350um 55-500Hz 2G</div> <div>EUCE EN60939</div> <div>USn/a</div> <div>CANn/a</div> | | | | | | |
| A | | | | | | | |
| | | | | | | | |
| B | | | | | | | |
| | | | | | | | |
| C | | | | | | | |
| | | | | | | | |
| D | | | | | | | |
| | | | | | | | |
| E | | | | | | | |




ROXBURGH ELECTRONICS LTD
FILTER INSERTION LOSS CHARACTERISTICS
CISPR 17 - 50 OHM METHOD

DRF03



COMMON MODE



DIFFERENTIAL MODE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Deltron:](#)

[DRF03](#)