



Product: [9563](#)

High Perform Instr, 11 Pr #18 Str TC, PVC Ins E2, OS, PVC Jkt, PLTC-ER

Request Sample

Product Description

High Performance Instrumentation, 11 Pair 18AWG (19x30) Tinned Copper, PVC Insulation E2 Color Code, Overall Beldfoil® Shield, PVC Outer Jacket, PLTC-ER

Technical Specifications

Physical Characteristics (Overall)

Conductor			
AWG	Stranding	Material	No. of Pairs
18	19x30	TC - Tinned Copper	11
Conductor Count:			22
Total Number of Pairs:			11

Insulation	
Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.078 mm

Color Chart	
Number	Color
1	Black & Red and Numbered 1
2	Black & Red and Numbered 2
3	Black & Red and Numbered 3
4	Black & Red and Numbered 4
5	Black & Red and Numbered 5
6	Black & Red and Numbered 6
7	Black & Red and Numbered 7
8	Black & Red and Numbered 8
9	Black & Red and Numbered 9
10	Black & Red and Numbered 10
11	Black & Red and Numbered 11

Outer Shield Material						
Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	18	7x26

Outer Jacket Material			
Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	0.665 in	0.063 in	Yes

Construction and Dimensions

Cabling	
Lay Direction	
Left-hand Lay	

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
5.96 Ohm/1000ft	9 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Shield
35 pF/ft	54 pF/ft

Inductance

Nominal Inductance
0.17 µH/ft

Current

Max. Recommended Current [A]
4.5 Amps per Conductor at 25°C

Voltage

UL Voltage Rating
300 V RMS
150 V RMS (ITC)

Temperature Range

UL Temp Rating:	105°C
Operating Temp Range:	-30°C To +105°C

Mechanical Characteristics

Bulk Cable Weight:	230 lbs/1000ft
Max. Pull Tension:	478 lbs
Min Bend Radius/Minor Axis:	6.65 in

Standards

NEC/(UL) Compliance:	CMG, ITC-ER, PLTC-ER
CEC/C(UL) Compliance:	CMG
UL AWM Style Compliance:	2464

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Burial:	Yes
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LS0H, Toxicity Testing

C(UL) Flammability:	FT4
UL Flammability:	UL1685 UL Loading
ICEA Flammability:	T-29-520
IEEE Flammability:	1202
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	UPC
9563 0601000	Chrome	612825255987
9563 060500	Chrome	612825255994

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

History

Update and Revision:	Revision Number: 0.327 Revision Date: 09-30-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[9563 0601000](#) [9563 060500](#)