

Single Stage HSI Integrated Furnace Control Kit

Universal 50M56U-843

Replaces:
Virtually All White-Rodgers and Competitive Single Stage Carbide and Nitride HSI Systems – Including Carrier HK42FZ004, HK42FZ007, HK42FZ008, HK42FZ009, HK42FZ011 and HK42FZ016.

Specifications

Electrical Rating [@ 77°F (25°C)]

Input Voltage: 25 VAC 50/60 Hz
Max. Input Current @ 25 VAC: 0.45 amp
Relay Load Ratings
Valve Relay: 1.5 amp @ 25 VAC 50/60 Hz 0.6 pf
Ignitor Relay: 6.0 amp @ 120 VAC 50/60 Hz (resistive)
Inducer Relay: 2.2 FLA–3.5 LRA @ 120 VAC
Circulator Relay: 14.5 FLA–25.0 LRA @ 120 VAC

Flame Current Requirements

Minimum current to insure flame detection: 1 µA DC*
Maximum current for non-detection: 0.1 µA DC*
Maximum allowable leakage resistance: 100 M ohms
*Measured with a DC microammeter in the flame probe lead

Operating Temperature Range

-40° to 176°F (-40° to 80°C)

Mounting

Surface mount multipoise

Timing Specifications (@ 60 Hz)

	Maximum
Flame Establishing Time:	0.8 sec
Flame Failure Response Time:	2.0 sec

Gases Approved: Natural, Manufactured, Mixed, Liquified Petroleum, and LP Gas-Air Mixtures are all approved for use.

Relay Load Rating

Main Valve Relay: 1.5 amp @ 25 VAC 60 Hz

Hot Surface Ignition


120 VAC

Dimensions

5.25" W x 7" H x 1.25" D

For Additional Information


Visit www.white-rodders.com



Universal Single Stage HSI Integrated Furnace Control Kit

50M56U-843

Replaces:
Virtually All White-Rodgers and Competitive Single Stage Carbide and Nitride HSI Systems – Including Carrier Systems.*



Universal Integrated Furnace Module – 50M56-843

Simplify Your Inventory

Go with the leader, and stock one kit that replaces them all!

*Replaces:

- More OEM Boards Than Competitive Models Because 50M56U-843 Can Be Used on Both 80V and 120V Ignitor Applications
- Carrier HK42FZ004, HK42FZ007, HK42FZ008, HK42FZ009, HK42FZ011 and HK42FZ016

Fast-Install Kit – includes everything you need for quick and accurate replacement:

- Ignition Control Module – 50M56-843
- 12 Quick-Select/Quick-Connect Wiring Harnesses
- HotRod™ Universal Ignitor Kit – 21D64-2
- Installation Instructions and OEM Cross-Reference

Features:

- 3 Fan Speeds – Cool, Low Heat & High Heat Speeds (Terminal Connections)
- Color-Coded (Labeled) Thermostat Connection – For Quick Helpful Selection
- System Diagnostics, with Fault Recall (Stored)
- Cover Label – Displays Diagnostic Table
- Red LED Light – Used for Diagnostic Flash Codes
- Low Voltage – Fuse Protection – 3A Replaceable Automotive Type
- Humidifier & Electronic Air Cleaner Connections (Optional)

White-Rodgers

Saint Louis, Missouri
314-553-3600
www.white-rodders.com
www.emersonclimate.com

Markham, Ontario
905-948-3411

The Emerson logo is a trademark and a service mark of Emerson Electric Co.

EMERSON
Climate Technologies

WR-6571-5

White-Rodgers

EMERSON
Climate Technologies

50M56U-843 Kit Cross-Reference and Harness Application Data

Replaces: Virtually All White-Rodgers and Competitive Single Stage Carbide and Nitride HSI Systems – Including Carrier HK42FZ004, HK42FZ007, HK42FZ008, HK42FZ009, HK42FZ011 and HK42FZ016.

Module Model #	Harness	Ignitor	Furnace OEM
031-00662	F	Use existing or 21D64-2	Coleman/Evcon/Luxaire/York
031-00662-000	F		
031-00662-700	F		
031-01250-000	F		
031-01250-700	F		
031-01266-000	F		
031-01266-700	F		
031-01284-000	F		
031-09166-000	F		
031-09167-000	F		
100925-02	F	21D64-2	Lennox
100925-03	F		
1010806	E & F	Use existing or 21D64-2	Heil Quaker/ICP/ Thermo Products/Whirlpool
1012-83-9336AHSC1	A & C	21D64-2	United Technologies
1012-83-9337A	A & C		
1012-925A	B & D		
1012-925B	B & D		
1012-925C	B & D		
1012933D	A & C		
1012-933D	A & C		
10207701	F		
102077-02	E & F		
102077-03	E & F		
10207704	E & F	Use existing or 21D64-2	Amana/Goodman
102077-04	E & F		
10207706	E & F		
102077-09	E & F		
10207710	E & F		
10207714	E & F		
10207717	F		
10207718	E & F		
10207719	E & F		
10207720	F		
10207720S	F	21D64-2	Lennox
10M93	F		
10M9301	F		
12L6901	F		
1214201	F		
1380686	F		International Comfort Products
1380698	F		
1380699	F		
265901	F		
265902	F		Coleman/Evcon/Luxaire/York
3101250000	F		
031-01973-000	F		
32M8801	F	21D64-2	Lennox
331-01933-000	F	Use existing or 21D64-2	Coleman/Evcon/Luxaire/York
331-01972-000	F		
331-09167-000	F		
350486	F		
350836	F	21D64-2	Thermo Products
41F-5	A & C		Texas Instruments
50A50-110	F	Use existing or 21D64-2	Heil Quaker/ICP
50A50-111	F		Synder General
50A50-112	F		Heil Quaker/ICP
50A50-113	F		American Standard/Trane
50A50-130	F		Heil Quaker/ICP
50A50-131	F		
50A50-142	F		
50A50-143	F		
50A50-205	F		American Standard/Trane Amana/Goodman
50A50-206	F		
50A50-207	E & F		
50A50-208	F	Coleman/Evcon/Luxaire/York	Coleman/Evcon/Luxaire/York
50A50-209	F		

Module Model #	Harness	Ignitor	Furnace OEM
50A50-210	F	Use existing or 21D64-2	Armstrong/Heil Quaker
50A50-215	F		Clare Brothers-Canada
50A50-216	F		DMO Industries
50A50-229	F		Coleman/Evcon/Luxaire/York
50A50-230	F		
50A50-240	F		
50A50-241	F		
50A50-245	F		
50A50-285	E & F		White-Rodgers Standard
50A50-286	F		
50A50-288	E & F		
50A50-295	F		Amana/Goodman
50A50-296	F		American Standard/Trane
50A50-298	E & F		
50A50-405	F		Amana/Goodman
50A50-406	F		American Standard/Trane
50A50-407	F		
50A50-408	F		White-Rodgers Standard
50A50-438	F		American Standard/Trane
50A50-471	F		
50A50-472	F		
50A50-473	F		
50A50-474	F		
50A50-475	F		
50A50-571	F		Canadian Market
50A55-143	F		American Standard/Trane
			Thermo Products/Heil Quaker/ICP/Whirlpool
50A55-241	F		Coleman/Evcon/Luxaire/York
50A55-245	F		Canadian Market
50A55-250	F		Fedders
50A55-285	E & F		White-Rodgers Standard
50A55-286	F		
50A55-288	E & F		
50A55-289	E & F		Amana/Goodman
50A55-438	F		
50A55-474	F		Heil Quaker/ICP/Whirlpool/White-Rodgers Standard
50A55-476	F		American Standard/Trane
50A55-480	F		
50A55-486	F		
50A55-571	F		
50A55-843	F	Lennox/White-Rodgers Standard	
50A56-242	F	Coleman/Evcon/Luxaire/York	
50A56-243	F		
50A65-120	F	21D64-2	Lennox
50A65-121	F		
50A65-143	F		Thermo Products
50A65-288	F		Amana/Goodman
50A65-289	F		
50A65-474	F		
50A65-475	F		American Standard/Trane
50A65-476	F		
50A65-843	F		White-Rodgers Standard
50A66-123	F		Lennox
50M56-289	E	Use existing or 21D64-2	Amana/Goodman
50M56-843		50M56U-843 Replacement Kit	
50T35-730	A, C & G	Use existing or 21D64-2	Amana/Goodman
50T35-743	A, C & G		American Standard/Trane/White-Rodgers Standard
50T55-288	E & F		Amana/Goodman
50T55-289	E & F		
52537074000	F		Coleman/Evcon/Luxaire/York
52537077000	F		
56L84	F	21D64-2	Lennox
56L8401	F		
61F3	F		Texas Instruments

50M56U-843 Kit Cross-Reference and Harness Application Data
(continued)


Module Model #	Harness	Ignitor	Furnace OEM	
62-22694-xx	B & D	Use existing or 21D64-2	Rheem/RUUD*	
62-22732-xx	B & D			
62-24044-xx	B & D			
62-24045-01	B & D			
62-24046-01	B & D			
62-24084-82	B & D			
62-24268-01	B & D			
62-24268-02	B & D			
62-24268-03	B & D			
624557	B, H & I			
6245570	B, H & I	21D64-2	Nordyne	
624564	B, H & I			
6245640	B, H & I	Use existing or 21D64-2		
624591	B, H & I	21D64-2		
624591-x	B, H & I	Use existing or 21D64-2		
624628	B, H & I	21D64-2		
624628-0	B, H & I			
6246310	B, H & I			
624631-0	B, H & I			
624631A	B, H & I			
695-200	B & D	Use existing or 21D64-2	Rheem	
69M0801	F	21D64-2	Lennox	
6DT-1	F		Texas Instruments	
6DT-2	F			
710128A	B, H & I		Nordyne	
8068142	F	Use existing or 21D64-2	Whirlpool	
8068561	F			
8068563	F			
902378	B, H & I		21D64-2	Nordyne
902696	B, H & I			
903106	B, H & I	Use existing or 21D64-2	Coleman/Evcon/Lennox/ Luxaire/York	
99958174	F			
99958175	F			
B18099265	E & F			
D330927P01	F			
D330930P01	F			
D330934P01	F			
D340035P01	F			
D340774P01	F			
D341213P01	F	21D64-2		
D341396P01	F			
G951ADB1401	F			
G951ADB1401C	F			
G951ADB-1401C	F			
G951ADB1402	F	Use existing or 21D64-2	Coleman/Evcon/Luxaire/York	
G951ADB-1402	F			
G951ADB-1403	F			
G951AEB-1403	F			
HK42FZ004, HK42FZ007, HK42FZ008, HK42FZ009, HK42FZ011 or HK42FZ016	K & L			
HK42F2013‡		No Replacement‡		
ICM280	A & C	21D64-2	ICM	
P031-01267-001	F	Use existing or 21D64-2	Coleman/Evcon/Luxaire/York	
X4459	F		Lennox	
X445901	F			

Notes:
OEM furnace models abbreviated to shorten the length. Reference the control board P/N for proper replacement.
* If existing furnace circuit board has 2 green lights and NO amber light (furnace date code 3294 or earlier), an additional Flame Sensor Kit (Rheem Part 62-24044-71) may be required.
‡ 50M56U-843 will not replace HK42FZ013 or control boards with an 11-pin bar connector.
N/A = Not Available
Important: 21D64-2 Ignitor Note –
In these applications, the existing 80V ignitor must be replaced by the 120V 21D64-2 ignitor.

See our other Universal Replacement Ignition Modules:

Hot Surface Ignition Modules


Non-Integrated Module
for Silicon Carbide Ignitor
50E47-843



Integrated Module
for Nitride Ignitor
50A65-843



Universal Single Stage
HSI Integrated
Furnace Control Kit
50M56U-843



Universal Two-Stage HSI Integrated
3-Speed (PSC) Circulator
Furnace Control Kit
21M51U-843




Universal Two-Stage HSI Integrated Variable
Speed (ECM) Circulator Furnace Control Kit
21V51U-843



Spark Ignition Modules

Direct Spark Ignition Module
50D50-842



Intermittent Spark Pilot Module
50D50-843



White-Rodgers™

Replaces: Virtually All White-Rodgers and Competitive Single Stage Carbide and Nitride HSI Systems – Including Carrier HK42FZ004, HK42FZ007, HK42FZ008, HK42FZ009, HK42FZ011 and HK42FZ016.


EMERSON
Climate Technologies

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[White-Rodgers:](#)

[50M56U-843](#)