



LioN-M PROFINET I/O Modules with 16 Digital Inputs and 16 Digital Outputs



Type	0980 ESL 700
Product Description	LioN-M Profinet device with 16 digital I/O channels, channels can be used universally as inputs or outputs, M12 socket, rotary address switches for addressing, M12 LAN-Ports, D-coded, 7/8" power supply

Diagnostic indication		
LED	Indication	Condition
US	Green	Sensor power supply
UL	Green	Actuator power supply
1...8 A	Yellow	Channel status 1
1...8 DIA A	Red	Periphery fault
1...8 B	Yellow (alternative White)	Channel status 2
1...8 DIA B	Red	Periphery fault
P1 Lnk/Act	Green Yellow flashing Off	Connected to a Profinet device I/O device exchanging data No connection to a Profinet device
P2 Lnk/Act	Green Yellow flashing Off	Connected to a Profinet device I/O device exchanging data No connection to a Profinet device
BF	Red Off	Device I/O controller or wrong configuration No faults
DIA	Red Red flashing Off	General indication for periphery faults Firmware update No faults

Bit assignment								
DIA	7	6	5	4	3	2	1	0
M12 Input								
Byte 0	4B	4A	3B	3A	2B	2A	1B	1A
Byte 1	8B	8A	7B	7A	6B	6A	5B	5A
M12 Output								
Byte 0	4B	4A	3B	3A	2B	2A	1B	1A
Byte 1	8B	8A	7B	7A	6B	6A	5B	5A

Pin assignment		
LAN connection M12, D-coded  1 = TD+ 2 = RD+ 3 = TD- 4 = RD - Housing = shielding	Power supply 7/8"  1 = GND (0 V) 2 = GND (0 V) 3 = PE/Earth 4 = 24 V 5 = 24 V	Input/Output M12  1 = +24 V 2 = IN/OUT B 3 = GND (0 V) 4 = IN/OUT A 5 = earth - Housing = PE

Part number	Order number
0980 ESL 700	0980 ESL 700



Be Certain with Belden



LioN-M PROFINET I/O Modules with 16 Digital Inputs and 16 Digital Outputs

Environmental	
Degree of protection	IP 67
Operating temperature range	-10°C (+14°F) to +60°C (+140°F)
Mechanical	
Weight	380 g
Housing material	PBT
Bus system	PROFINET
Transmission rate	10/100 Mbs
Address range	0 - 255
Rotary address switches	0 - 255
Default address	0
System/Sensors power supply	System power supply
Nominal voltage	24V DC
Voltage range	11–30 V DC
Power consumption	typ. 90 mA
Reverse polarity protection	yes
Input power supply	Us
Voltage range	19–30 V DC
Sensor current	200 mA per port (at Tamb 30°C)
Short-circuit proof	yes
Indication	LED green
Inputs	Type 3 acc. to IEC 61131-3
Rated input voltage	24 V DC
Channel type N.O.	p-switching
Number of digital channels	max. 16
Channel status indicator	LED yellow per channel
Diagnostic indication	LED red per socket
Output power supply	UL
Rated voltage	24 V DC
Voltage range	19–30 V DC
Reverse polarity protection	yes/antiparallel diode
Indication	LED green
Diagnostic indication	LED red per socket
Outputs	
Rated output current	1.6 A per channel
Short-circuit proof	yes
Max. output current	9 A (12 A*) per module
Overload-proof	yes
Number of digital channels	max. 16
Channel type N.O.	p-switching
Channel status indicator	LED yellow per channel
Diagnostic indication	LED red per socket
Included in delivery/accessories	
Dust covers M12	4 pieces
Attachable labels	10 pieces

The application of these products in harsh environments should always be checked before use.
Specifications subject to alteration.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Lumberg Automation:](#)

[0980 ESL 700](#)