



Product: [9717](#)

Speaker Cable, 2 Conductor 14 AWG BC, Unshielded, CM



Product Description

2 Conductor 14 AWG stranded (19x27) ETP high-conductivity copper conductors, PVC insulation, parallel: (1) tinned, (1) bare.

Technical Specifications

Product Overview

Suitable Applications:	Speaker Cable
------------------------	---------------

Physical Characteristics (Overall)

Conductor				
AWG	Stranding	Material	Nominal Diameter	No. of Conductors
14	19x27	TC - Tinned Copper (High Conductivity)	0.071 in	1
14	19x27	BC - Bare Copper	0.071 in	1
Conductor Count:		2		

Insulation	
Material	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.035 in

Outer Shield

Material
No Shield

Outer Jacket	
Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.146 x 0.292 in

Electrical Characteristics

Conductor DCR	
Nominal Conductor DCR	
2.7 Ohm/1000ft	

Inductance	
Nominal Inductance	
0.2 µH/ft	

Current	
Max. Recommended Current [A]	
9.5 Amps per Conductor at 25°C	

Voltage	
Non-UL Voltage Rating	
300 V RMS	

Temperature Range

Non-UL Temp Rating:	60°C
Operating Temperature Range:	-20°C To +60°C

Mechanical Characteristics

Bulk Cable Weight:	40 lbs/1000ft
Max. Pull Tension:	125 lbs
Min. Bend Radius/Minor Axis:	3 in

Standards

CPR Euroclass:	Eca
----------------	-----

Applicable Environmental and Other Programs

Environmental Space:	Indoor (Not Riser or Plenum)
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LS0H, Toxicity Testing

IEC Flammability:	IEC 60332-1-2
-------------------	---------------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	UPC
9717 3681000	Clear, Transparent	Reel	1,000 ft	612825257332
9717 368U1000	Clear, Transparent	UnReel	1,000 ft	612825257356

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

History

Update and Revision:	Revision Number: 0.356 Revision Date: 02-03-2025
----------------------	--

© 2025 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[9717 3681000](#) [9717 368U1000](#)