



Product: [1054A](#)

Inst, 36 Pr #18 Str BC, PVC-NYL Ins E1, IS/OS, Blk PVC Jkt, 600V TC-ER
150V NPLF 90C Dry 75C Wet

[Request Sample](#)

Product Description

UL Instrumentation, 36 Pair 18AWG (7x26) Bare Copper, PVC-NYL Insulation E1 Color Code, Individual & Overall Beldfoil® Shield, Black PVC Outer Jacket, 600V TC-ER 150V NPLF 90C Dry 75C Wet SUN RES DIR BUR

Technical Specifications

Product Overview

Suitable Applications:	Industrial Control, Raceways Cable trays and ducts, Digital Control, Instruments (4-20ma, 0-10v, ...),low voltage digital control (24v, ...), encoders, control circuits, distributed control system (DCS),programmable logic controller (PLC), Solenoids, Valves, Actuators, Positioners
------------------------	---

Construction Details

Conductor				
Element	No. of Elements	Size	Stranding	Material
Pair(s)	36	18 AWG	7x26	BC - Bare Copper

Insulation				
Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	PVC/Nylon - Polyvinyl Chloride + Nylon	0.021 in (0.53 mm)	0.088 in (2.2 mm)	Black, White Numbered

Inner Shield					
Element	Shield Type	Material	Coverage	Drainwire Type	Notes
Pair(s)	Tape	Bi-Laminate (Alum+Poly)	100%	20 AWG (7x28) TC	Extra polyester tape for isolation

Outer Shield			
Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	18 AWG (7x26) TC

Outer Jacket				
Material	Nom. Thickness	Nom. Diameter	Ripcord	
PVC - Polyvinyl Chloride	0.083 in (2.1 mm)	1.320 in (33.53 mm)	Yes	
Overall Cable Diameter (Nominal):	1.320 in (33.53 mm)			

Electrical Characteristics

Electricals	
Element	Nom. Conductor DCR
Pair(s)	5.86 Ohm/1000ft (19.2 Ohm/km)

Voltage	
UL Voltage Rating	
600 V (TC-ER), 150 V (NPLF)	

Mechanical Characteristics

Temperature	
UL Temperature	Operating

90°C Dry, 75°C Wet	-30C to 90C Dry, 75C wet
--------------------	--------------------------

Bend Radius

Stationary Min.	Installation Min.
15.8 in (401 mm)	15.8 in (401 mm)

Max. Pull Tension:	2139 lbs (970.2 kg)
Bulk Cable Weight:	914 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Outdoor, Sunlight Resistance, Burial
Flammability / Reaction to Fire:	UL1685 (FT4 Loading), FT4, 1202
NEC / UL Compliance:	Article 336, Article 760, NPLF, TC-ER
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.575 Revision Date: 01-04-2024
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
1054A 0101250	Black	Reel	1,250 ft	612825105480	C Z

© 2024 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[1054A 0101250](#)