



Product: [9767](#)

Audio, Control & Instrument, #22-37pr, PP, Individ. Foil, PVC Jkt, CM

Product Description

Audio, Control & Instrument Cable, 37-Pair, 22 AWG stranded (7x30) tinned copper conductor, polypropylene insulation, individually shielded pairs with Beldfoil® (100% coverage), overall PVC jacket and 22 AWG stranded tinned copper drain wire.

Technical Specifications

Product Overview

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; computer communication; panel wiring
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	37	22 AWG	7x30	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Color Code
Pair(s)	PP - Polypropylene	0.0105 in (0.267 mm)	Black & Red, Black & White, Black & Green, Black & Blue, Black & Yellow, Black & Brown, Black & Orange, Red & White, Red & Green, Red & Blue, Red & Yellow, Red & Brown, Red & Orange, Green & White, Green & Blue, Green & Yellow, Green & Brown, Green & Orange, White & Blue, White & Yellow, White & Brown, White & Orange, Blue & Yellow, Blue & Brown, Blue & Orange, Brown & Yellow, Brown & Orange, Orange & Yellow, Purple & Orange, Purple & Red, Purple & White, Purple & Green, Purple & Blue, Purple & Yellow, Purple & Brown, Purple & Black, Gray & White

Inner Shield

Element	Shield Type	Material	Coverage	Drainwire Type	Notes
Pair(s)	Tape	Bi-Laminate (Alum+Poly)	100%	22 AWG (7x30) TC	Each pair

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.069 in (1.8 mm)	0.8 in (20 mm)

Overall Cable Diameter (Nominal):	0.8 in (20 mm)
-----------------------------------	----------------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedence	Nom. Velocity of Prop.	Max. Current
Pair(s)	15 Ohm/1000ft (49 Ohm/km)	30 pF/ft (98 pF/m)	55 pF/ft (180 pF/m)	50 Ohm	66%	1 Amp per Conductor at 25°C

Voltage

UL Voltage Rating
300 V (CM), 30 V (UL AWM 2919)

Mechanical Characteristics

Temperature

UL Temperature	Operating
80°C (UL AWM 2919)	-20°C to +80°C

Max. Pull Tension:	368 lbs (167 kg)
Bulk Cable Weight:	393 lbs/1000ft (585 kg/km)

Standards and Compliance

Environmental Suitability:	Indoor
Flammability / Reaction to Fire:	UL1685 UL Loading
NEC / UL Compliance:	Article 800, CM
AWM Compliance:	AWM 2919
CEC / C(UL) Compliance:	CM
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.325 Revision Date: 05-05-2023
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
9767 060500	Chrome	Reel	500 ft	612825258308	C D
9767 0601000	Chrome	Reel	1,000 ft	612825258292	C D

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[9767 0601000](#) [9767 060500](#)