



Product: [10GX32](#)

10GX Category 6A Enhanced Cable, 4 Bonded-Pairs, U/UTP, CMR

Product Description

10GX Category 6A Enhanced Premise Horizontal Cable (625MHz), 4 Bonded-Pairs, 23 AWG Solid Bare Copper Conductors, U/UTP, Riser-CMR, PVC Jacket

Technical Specifications

Product Overview

Suitable Applications:	Premise Horizontal Cable, Ethernet up to 10GBASE-T, HDBaseT, PoE++, PoE+, PoE
Patent:	This product has one or more applicable patents. More information on patents can be found at https://www.belden.com/patents .

Construction Details

Conductor

Size	Stranding	Material	No. of Pairs
23 AWG	Solid	BC - Bare Copper	4

Insulation

Material	Color Code
PO - Polyolefin	White/Blue Stripe & Blue, White/Orange Stripe & Orange, White/Green Stripe & Green, White/Brown Stripe & Brown

Bonded-Pair:	Yes
--------------	-----

Outer Jacket

Separator	Material	Nom. Diameter	Ripcord
Double H Cross-Web (Patented RoundFlex®)	PVC - Polyvinyl Chloride	0.295 in (7.49 mm)	Yes

Overall Cable Diameter (Nominal):	0.295 in (7.49 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Max. Conductor DCR	Max. Capacitance Unbalance
74 Ohm/km (23 Ohm/1000ft)	330 pF/100m

Delay

Frequency	Max. Delay	Max. Delay Skew	Nom. Velocity of Prop.
100 MHz	537.6 ns/100m	30 ns/100m	64%

High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted) [Ohm]	Max./Min. Fitted Impedance [Ohm]	Min. PSANEXT [dB]	Min. PSAACRF [dB]	Min. TCL [dB]	Min. ELTCTL [dB]
1	2.1 dB/100m	75.3	73.3	73.2	71.2	70.8	68.8	20.0	100 ± 15	100 ± 15	67.0	67.0	48.0	43.0
4	3.8 dB/100m	66.3	64.3	62.5	60.5	58.8	56.8	23.0	100 ± 15	100 ± 10.4	67.0	67.0	48.0	41.0
8	5.3 dB/100m	61.8	59.8	56.4	54.4	52.7	50.7	24.5	100 ± 15	100 ± 8	67.0	61.1	48.0	24.9
10	5.9 dB/100m	60.3	58.3	54.4	52.4	50.8	48.8	25.0	100 ± 15	100 ± 7.3	67.0	59.2	48.0	23.0
16	7.5 dB/100m	57.2	55.2	49.8	47.8	46.7	44.7	25.0	100 ± 15	100 ± 5	67.0	55.1	46.0	18.9
20	8.4 dB/100m	55.8	53.8	47.4	45.4	44.8	42.8	25.0	100 ± 15	100 ± 5	67.0	53.2	45.0	17.0
25	9.4 dB/100m	54.3	52.3	45.0	43.0	42.8	40.8	25.0	100 ± 15	100 ± 5	67.0	51.2	44.0	15.0

31.25	10.5 dB/100m	52.9	50.9	42.4	40.4	40.9	38.9	25.0	100 ± 15	100 ± 5	67.0	49.3	43.1	
62.5	15.0 dB/100m	48.4	46.4	33.4	31.4	34.9	32.9	25.0	100 ± 15	100 ± 5	66.6	43.3	40.0	
100	19.1 dB/100m	45.3	43.3	26.2	24.2	30.8	28.8	25.0	100 ± 15	100 ± 5	63.5	39.2	38.0	
200	27.6 dB/100m	40.8	38.8	13.2	11.2	24.8	22.8	21.0	100 ± 22	100 ± 5	59.0	33.2	35.0	
250	31.1 dB/100m	39.3	37.3	8.3	6.3	22.8	20.8	20.5	100 ± 32	100 ± 5	57.5	31.2	34.0	
300	34.3 dB/100m	38.1	36.1	3.9	1.9	21.3	19.3	20.1	100 ± 32	100 ± 5	56.3	29.7	33.2	
350	37.2 dB/100m	37.1	35.1			19.9	17.9	19.8	100 ± 32	100 ± 5	55.3	28.3	32.6	
400	40.1 dB/100m	36.3	34.3			18.8	16.8	19.5	100 ± 32	100 ± 5	54.5	27.2	32.0	
450	42.7 dB/100m	35.5	33.5			17.7	15.7	18.9	100 ± 32	100 ± 5	53.7	26.1	31.5	
500	45.3 dB/100m	34.8	32.8			16.8	14.8	18.4	100 ± 32	100 ± 5	53.0	25.2	31.0	
550	47.7 dB/100m	34.2	32.2			16.0	14.0	18.0	100 ± 32	100 ± 5	52.4	24.4		
600	50.1 dB/100m	33.6	31.6			15.2	13.2	17.6	100 ± 32	100 ± 5	51.8	23.6		
625	51.2 dB/100m	33.4	31.4			14.9	12.9	17.4	100 ± 32	100 ± 5	51.6	23.3		
750	56.7 dB/100m	32.2	30.2			13.3	11.3	16.5			50.4	21.7		
860	61.2 dB/100m	31.3	29.3			12.1	10.1	15.8			49.5	20.5		

Voltage

UL Voltage Rating
300 V (CMR), 300 V (CL3R)

Mechanical Characteristics

Temperature

UL Temperature	Operating	Installation	Storage
90°C	-20°C To +75°C	0°C To +50°C	-20°C To +75°C

Bend Radius

Stationary Min.	Installation Min.
0.6 in (15 mm)	3.0 in (76 mm)

Max. Pull Tension:	40 lbs (18 kg)
Bulk Cable Weight:	40 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Riser, Indoor
Sustainability:	Product Lens™, Environmental Product Declaration (EPD) Available
Flammability / Reaction to Fire:	UL 1666 Riser, FT4, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMR, CMR-LP (0.5A), CL3R-LP (0.5A)
CEC / C(UL) Compliance:	CMR
ICEA Compliance:	S-116-732
IEEE Compliance:	IEEE 802.3bt Type 1, Type 2, Type 3, Type 4
NEMA Compliance:	ANSI/NEMA WC-66
Data Category:	Category 6A
TIA/EIA Compliance:	ANSI/TIA-568.2-D Category 6A
ISO/IEC Compliance:	ISO/IEC 11801-1, IEC 61156-5
CENELEC Compliance:	Segregation class according EN50174-2 = a
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE), REACH: 2020-01-16
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Plenum Number:	10GX33

Product Notes

Notes:	Electrical values are expected performance based on cable testing and representative performance within a typical Belden system. Values above 625 MHz are for Engineering Information Only. 0.295" Cable Dimension per TIA 6@1 Equivalent Diameter. Print Includes Descending Footage/Meter Markings from Max. Put-Up Length to 0.
--------	--

History

Update and Revision:	Revision Number: 0.527 Revision Date: 04-29-2024
----------------------	--

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
10GX32 0061000	Blue	Reel	1,000 ft	612825102304	
10GX32 0081000	Gray	Reel	1,000 ft	612825102311	C
10GX32 0091000	White	Reel	1,000 ft	612825102328	C
10GX32 0041000	Yellow	Reel	1,000 ft	612825102298	C

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[10GX32 0041000](#) [10GX32 0061000](#) [10GX32 0081000](#) [10GX32 0091000](#)