



Product: [1224](#)

CAT5e+ Horizontal, 4pr, UTP, LSZH Jkt

Product Description

CAT5e+ (350MHz), 4-Pair, U/UTP-unshielded, Zero Halogen, Premise Horizontal cable, 24 AWG solid bare copper conductors, Polyethylene insulation, ripcord, LSZH jacket.

Technical Specifications

Product Overview

Suitable Applications:	Premise Horizontal Cable, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU, Digital Video, RS-422
------------------------	--

Physical Characteristics (Overall)

Conductor			
AWG	Stranding	Material	No. of Pairs
24	Solid	BC - Bare Copper	4
Conductor Count:			8
Total Number of Pairs:			4

Insulation	
Material	
PE - Polyethylene	
Bonded-Pair:	N/A

Color Chart	
Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Outer Jacket			
Material	Material Trade Name	Nominal Diameter	Ripcord
LSZH - Low Smoke Zero Halogen (Flame Retardant)	Haloarrest®	0.193 in	Yes

Electrical Characteristics

Conductor DCR	
Max. Conductor DCR	Max. DCR Unbalance
89 Ohm/km	3 %

Capacitance	
Max. Capacitance Unbalance	Nom.Mutual Capacitance
330 pF/100m	15 pF/ft

Delay			
Frequency [MHz]	Max. Delay	Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]
100 MHz	537.6 ns/100m	25 ns/100m	70%

High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance
1 MHz	2.0 dB/100m	70.3 dB	69.3 dB	68.3 dB	67.3 dB	67.8 dB	65.8 dB	20.0 dB	100 ± 15 Ohm	100 ± 15 Ohm
4 MHz	4.0 dB/100m	61.3 dB	60.3 dB	57.3 dB	56.3 dB	55.8 dB	53.8 dB	23.0 dB	100 ± 15 Ohm	100 ± 15 Ohm
8 MHz	5.7 dB/100m	56.8 dB	55.8 dB	51.1 dB	50.1 dB	49.7 dB	47.7 dB	24.5 dB	100 ± 15 Ohm	100 ± 15 Ohm
10 MHz	6.4 dB/100m	55.3 dB	54.3 dB	48.9 dB	47.9 dB	47.8 dB	45.8 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm
16 MHz	8.1 dB/100m	52.2 dB	51.2 dB	44.1 dB	43.1 dB	43.7 dB	41.7 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm
20 MHz	9.1 dB/100m	50.8 dB	49.8 dB	41.7 dB	40.7 dB	41.8 dB	39.8 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm
25 MHz	10.2 dB/100m	49.3 dB	48.3 dB	39.1 dB	38.1 dB	39.8 dB	37.8 dB	24.3 dB	100 ± 15 Ohm	100 ± 15 Ohm
31.25 MHz	11.4 dB/100m	47.9 dB	46.9 dB	36.4 dB	35.4 dB	37.9 dB	35.9 dB	23.6 dB	100 ± 15 Ohm	100 ± 15 Ohm
62.5 MHz	16.4 dB/100m	43.4 dB	42.4 dB	27.0 dB	26.0 dB	31.9 dB	29.9 dB	21.5 dB	100 ± 15 Ohm	100 ± 15 Ohm
100 MHz	21.0 dB/100m	40.3 dB	39.3 dB	19.3 dB	18.3 dB	27.8 dB	25.8 dB	20.1 dB	100 ± 15 Ohm	100 ± 15 Ohm
155 MHz	26.6 dB/100m	37.4 dB	36.4 dB	10.9 dB	9.9 dB	24.0 dB	22.0 dB	18.8 dB	100 ± 22 Ohm	100 ± 15 Ohm
200 MHz	30.5 dB/100m	35.8 dB	34.8 dB	5.3 dB	4.3 dB	21.8 dB	19.8 dB	18.0 dB	100 ± 22 Ohm	100 ± 15 Ohm
250 MHz	34.4 dB/100m	34.3 dB	33.3 dB	-0.1 dB	-1.1 dB	19.8 dB	17.8 dB	17.3 dB	100 ± 32 Ohm	100 ± 15 Ohm
300 MHz	38.0 dB/100m	33.1 dB	32.1 dB	1.9 dB		18.3 dB	16.3 dB	14.4 dB	100 ± 32 Ohm	100 ± 15 Ohm
350 MHz	41.4 dB/100m	32.1 dB	31.1 dB			16.9 dB	14.9 dB	13.8 dB	100 ± 32 Ohm	100 ± 15 Ohm
400 MHz	44.6 dB/100m	31.3 dB	30.3 dB			15.8 dB	13.8 dB	13.3 dB	100 ± 32 Ohm	100 ± 15 Ohm
450 MHz	47.7 dB/100m	30.5 dB	29.5 dB			14.7 dB	12.7 dB	12.8 dB	100 ± 32 Ohm	100 ± 15 Ohm

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

Installation Temperature Range:	+5°C To +50°C
Non-UL Temp Rating:	+75°C
Storage Temperature Range:	-20°C To +75°C
Operating Temperature Range:	-20°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	25 lbs/1000ft
Max. Pull Tension:	25 lbs
Min. Bend Radius During Installation:	2.0 in
Min. Bend Radius/Minor Axis:	1.0 in

Standards

ISO/IEC Compliance:	11801 ed 2.2 (2011) Class D
CPR Euroclass:	Eca
Data Category:	Category 5e
ANSI Compliance:	S-90-661-2012 Category 5e, ANSI/NEMA WC-63.1 Category 5e
TIA/EIA Compliance:	ANSI/TIA-568-C.2 Category 5e
IEEE Compliance:	IEEE 802.3bt Type 1, Type 2, Type 3

Applicable Environmental and Other Programs

Environmental Space:	Indoor - Euroclass Eca
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	Yes
EU CE Mark:	No
EU REACH SVHC Compliance (yyyy-mm-dd):	2017-07-10
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Aerial:	No
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Non-Halogenated:	Yes
Suitability - Oil Resistance:	No
Suitability - Outdoor:	No
Suitability - Sunlight Resistance:	No

Flammability, LS0H, Toxicity Testing

IEC Flammability:	IEC 60332-1-2
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	1213

Related Part Numbers

Non-Plenum Number:	1212
--------------------	------

Variants

Item #	Color	Put-Up Type	Length	UPC/EAN
1224.08U305	Gray	UnReel	305 m	8719605000682
1224.07U305	Purple	UnReel	305 m	8719605000675
1224 007U1000	Purple	UnReel	1,000 ft	612825061526
1224.09U305	White	UnReel	305 m	8719605000705
1224.09500	White	Reel	500 m	8719605000699

Product Notes

Notes:	Electrical values are expected performance based on cable testing and representative performance within a typical Belden system. Values above 350 MHz are for Engineering Information Only. Print Includes Descending Footage/Meter Markings.
--------	---

History

Update and Revision:	Revision Number: 0.516 Revision Date: 04-29-2024
----------------------	--

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[1224 007U1000](#)