

B9C010 Fiber - Breakout Cable - Riser



For more Information
please call

1-800-Belden1



General Description:

FiberExpress Breakout Cable with 2.0mm Subunits, 12-Fiber, OM3 OFNR, Tight Buffer, Indoor Rated with Aqua Jacket, Breakout or fanout cables are designed for harsh environment installations and offer a high degree of flexibility for backbone and horizontal applications.

Physical Characteristics (Overall)

Product Family - Plenum:

Fiber Count	Type	B.O.	OM1 MM 62.5/125 1 Gb	OM2 MM 50/125 1 Gb	OM3 MM 50/125 10 Gb 300m	OM4 MM 50/125 10 gB 500m	OS2 SM
2	Indoor	2.0mm	B9B013	B9A013	B9C013	B9E013	B9W013
2	Indoor	2.5mm	B9B029	B9A029	B9C029	B9E029	B9W029
4	Indoor	2.0mm	B9B014	B9A014	B9C014	B9E014	B9W014
4	Indoor	2.5mm	B9B030	B9A030	B9C030	B9E030	B9W030
6	Indoor	2.0mm	B9B015	B9A015	B9C015	B9E015	B9W015
6	Indoor	2.5mm	B9B031	B9A031	B9C031	B9E031	B9W031
6	Indoor/Outdoor	2.5mm	B9B031T	B9A031T	B9C031T	B9E031T	B9W031T
8	Indoor	2.0mm	B9B016	B9A016	B9C016	B9E016	B9W016
10	Indoor	2.0mm	B9B017	B9A017	B9C017	B9E017	B9W017
12	Indoor	2.0mm	B9B018	B9A018	B9C018	B9E018	B9W018
12	Indoor	2.5mm	B9B034	B9A034	B9C034	B9E034	B9W034
18	Indoor	2.0mm	B9B019	B9A019	B9C019	B9E019	B9W019
24	Indoor	2.0mm	B9B020	B9A020	B9C020	B9E020	B9W020

Product Family - Riser:

Fiber Count	Type	B.O.	OM1 MM 62.5/125 1Gb	OM2 MM 50/125 1Gb	OM3 MM 50/125 10Gb 300m	OM4 MM 50/125 10Gb 500m	OS2 SM
2	Indoor	2.0mm	B9B005	B9A005	B9C005	B9E005	B9W005
2	Indoor/LSZH	2.0mm	B9B130	B9A130	B9C130	B9E130	B9W130
2	Indoor/Outdoor	2.5mm	B9B021T	B9A021T	B9C021T	B9E021T	B9W021T
4	Indoor	2.0mm	B9B006	B9A006	B9C006	B9E006	B9W006
4	Indoor/LSZH	2.0mm	B9B131	B9A131	B9C131	B9E131	B9W131
4	Indoor	2.5mm	B9B022	B9A022	B9C022	B9E022	B9W022
6	Indoor	2.0mm	B9B007	B9A007	B9C007	B9E007	B9W007
6	Indoor/LSZH	2.0mm	B9B132	B9A132	B9C132	B9E132	B9W132
6	Indoor	2.5mm	B9B023	B9A023	B9C023	B9E023	B9W023
8	Indoor	2.0mm	B9B008	B9A008	B9C008	B9E008	B9W008
8	Indoor/LSZH	2.0mm	B9B133	B9A133	B9C133	B9E133	B9W133
10	Indoor	2.0mm	B9B009	B9A009	B9C009	B9E009	B9W009
10	Indoor/LSZH	2.0mm	B9B134	B9A134	B9C134	B9E134	B9W134
12	Indoor	2.0mm	B9B010	B9A010	B9C010	B9E010	B9W010
12	Indoor/LSZH	2.0mm	B9B135	B9A135	B9C135	B9E135	B9W135
12	Indoor	2.5mm	B9B026	B9A026	B9C026	B9E026	B9W026
18	Indoor	2.0mm	B9B011	B9A011	B9C011	B9E011	B9W011
18	Indoor/LSZH	2.0mm	B9B136	B9A136	B9C136	B9E136	B9W136
18	Indoor	2.5mm	B9B027	B9A027	B9C027	B9E027	B9W027
24	Indoor	2.0mm	B9B012	B9A012	B9C012	B9E012	B9W012
24	Indoor/LSZH	2.0mm	B9B137	B9A137	B9C137	B9E137	B9W137
36	Indoor/LSZH	2.0mm	B9B138	B9A138	B9C138	B9E138	B9W138

B9C010 Fiber - Breakout Cable - Riser

Fiber Type: 50 Micron (OM3)

Number of Fibers: 12

Buffer Tube Material: Thermoplastic

Breakout Element Diameter: .0787

Inner Jacket**Inner Jacket Color Code Chart:**

Number	Color
1	Blue
2	Orange
3	Green
4	Brown
5	Gray
6	White
7	Red
8	Black
9	Yellow
10	Violet
11	Pink
12	Aqua

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material
PVC - Polyvinyl Chloride

Outer Jacket Color: Aqua

Strength Member

Strength Member Material: Aramid Yarn

Overall Cable

Overall Nominal Diameter: 13.056 mm

Mechanical Characteristics (Overall)

Storage Temperature Range: -40°C To +75°C

Installation Temperature Range: 0°C To +70°C

Operating Temperature Range: -20°C To +70°C

Bulk Cable Weight: 163.702 Kg/Km

Min. Bend Radius/Minor Axis: 195.580 mm

Min. Bend Radius for Long Term Application: 129.540 mm

Max. Load for Installation: 667.230 N

Max. Load for Long Term Application: 200.169 N

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification: OFNR

CEC/C(UL) Specification: OFN

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 12/17/2008

EU Directive 2002/96/EC (WEEE): Yes

B9C010 Fiber - Breakout Cable - Riser

EU Directive 2003/11/EC (BFR):	Yes
--------------------------------	-----

CA Prop 65 (CJ for Wire & Cable):	Yes
-----------------------------------	-----

MII Order #39 (China RoHS):	Yes
-----------------------------	-----

Flame Test

UL Flame Test:	UL910 Steiner Tunnel
----------------	----------------------

CSA Flame Test:	FT4
-----------------	-----

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Suitability - Outdoor:	No
------------------------	----

Suitability - Aerial:	No
-----------------------	----

Suitability - Burial:	No
-----------------------	----

Sunlight Resistance:	No
----------------------	----

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Optical Characteristics (Overall)

Maximum Attenuation @ 850nm:	3.0 dB/km
------------------------------	-----------

Maximum Attenuation @ 1300nm:	1.2 dB/km
-------------------------------	-----------

Minimum Bandwidth @ 850nm:	1500 MHz*km
----------------------------	-------------

Minimum Bandwidth @ 1300nm:	500 MHz*km
-----------------------------	------------

Maximum Gigabit Ethernet Length @ 850nm:	1000 meters
--	-------------

Maximum Gigabit Ethernet Length @ 1300nm:	550 meters
---	------------

Fiber Coding MLT EMEA:

Fiber/Tube No.	Color
1	Blue
2	Orange
3	Green
4	Brown
5	Slate
6	White
7	Red
8	Black
9	Yellow
10	Violet
11	Rose
12	Aqua

Related Documents:

[Breakout Cable.pdf](#) - Breakout Cable technical information.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
B9C010	1 FT	0.129 LB	AQUA		REPLACED BY FI3B012RB

Revision Number: 2 Revision Date: 08-12-2014

© 2019 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or

B9C010 Fiber - Breakout Cable - Riser

exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[B9C010](#)