




Product: [1352A](#) 

Category 6 Cable, 4 Pair, F/UTP, CMP

Product Description

Category 6 Premise Horizontal Cable (250MHz), 4 Pair, 23 AWG Solid Bare Copper Conductors, F/UTP - Foil Shielded, Plenum-CMP, Flamarrest® PVC-LS Jacket

Technical Specifications

Product Overview

Suitable Applications:	Premise Horizontal Cable, Ethernet 1000BASE-T, Ethernet 100BASE-TX, Ethernet 10BASE-T, Surveillance, PoE++, PoE+, PoE, Noisy Environments
Patent:	This product has one or more applicable patents. More information on patents can be found at https://www.belden.com/resources/patents .

Construction Details

Conductor

AWG	Stranding	Material	Number of Pairs
23	Solid	BC - Bare Copper	4

Insulation

Material	Color Code
FEP - Fluorinated Ethylene Propylene	White/Blue Stripe & Blue, White/Orange Stripe & Orange, White/Green Stripe & Green, White/Brown Stripe & Brown

Bonded-Pair:	No
--------------	----

Outer Shield Material

Type	Material	Coverage	Drainwire Type
Tape	Polyester + Bi-Laminate (Alum+Poly)	100%	24 AWG (Solid) TC

Outer Jacket Material

Separator Material	Material	Material Trade Name	Nom. Diameter	Ripcord
Center Member (Patented X-Spline®)	PVC - Polyvinyl Chloride	Flamarrest®	0.310 in	No

Electrical Characteristics

Electricals

Max. Conductor DCR	Max. DCR Unbalance	Max. Capacitance Unbalance	Nom. Mutual Capacitance
93.8 Ohm/km	3%	160 pF/100m	14 pF/ft

Delay

Frequency [MHz]	Max. Delay	Max. Delay Skew
100 MHz	537.6 ns/100m	45 ns/100m

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance	Min. TCL [dB]	Min. ELTCTL [dB]
1 MHz	2.0 dB/100m	74.3 dB	72.3 dB	70.3 dB	67.8 dB	64.8 dB	20.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	40.0 dB	35.0 dB
4 MHz	3.8 dB/100m	65.3 dB	63.3 dB	59.5 dB	55.7 dB	52.7 dB	23.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	40.0 dB	23.0 dB
8 MHz	5.3 dB/100m	60.8 dB	58.8 dB	53.4 dB	49.7 dB	46.7 dB	24.5 dB	100 ± 15 Ohm	100 ± 15 Ohm	40.0 dB	16.9 dB
10 MHz	6.0 dB/100m	59.3 dB	57.3 dB	51.4 dB	47.8 dB	44.8 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	40.0 dB	15.0 dB

16 MHz	7.6 dB/100m	56.3 dB	54.3 dB	46.7 dB	43.7 dB	40.7 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	38.0 dB	10.9 dB
20 MHz	8.5 dB/100m	54.8 dB	52.8 dB	44.3 dB	41.7 dB	38.7 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	37.0 dB	9.0 dB
25 MHz	9.5 dB/100m	53.3 dB	51.3 dB	41.8 dB	39.8 dB	36.8 dB	24.3 dB	100 ± 15 Ohm	100 ± 15 Ohm	36.0 dB	7.0 dB
31.25 MHz	10.7 dB/100m	51.9 dB	49.9 dB	39.2 dB	37.9 dB	34.9 dB	23.6 dB	100 ± 15 Ohm	100 ± 15 Ohm	35.1 dB	5.1 dB
62.5 MHz	15.4 dB/100m	47.4 dB	45.4 dB	30.0 dB	31.8 dB	28.8 dB	21.5 dB	100 ± 15 Ohm	100 ± 15 Ohm	32.0 dB	
100 MHz	19.8 dB/100m	44.3 dB	42.3 dB	22.5 dB	27.8 dB	24.8 dB	20.1 dB	100 ± 15 Ohm	100 ± 15 Ohm	30.0 dB	
155 MHz	25.2 dB/100m	41.5 dB	39.5 dB	14.3 dB	23.9 dB	20.9 dB	18.8 dB	100 ± 22 Ohm	100 ± 15 Ohm	28.1 dB	
200 MHz	29.0 dB/100m	39.8 dB	37.8 dB	8.8 dB	21.7 dB	18.7 dB	18.0 dB	100 ± 22 Ohm	100 ± 15 Ohm	27.0 dB	
250 MHz	32.8 dB/100m	38.3 dB	36.3 dB	3.5 dB	19.8 dB	16.8 dB	17.3 dB	100 ± 32 Ohm	100 ± 15 Ohm	26.0 dB	

Voltage

UL Voltage Rating
300 V (CMP)

Mechanical Characteristics

Temperature

UL Rating	Operating	Installation	Storage
75°C	-20°C To +75°C	0°C To +50°C	-20°C To +75°C

Bend Radius

Stationary Min.	Installation Min.
1.0 in	2.25 in

Max. Pull Tension:	25 lbs
Bulk Cable Weight:	44 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Plenum, Indoor
Sustainability:	Product Lens™, Environmental Product Declaration (EPD) Available
Flammability / Fire Resistance:	NFPA 262, UL 910 (Plenum), FT6, FT6, IEC 60332-1-2
NEC / UL Compliance:	800, CMP
CEC / C(UL) Compliance:	CMP
ICEA Compliance:	S-116-732-2013
IEEE Compliance:	IEEE 802.3bt Type 1, Type 2, Type 3, Type 4
NEMA Compliance:	ANSI/NEMA WC-66
Data Category:	Category 6
TIA/EIA Compliance:	ANSI/TIA-568.2-D Category 6
CPR Euroclass:	Eca
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE), REACH: 2020-01-16
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Part Number

Non-Plenum Number:	1351A
--------------------	-------

Variants

Item #	Color	Putup Type	Length	UPC
1352A D151000	Blue	Reel	1,000 ft	612825112457
1352A 0081000	Gray	Reel	1,000 ft	612825112471
1352A 0091000	White	Reel	1,000 ft	612825112488
1352A 0041000	Yellow	Reel	1,000 ft	612825112464

Product Notes

Notes:	Electrical values are expected performance based on cable testing and representative performance within a typical Belden system. Shield is Bonded to Jacket Inner Wall for Electrical Stability. Print Includes Descending Footage Markings from Max. Put-Up Length to 0.
--------	---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

History

Update and Revision:	Revision Number: 0.403 Revision Date: 08-25-2020
----------------------	--------------------------------------------------

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Belden Wire & Cable:

[1352A 0041000](#) [1352A 0081000](#) [1352A 0091000](#) [1352A D151000](#)