



Product: [FISI001LC](#)

Indoor LSZH/Riser OS2 Interconnect 1F SX SX Cord 3.0mm

Product Description

FX Indoor OS2 Interconnect 1 Fiber LSZH/OFNR SX SX Cord 3.0MM (900UM) Yellow Jacket

Technical Specifications

Part Number:	FISI001LC
Construction Type:	Interconnect

Product Overview

Environmental Space:	Indoor
Suitable Applications:	Indoor

Construction

Fiber Cable Construction

Fiber Type	Fiber Count
OS2	1

Buffer Specification

Buffer Material	Buffer Diameter
LSZH	900 μm

Bulk Cable Weight:	5.5 lbs/1000ft
--------------------	----------------

Jacket Specifications

Outer Jacket Material

Material	Nominal Diameter
LSZH	0.11 in (2.8 mm)

Outer Jacket Color:	Yellow
OuterJacket1, Nominal Diameter:	0.118 in

Optical Characteristics

Mode Field Diameter:	9.2
Fiber Core Diameter:	8.2/125μm
Max Attenuation at 1310 nm:	0.5 dB/km
Max Attenuation at 1550 nm:	0.5 dB/km
Wavelength:	1310 nm / 1550 nm
10 Gigabit Ethernet Performance:	10,000 m / 40,000 m
1 Gigabit Ethernet Performance:	5,000 m / -

Mechanical Characteristics

Mechanical Tests

Description	Requirement/Value
Cable Min. Bend Radius Installation (Short Term)	20x Cable OD
Cable Min. Bend Radius Operation (Long Term)	10x Cable OD

Cable Max. Tensile Strength Installation (Short Term)	11 N (50 lbf)
Cable Max. Tensile Strength Operation (Long Term)	3 N (15 lbf)

Temperature Range

Operating Temp Range:	0C to +70C
Installation Temp Range:	-10C to +60C
Storage Temp Range:	-40C to +70C

Standards

UL Rating/Flame Test:	LSZH/Riser
CEC/C(UL) Specification:	FT4
NEC/(UL) Specification:	OFNR
Telecommunications Standards:	ANSI/ICEA S-83-596
RoHS:	Yes

History

Variants

Item #	Color	UPC
FISI001LC	Yellow	612825286776

Update and Revision:	Revision Number: 0.44 Revision Date: 03-04-2019
----------------------	---

© 2019 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[FISI001LC](#)