



For more Information
please call

1-800-Belden1



General Description:

20 AWG solid .032" bare copper conductor, plenum, foam FEP insulation, Duofoil® + tinned copper braid shield (95% coverage), Flamarrest® jacket.

Usage (Overall)

Suitable Applications: SMPTE 2081-1 6 Gb/s UHD TV, SMPTE 424M 3 Gb/s HD-SDI 1080p

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (mm)
1	20	Solid	BC - Bare Copper	0.8128

Total Number of Conductors: 1

Insulation

Insulation Material:

Insulation Trade Name	Insulation Material	Dia. (mm)
Teflon®	FFEP - Foam Fluorinated Ethylene Propylene	3.3782

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Duofoil®	Tape	Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	TC - Tinned Copper	95

Outer Jacket

Outer Jacket Material:

Outer Jacket Trade Name	Outer Jacket Material
Flamarrest®	PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 4.978 mm

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +75°C

UL Temperature Rating: 75°C

Bulk Cable Weight: 43.158 Kg/Km

Max. Recommended Pulling Tension: 302.478 N

Min. Bend Radius/Minor Axis: 50.800 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMP

CEC/C(UL) Specification: CMP

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
RG Type:	59/U

Flame Test

UL Flame Test:	NFPA 262
CSA Flame Test:	FT6

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	Yes
Non-Plenum Number:	1505A

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)
75

Nom. Inductance:

Inductance (µH/m)
0.318257

Nom. Capacitance Conductor to Shield:

Capacitance (pF/m)
52.8241

Nominal Velocity of Propagation:

VP (%)
84

Nominal Delay:

Delay (ns/m)
3.97001

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
32.81

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)
10.4992

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100m)
1.000	0.951
3.580	2.034
5.000	2.297
7.000	2.690
10.000	3.445
67.500	7.218
71.500	7.382
100.000	8.859
135.000	10.499

143.000	10.663
180.000	11.976
270.000	14.929
360.000	17.225
540.000	20.998
720.000	23.951
750.000	24.608
1000.000	29.529
1500.000	37.075
2250.000	47.246
3000.000	56.433
4500.000	71.526
6000.000	84.978

Max. Operating Voltage - UL:

Voltage
300 V RMS

Other Electrical Characteristic 1: Impedance: 75 +/- 3 Ohms

Other Electrical Characteristic 2: Return Loss: Fixed bridge and termination.

Minimum Return Loss:

Start Freq. (MHz)	Stop Freq. (MHz)	Min. RL (dB)
5.000	1600.000	23.000
1600.000	4500.000	21.000
4500.000	6000.000	15.000

Sweep Test

Sweep Testing: 100%; Sweep tested 5 MHz to 6 GHz.

Notes (Overall)

Notes: Print legend includes sequential footage marks.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1506A N3U1000	1,000 FT	31.000 LB	GREEN, MIL	C Z	#20 FFEP SH FLMRST
1506A 0011000	1,000 FT	31.000 LB	BROWN	C Z	#20 FFEP SH FLMRST
1506A 0021000	1,000 FT	31.000 LB	RED	C Z	#20 FFEP SH FLMRST
1506A 0025000	5,000 FT	155.000 LB	RED		#20 FFEP SH FLMRST
1506A 0031000	1,000 FT	31.000 LB	ORANGE	Z	#20 FFEP SH FLMRST
1506A 0041000	1,000 FT	31.000 LB	YELLOW	Z	#20 FFEP SH FLMRST
1506A 0045000	5,000 FT	155.000 LB	YELLOW		#20 FFEP SH FLMRST
1506A 0061000	1,000 FT	31.000 LB	BLUE, LIGHT	C Z	#20 FFEP SH FLMRST
1506A 0065000	5,000 FT	155.000 LB	BLUE, LIGHT		#20 FFEP SH FLMRST
1506A 0071000	1,000 FT	31.000 LB	VIOLET	C Z	#20 FFEP SH FLMRST
1506A 0075000	5,000 FT	155.000 LB	VIOLET		#20 FFEP SH FLMRST
1506A 0081000	1,000 FT	31.000 LB	GRAY	Z	#20 FFEP SH FLMRST
1506A 0085000	5,000 FT	155.000 LB	GRAY		#20 FFEP SH FLMRST
1506A 0095000	5,000 FT	155.000 LB	WHITE		#20 FFEP SH FLMRST
1506A 0101000	1,000 FT	31.000 LB	BLACK	C	#20 FFEP SH FLMRST
1506A 010500	500 FT	16.500 LB	BLACK	C Z	#20 FFEP SH FLMRST
1506A 0105000	5,000 FT	155.000 LB	BLACK		#20 FFEP SH FLMRST
1506A 8771000	1,000 FT	31.000 LB	NATURAL	C	#20 FFEP SH FLMRST
1506A 877500	500 FT	16.500 LB	NATURAL	C Z	#20 FFEP SH FLMRST
1506A 8775000	5,000 FT	155.000 LB	NATURAL		#20 FFEP SH FLMRST

Notes:

C = CRATE REEL PUT-UP.

Z = FINAL PUT-UP LENGTH MAY VARY (+ OR -) 10% FOR SPOOLS OR REELS AND (+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

Revision Number: 7 Revision Date: 04-12-2017

© 2019 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Belden Wire & Cable:

[1506A 877500](#) [1506A N3U1000](#) [1506A 010500](#) [1506A \(RED PRINT 1000'\)](#) [1506A 0011000](#) [1506A 0081000](#)
[1506A 8771000](#) [1506A 0101000](#) [1506A 0031000](#) [1506A 0041000](#) [1506A 0021000](#) [1506A 0071000](#) [1506A 0061000](#)
[1506A 0091000](#) [1506A 00Q](#)