



Product: [1617AP](#)

Broadband Coax, Series 11, 14 AWG Solid BCCS, Quad Shield, PVDF Jkt, CMP

Product Description

Broadband Coax, Series 11, 14 AWG Solid Bare Copper Covered Steel Conductor, FEP Insulation, Foil + 60% Aluminum Braid + Foil + 40% Aluminum Braid Shield, PVDF Jacket, CMP

Technical Specifications

Product Overview

Suitable Applications:	Broadband, Cable Television (CATV), RF drop cable, Direct Broadcast Satellite (DBS), Over-The-Air (OTA) antennas
Suitable Applications:	Broadband, Cable Television (CATV), RF drop cable, Direct Broadcast Satellite (DBS), Over-The-Air (OTA) antennas

Construction Details

Series Type:	11
Series Type:	11

Conductor

Size	Stranding	Nom. Diameter	Material
14 AWG	Solid	0.064 in	BCCS - Bare Copper Covered Steel

Conductor

Size	Stranding	Nom. Diameter	Material
14 AWG	Solid	0.064 in	BCCS - Bare Copper Covered Steel

Insulation

Material	Nom. Insulation Diameter	Color Code
FEP - Fluorinated Ethylene Propylene (Foam)	0.274 in (6.96 mm)	White

Insulation

Material	Nom. Insulation Diameter	Color Code
FEP - Fluorinated Ethylene Propylene (Foam)	0.274 in (6.96 mm)	White

Outer Shield

Layer	Outer Shield Type	Material	Material Trade Name	Coverage
1	Tape	Tri-Laminate (Alum+Poly+Alum)	Duobond® II	100%
2	Braid	Aluminum		60%
3	Tape	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%
4	Braid	Aluminum		40%

Outer Shield

Layer	Outer Shield Type	Material	Material Trade Name	Coverage
1	Tape	Tri-Laminate (Alum+Poly+Alum)	Duobond® II	100%
2	Braid	Aluminum		60%
3	Tape	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%
4	Braid	Aluminum		40%

Outer Jacket

Material	Nom. Diameter
PVDF - Polyvinylidene Fluoride	0.372 in (9.45 mm)

Outer Jacket

Material	Nom. Diameter
PVDF - Polyvinylidene Fluoride	0.372 in (9.45 mm)

Overall Cable Diameter (Nominal):	0.372 in (9.45 mm)
Overall Cable Diameter (Nominal):	0.372 in (9.45 mm)

Electrical Characteristics

Return Loss (RL)

Frequency	Min. Structural Return Loss
5 - 1000 MHz	20 dB
1000 - 2250 MHz	15 dB

Return Loss (RL)

Frequency	Min. Structural Return Loss
5 - 1000 MHz	20 dB
1000 - 2250 MHz	15 dB

Attenuation

Frequency	Max. Attenuation
5 MHz	0.38 dB/100ft
55 MHz	0.96 dB/100ft
211 MHz	1.90 dB/100ft
240 MHz	2.43 dB/100ft
270 MHz	2.59 dB/100ft
300 MHz	2.75 dB/100ft
325 MHz	2.92 dB/100ft
350 MHz	3.08 dB/100ft
400 MHz	3.34 dB/100ft
450 MHz	3.64 dB/100ft
500 MHz	3.92 dB/100ft
550 MHz	4.19 dB/100ft
600 MHz	4.48 dB/100ft
750 MHz	5.31 dB/100ft
870 MHz	5.86 dB/100ft
1000 MHz	6.53 dB/100ft

Attenuation

Frequency	Max. Attenuation
5 MHz	0.38 dB/100ft
55 MHz	0.96 dB/100ft
211 MHz	1.90 dB/100ft
240 MHz	2.43 dB/100ft
270 MHz	2.59 dB/100ft
300 MHz	2.75 dB/100ft
325 MHz	2.92 dB/100ft
350 MHz	3.08 dB/100ft
400 MHz	3.34 dB/100ft
450 MHz	3.64 dB/100ft
500 MHz	3.92 dB/100ft
550 MHz	4.19 dB/100ft
600 MHz	4.48 dB/100ft
750 MHz	5.31 dB/100ft
870 MHz	5.86 dB/100ft
1000 MHz	6.53 dB/100ft

Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
12 Ohm/1000ft	3 Ohm/1000ft (9.8 Ohm/km)	16.3 pF/ft (53.5 pF/m)	75 Ohm	83%

Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
--------------------	-----------------------	---------------------------------	-------------------------------	------------------------

12 Ohm/1000ft	3 Ohm/1000ft (9.8 Ohm/km)	16.3 pF/ft (53.5 pF/m)	75 Ohm	83%
---------------	---------------------------	------------------------	--------	-----

Voltage

UL Voltage Rating
300 V (CMP)

Voltage

UL Voltage Rating
300 V (CMP)

Mechanical Characteristics

Temperature

UL Temperature	Operating
150°C	-20°C to +150°C

Temperature

UL Temperature	Operating
150°C	-20°C to +150°C

Bend Radius

Installation Min.
3.7 in (94 mm)

Bend Radius

Installation Min.
3.7 in (94 mm)

Max. Pull Tension:	308 lbs (140 kg)
Max. Pull Tension:	308 lbs (140 kg)
Bulk Cable Weight:	63 lbs/1000ft
Bulk Cable Weight:	63 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor - Plenum, Indoor, Aerial - Black only, When supported by messenger wire
Environmental Suitability:	Indoor - Plenum, Indoor, Aerial - Black only, When supported by messenger wire
Sustainability:	CA Prop 65
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	NFPA 262
Flammability / Reaction to Fire:	NFPA 262
CEC / C(UL) Compliance:	CMP
CEC / C(UL) Compliance:	CMP
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Non-Plenum Number:	1617A, 7999A
Non-Plenum Number:	1617A, 7999A

History

Update and Revision:	Revision Number: 0.360 Revision Date: 04-29-2024
Update and Revision:	Revision Number: 0.360 Revision Date: 04-29-2024

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC
1617AP 0101000	Black	Reel	1,000 ft	612825119265

Variants

Item #	Color	Putup Type	Length	UPC
1617AP 0101000	Black	Reel	1,000 ft	612825119265

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[1617AP 0101000](#)