



lumbergautomation

A **BELDEN** BRAND




0936 DMC 355 | 0936 DFC 355



5-Pole, Male

DeviceNet, 5-pole, male 7/8" receptacle, assembled THIN cable, shielded, 1/2" NPT thread for panel mount.

0936 DMC 355




0936 DFC 355



5-Pole, Female


DeviceNet, 5-pole, female 7/8" receptacle, assembled THIN cable, shielded, 1/2" NPT thread for panel mount.



Pin Assignments

Face Views, 7/8"

5 pole



1 = green
2 = red
3 = black
4 = white
5 = blue



Be Certain with Belden

DeviceNet Receptacles, 7/8"

0936 DMC 355 | 0936 DFC 355

Technical Data

Environmental	
Degree of protection	IP 67 / NEMA 6P
Operating temperature range	-25°C (-13°F) / +90°C (+194°F)
Materials	
Housing	DMC: Zinc die cast, e-coated black DFC: Aluminum, anodized clear
Insert	PUR, yellow
Contacts	Brass, gold over nickel plated per DN specification
Electrical	
Current rating	4 A
Voltage rating	300 V
Cable specifications	
Cable jacket	Thin cable (614) PVC, grey
Shielding	Shielded
Overall diameter	.270"
Conductor	1Pair, 22 AWG / 1 Pair 24 AWG
Cable construction	According to DeviceNet THIN cable specifications

Part Number		Pins	Cable Lengths	Characteristics
Male	Female			
0936 DMC 355/...M		5	1 M / 2 M / 3 M / 4 M / 5 M	
	0936 DFC 355/...M	5	1 M / 2 M / 3 M / 4 M / 5 M	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lumberg Automation:

[0936 DFC 355/2M](#) [0936 DFC 355/3M](#) [0936 DMC 355/12M](#) [0936 DMC 355/2M](#) [0936 DFC 355/2.5M](#) [0936 DFC](#)
[355/3F](#) [0936 DMC 355/1M](#) [0936 DMC 355/2F](#) [0936 DFC 355/6M](#) [0936 DMC 355/3M](#) [0936 DMC 355/4M](#) [0936 DFC](#)
[355/0.3M](#) [0936 DFC 355/4M](#)