

1794A Coax - Low Loss Serial Digital Coax



For more Information
please call

1-800-Belden1

**General Description:**

RG-7 Type 16 AWG solid 0.051" bare copper conductor, gas-injected foamed high-density polyethylene insulation, Duofoil® + tinned copper braid shield (95% coverage) plus Beldfoil® with shorting fold, PVC jacket.

Usage (Overall)

Suitable Applications: SMPTE 2081-1 6 Gb/s UHDTV, SMPTE 424M 3 Gb/s HD-SDI 1080p

Physical Characteristics (Overall)**Conductor**

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (mm)
1	16	Solid	BC - Bare Copper	1.295

Total Number of Conductors: 1

Insulation

Insulation Material:

Insulation Material	Dia. (mm)
Gas-injected FHDPE - Foam High Density Polyethylene	5.715

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Duofoil®	Tape	Aluminum Foil-Polyester Tape-Aluminum Foil	100.000
2		Braid	TC - Tinned Copper	95.000
3	Beldfoil® with shorting fold	Tape	Polyester Tape-Aluminum Foil	100.000

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 8.128 mm

Mechanical Characteristics (Overall)

Operating Temperature Range: -30°C To +75°C

Bulk Cable Weight: 87.804 Kg/Km

Max. Recommended Pulling Tension: 493.750 N

Min. Bend Radius/Minor Axis: 82.550 mm

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification: CMR

CEC/C(UL) Specification: CMG

EU Directive 2011/65/EU (ROHS II): Yes

1794A Coax - Low Loss Serial Digital Coax

EU CE Mark:	Yes
-------------	-----

EU Directive 2000/53/EC (ELV):	Yes
--------------------------------	-----

EU Directive 2002/95/EC (RoHS):	Yes
---------------------------------	-----

EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
---------------------------------------	------------

EU Directive 2002/96/EC (WEEE):	Yes
---------------------------------	-----

EU Directive 2003/11/EC (BFR):	Yes
--------------------------------	-----

CA Prop 65 (CJ for Wire & Cable):	Yes
-----------------------------------	-----

MII Order #39 (China RoHS):	Yes
-----------------------------	-----

Series Type:	Series 7
--------------	----------

Flame Test

UL Flame Test:	UL1666 Vertical Shaft
----------------	-----------------------

CSA Flame Test:	FT4
-----------------	-----

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)**Nom. Characteristic Impedance:**

Impedance (Ohm)

75

Nom. Inductance:

Inductance (μH/m)

0.299

Nom. Capacitance Conductor to Shield:

Capacitance (pF/m)

52.824

Nominal Velocity of Propagation:

VP (%)

84.000

Nominal Delay:

Delay (ns/m)

3.970

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

13.124

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)

6.234

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100m)
-------------	-----------------------

1.000	0.558
-------	-------

3.580	0.984
-------	-------

5.000	1.148
-------	-------

6.000	1.247
-------	-------

7.000	1.312
-------	-------

10.000	1.575
--------	-------

12.000	1.706
--------	-------

25.000	2.428
--------	-------

55.000	3.543
--------	-------

67.500	3.937
--------	-------

METRIC MEASUREMENT VERSION

1794A Coax - Low Loss Serial Digital Coax

71.500	4.068
88.500	4.495
100.000	4.790
135.000	5.578
143.000	5.742
180.000	6.464
270.000	7.973
360.000	9.285
540.000	11.812
720.000	13.780
750.000	14.108
1000.000	16.405
1500.000	20.342
2000.000	24.279
2250.000	25.592
3000.000	30.185
4500.000	38.388
6000.000	45.179

Max. Operating Voltage - UL:

Voltage

300 V RMS

Other Electrical Characteristic 1:

TDR Impedance: 75 +/- 3 Ohms

Other Electrical Characteristic 2:

Return Loss: Fixed bridge and termination.

Minimum Return Loss:

Start Freq. (MHz)	Stop Freq. (MHz)	Min. RL (dB)
5.000	1600.000	23.000
1600.000	4500.000	21.000
4500.000	6000.000	15.000

Sweep Test

Sweep Testing:

100% Sweep tested 5 MHz to 6 GHz.

Notes (Overall)

Notes: Also available in 4.5 GHz multi-coax bundled version. See 2177A.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1794A N3U1000	1,000 FT	59.000 LB	GREEN, MIL	C	#16 LDPE/GIFHDLDP SH FRPVC
1794A 0011000	1,000 FT	59.000 LB	BROWN	C	#16 LDPE/GIFHDLDP SH FRPVC
1794A 0021000	1,000 FT	59.000 LB	RED	C	#16 LDPE/GIFHDLDP SH FRPVC
1794A 0031000	1,000 FT	59.000 LB	ORANGE	C	#16 LDPE/GIFHDLDP SH FRPVC
1794A 0041000	1,000 FT	59.000 LB	YELLOW	C	#16 LDPE/GIFHDLDP SH FRPVC
1794A 0061000	1,000 FT	59.000 LB	BLUE, LIGHT	C	#16 LDPE/GIFHDLDP SH FRPVC
1794A 0071000	1,000 FT	59.000 LB	VIOLET	C	#16 LDPE/GIFHDLDP SH FRPVC
1794A 0081000	1,000 FT	59.000 LB	GRAY	C	#16 LDPE/GIFHDLDP SH FRPVC
1794A 0091000	1,000 FT	59.000 LB	WHITE	C	#16 LDPE/GIFHDLDP SH FRPVC
1794A 010N1000	1,000 FT	60.000 LB	BLACK		#16 LDPE/GIFHDLDP SH FRPVC
1794A 0101000	1,000 FT	59.000 LB	BLACK	C	#16 LDPE/GIFHDLDP SH FRPVC
1794A 0102500	2,500 FT	157.500 LB	BLACK		#16 LDPE/GIFHDLDP SH FRPVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 4 Revision Date: 06-17-2016

© 2019 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications

1794A Coax - Low Loss Serial Digital Coax

described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Belden Wire & Cable:

[1794A 0011000](#) [1794A 0021000](#) [1794A 0031000](#) [1794A 0041000](#) [1794A 0061000](#) [1794A 0071000](#) [1794A 0081000](#) [1794A 0091000](#) [1794A 0101000](#) [1794A N3U1000](#) [1794A 010N1000](#)