


Product: [1810A](#) 



Speaker Cable, 4 Conductor 14 AWG BC, Unshielded, CM

Product Description

Speaker Cable, 4 Conductor 14 AWG stranded (104x34) high conductivity bare copper conductors with polyolefin insulation, CL3 & CM PVC jacket.

Technical Specifications

Physical Characteristics (Overall)

Conductor			
AWG	Stranding	Material	No. of Conductors
14	104x34	BC - Bare Copper	4
Conductor Count:			4

Insulation	
Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.125 in

Color Chart	
Number	Color
1	Red
2	Green
3	White
4	Black

Outer Shield	
Material	No Shield

Outer Jacket			
Material	Nominal Diameter	Min. Wall Thickness	Separator Material
PVC - Polyvinyl Chloride	0.39 in	0.002 in	Paper Tape

Construction and Dimensions

Cabling	
Filler	Polypropylene

Cabling 2	
Filler	Paper Tape - Separator Material

Electrical Characteristics

Conductor DCR	
Nominal Conductor DCR	2.7 Ohm/1000ft

Capacitance

Nom. Capacitance Between Conductors in Quad	Nom. Capacitance Conductor to Conductor
57 pF/ft	18.5 pF/ft

Inductance

Nominal Inductance
0.2 µH/ft

Current

Max. Recommended Current [A]
9.5 Amps per Conductor at 25°C

Voltage

Non-UL Voltage Rating
300 V RMS

Electrical Characteristics Notes:	57 pF/ft - Nom. Cap. Between Cond. in a Quad Config.
-----------------------------------	--

Temperature Range

Non-UL Temp Rating:	60°C
Operating Temp Range:	-20°C To +60°C

Mechanical Characteristics

Bulk Cable Weight:	105 lbs/1000ft
Max. Pull Tension:	200 lbs
Min. Bend Radius/Minor Axis:	4 in

Applicable Environmental and Other Programs

Environmental Space:	Indoor (Not Riser or Plenum)
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Put-Up Type	Length	UPC
1810A B59250	Black, Matte	Reel	250 ft	612825123316
1810A B59500	Black, Matte	Reel	500 ft	612825123323
1810A B591000	Black, Matte	Reel	1,000 ft	612825123309

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

Product Notes

Notes:	Suggested Connectors: Neutrik Speakon®
--------	--

History

Update and Revision:	Revision Number: 0.305 Revision Date: 12-15-2021
----------------------	--

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[1810A B59500](#) [1810A B59250](#) [1810A B591000](#)