


0950 ISL 202

8 In

Interbus Installation Remote Bus terminal with 8 digital inputs (PNP) and M23 bus connectors. Features: Short circuit detection, protection degree IP67 / NEMA 6P, shock and vibration protected by using potting technology.



Diagnostic indication

LED	Indication	Condition
1...8	yellow	channel status
U _S	green	sensor supply active
U _L	green	module electronic supply active
BA	green	bus active
RC	green	remote bus-in connected
RD	red	continuing remote bus disconnected
OVL	red	sensor short circuit / sensor overload

Pin Assignment

Bus Connection Input M23



- 1 = DO
- 2 = DO
- 3 = DI
- 4 = DI
- 5 = COM
- 6 = earth
- 7 = +24 V
- 8 = GND (0 V)
- 9 = n.c.
- housing = earth

Bus Connection Output M23



- 1 = DO
- 2 = DO
- 3 = DI
- 4 = DI
- 5 = COM
- 6 = earth
- 7 = +24 V
- 8 = GND (0 V)
- 9 = RBST
- housing = earth

Input M12



- 1 = +24 V
- 2 = n.c.
- 3 = GND (0 V)
- 4 = IN
- 5 = earth



Technnical data	
Degree of protection	IP 67
Operating temperature range	0°C(+32°F) / +60°C (+140°F)
Weight	500 g
Housing	PUR
Slave profile	
ID code	10 dec
Power supply of the electronics (U_e)	
Nominal voltage	24 V DC
Voltage range	19-30 V DC
Current consumption	max. 70 mA
Reverse polarity protection	yes
Operating indicator (U _i)	LED, green
Power supply of the sensors (U_s)	
Nominal voltage	24 V DC
Voltage range	19 V - 30 V DC
Total current of all sensors	max. 400 mA
Short circuit protection	yes
Sensor short circuit indicator (OVL)	LED, red
Sensor pwr. supply indication (U _s)	LED, green
Input levels	
Nominal input voltage	24 V DC
Input	PNP
Number of digital channels	8
Channel status indicator	LED, yellow

Part Number

0950 ISL 202



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Lumberg Automation:](#)

[0950 ISL 202](#)