



Product: [1843A](#) 



DBS Cable, Dual RG6, 18 AWG BCCS, Foil + Braid

Product Description

Series 6, 18 AWG solid .040" bare copper-covered steel conductor, gas-injected foam polyethylene insulation, Duobond® II, aluminum braid shield (60% coverage), polyethylene jacket.

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
18	Solid	BCCS - Bare Copper Covered Steel	0.04 in	2

Conductor Count: 2

Insulation

Material	Nominal Diameter
PE - Polyethylene (Foam)	0.18 in

Table Notes: Gas Injected

Outer Shield

Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%
Braid	2	Aluminum		60%

Table Notes: Coreguard®

Outer Jacket

Material	Nominal Diameter
PE - Polyethylene	0.273 x 0.75 in

Construction and Dimensions

Static Ground:	BCCS - Bare Copper Covered Steel
Static Ground Diameter:	0.045 in

Electrical Characteristics

Conductor DCR		
Nominal Conductor DCR	Nominal Outer Shield DCR	Outer Conductor DCR
28 Ohm/1000ft	9 Ohm/1000ft	9 Ohm/1000ft
Capacitance		
Nom. Capacitance Conductor to Shield		
16.2 pF/ft		
Inductance		
Nominal Inductance		
0.097 µH/ft		
Impedance		

Nominal Characteristic Impedance
75 Ohm

Return Loss (RL)

Frequency [MHz]	Min. Structural Return Loss (SRL)
950 - 2250 MHz	15 dB
2250 - 3000 MHz	10 dB

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
5 MHz	0.5 dB/100ft
55 MHz	1.4 dB/100ft
211 MHz	2.6 dB/100ft
500 MHz	4.1 dB/100ft
750 MHz	5.1 dB/100ft
862 MHz	5.5 dB/100ft
1000 MHz	6 dB/100ft
1450 MHz	7.8 dB/100ft
1800 MHz	8.6 dB/100ft
2250 MHz	9.8 dB/100ft
3000 MHz	11.3 dB/100ft

Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.2 ns/ft	83%

High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)
5 MHz	0.58 dB/100ft
55 MHz	1.6 dB/100ft
211 MHz	3.05 dB/100ft
500 MHz	4.66 dB/100ft
750 MHz	5.65 dB/100ft
862 MHz	6.1 dB/100ft
1000 MHz	6.55 dB/100ft
1450 MHz	8 dB/100ft
1800 MHz	8.8 dB/100ft
2250 MHz	10 dB/100ft
3000 MHz	11.9 dB/100ft

Voltage

Non-UL Voltage Rating
350 V RMS

Temperature Range

Non-UL Temp Rating:	80°C
Operating Temp Range:	-55°C To +80°C

Mechanical Characteristics

Bulk Cable Weight:	57 lbs/1000ft
Max. Pull Tension:	195 lbs
Min. Bend Radius/Minor Axis:	3 in

Standards

RG Type:	6
Series Type:	6

Applicable Environmental and Other Programs

Environmental Space:	Outdoor - Water Exposure
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes

EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	No
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Burial:	Yes
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Put-Up Type	Length	UPC
1843A 0101000	Black	Reel	1,000 ft	612825124412

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

History

Update and Revision:	Revision Number: 0.376 Revision Date: 12-15-2021
----------------------	--

© 2022 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[1843A 0101000](#)