


LioN-Link I/O Module with 8 Digital Inputs

0942 UEM 601



8 IN

LioN-Link I/O module with 8 digital inputs to connect standard sensors, M12 sockets (4 x), 5 poles



Bit Assignment

Bit	7	6	5	4	3	2	1	0
M12 Input								
Byte 0	4B	4A	3B	3A	2B	2A	1B	1A


Diagnostic Indication

LED	Indication	Condition
1...4 A/B	yellow	channel status
1...4 A/B	red	periphery fault
I/O	red red flashing green	wrong configuration / module exchanged not recognized by the BusHead online, communication with BusHead
Us	green	sensor/system power supply
DIA	red	common indication for periphery faults

Pin Assignment

Bus connection M12	Actuator/sensor connection M12
<p>1 = Drain 2 = 24 V Sensor/System 3 = 0 V Sensor/System 4 = Data + 5 = Data -</p>	<p>1 = +24 V 2 = In B 3 = GND (0 V) 4 = In A 5 = Earth</p>

Be Certain with Belden



LioN-Link I/O Module with 8 Digital Inputs

0942 UEM 601

Technical Data

Environmental

Degree of protection	IP 67
Operating temperature range	-10°C (+14°F) to +60°C (+140°F)

Mechanical

Weight	200 g
Housing material	PBT

System/sensors

power supply	Us
Rated voltage	24 V DC
Voltage range	19–30 V DC
Power consumption	typ. 70 mA
Operating indication	LED green

Input power supply

Us	
Voltage range	min. (U _{System} – 1.5 V)
Sensor current	700 mA/module
Short circuit proof	yes
Indication	LED green

Input wiring

Type 3 acc. to IEC 61131-2	
Rated input voltage	24 V DC
Channel type N.O.	p-switching
Number of digital channels	max. 8
Channel status indicator	LED yellow per channel
Diagnostic indication	LED red per channel

Included in

delivery/accessories	Dust covers M12, attachable labels
-----------------------------	------------------------------------

Diagnostic

Periphery fault diagnosis for sensor short circuit, actuator short circuit /channel, sensor low voltage detection

Part Number

0942 UEM 601



The application of these products in harsh environments should always be checked before use.
Specifications subject to alteration.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Lumberg Automation:](#)

[0942 UEM 601](#)