



Product: [1908A](#)



Audio Snake Cable, #24-8pr, BC, Individ. Shielded

Product Description

Audio Snake Cable, 8-24 AWG bare copper pairs, polyolefin insulation, individually shielded with double serve "French Braid", drain, numbered/color-coded PVC jackets, flexible PVC jacket

Technical Specifications

Product Overview

Suitable Applications:	Recording Studio, Radio Broadcast, Sports Stadium, Nurse Call
------------------------	---

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Pairs
24	41x40	BC - Bare Copper	0.023 in	8

Conductor Count:	16
------------------	----

Insulation

Material	Nominal Diameter	Nominal Wall Thickness
PP - Polypropylene	0.04 in	0.008 in

Color Chart

Color
Numbered
Red and Black

Inner Shield

Type	Material	Coverage [%]	Drainwire Material	Drainwire Diameter	Drainwire AWG	Drainwire Construction n x D
French Braid	Bare Copper (BC)	95%	TC - Tinned Copper	0.025 in	24	19x26

Inner Jacket

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.119 in	0.0135 in

Outer Shield

Material
No Shield

Outer Jacket

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.482 in	0.050 in

Electrical Characteristics

Conductor DCR

Individual Pair Nominal Shield DCR	Nominal Conductor DCR	Nominal Conductor DCR Conductor Resistance
7.2 Ohm/1000ft	25.5 Ohm/1000ft	25.5 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
26.1 pF/ft	47.5 pF/ft

Inductance

Nominal Inductance
0.18 µH/ft

Impedance

Nominal Characteristic Impedance
60 Ohm

Delay

Nominal Velocity of Propagation (VP) [%]
66%

Current

Max. Recommended Current [A]
1.05 Amps per Conductor at 25°C

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

Operating Temperature Range:	-20°C To +60°C
------------------------------	----------------

Mechanical Characteristics

Bulk Cable Weight:	130 lbs/1000ft
Max. Pull Tension:	230 lbs
Min. Bend Radius/Minor Axis:	5 in

Standards

CPR Euroclass:	Eca
----------------	-----

Applicable Environmental and Other Programs

Environmental Space:	Indoor (Not Riser or Plenum)
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	No
MIL Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LSOH, Toxicity Testing

IEC Flammability:	IEC 60332-1-2
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	UPC
1908A B59250	Black, Matte	Reel	250 ft	612825126454

1908A B59500	Black, Matte	Reel	500 ft	612825126461
1908A B591000	Black, Matte	Reel	1,000 ft	612825126447

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

History

Update and Revision:	Revision Number: 0.433 Revision Date: 01-10-2024
----------------------	--

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[1908A B59250](#) [1908A B59500](#) [1908A B591000](#)