

Product: PP12M-MSSV4A-0288




M12 pigtail, Push Pull, industrial sensor cable, PUR black cable, shielded, male, straight, A-coded, 4-Pin, 4x0.34mm²

Product Description

M12 pigtail, Push Pull, industrial sensor cable, PUR black cable, shielded, male, straight, A-coded, 4-Pin, 4x0.34mm², 50 V AC / 60 V DC, 4 A, - 40 °C - + 85 °C (operating temp.), IP65, IP67

Technical Drawing



Technical Specifications

Technical Data

Product Family:	Sensor / Actuator Connectors
Product Sub Family:	M12 Standard push pull
Brand:	Lumberg Automation
Connector Type:	Cordset, single ended
Type of Contact / Gender:	Male
Connector Design:	Straight
Number of Pins:	4
Coding:	A
Shielding:	Shielded
Attachment Type:	Snap Ring
Rated Voltage:	60 V
Rated Voltage (UL):	50 V AC / 60 V DC
Rated Impulse Voltage:	1.5 kV
Operating Voltage:	50 V AC / 60 V DC
Rated Current*:	4 A
Rated Current (UL)*:	4A
Contact Resistance:	≤ 10 mOhm
Insulation Resistance:	> 10^9 Ohm
Mating Cycles:	≤ 100

Ambient Temperature (Operation)*:	- 40 °C - + 85 °C
Operating Temperature (UL):	max. 80 °C
Protection Degree / IP Rating**:	IP65, IP67
Pollution Degree:	3 acc. to DIN EN 60664-1 (VDE 0110-1)
Overvoltage Category:	III acc. to DIN EN 60664-1 (VDE 0110-1)

Materials

Contact Base Material:	CuSn
Contact Plating:	Cu/Au
Contact Bearer Material:	PA
Contact Bearer Color:	Black
Flammability Class (Contact Bearer):	UL 94 V-0
Molded Body Material:	TPU
Molded Body Color:	Black
Flammability Class (Molded Body):	UL 94 HB
Attachment Material:	PA
Shielding Material:	GD-Zn, nickel-plated

Additional Technical Data

|--|

Cable Data

Cable Number:	288
Conductor Size:	0.34 mm ²
Number of Wires:	4
Minimal Bending Radius (Fixed Inst):	>5xD
Minimal Bending Radius (Flexible Inst):	> 10 x D
Cycles (Bending):	> 5 Mio.
Cycles (Torsion):	> 1 M @ ± 180 °/1 m
Conductor material:	Cu
Cable Jacket Material:	PUR
Cable Jacket Color:	black
Cable Diameter D:	ø 5.50 ± 0.20 mm
Wire Insulation Material:	PP
Insulated Wire Diameter:	ø 1.30 ±0.1 mm
Overall Shield (Cable):	Cu-ETP1 tinned
Ambient Temperature (Fixed Installation):	- 50 °C - + 80 °C
Ambient Temperature (Flex Installation):	- 25 °C - + 80 °C
Ambient Temperature (Drag Chain Inst):	- 25 °C - + 60 °C
UL Cable Type:	AWM: 20549
Flammability Class (Cable Jacket):	DIN EN 60332-2-2, VDE 0482-332-2-2, IEC 60332-2-2, CSA FT2
Cable Characteristics:	Free of lacquer wetting disturbing substances; Good microbes and hydrolysis resistance; Mainly plasticizer diffusion free; Exclusion of PVC and silicone; Coldness flexibility
Core Colors:	brown, white, blue, black

Approvals

UL-File:	pending
UL:	UL 2238; cULus (pending)

Safety & Environmental Compliance

RoHS Compliant:	yes
Resistances	
Halogenfree:	DIN EN 50267-2-1, IEC 60754-1, VDE 0482-267-2-1
Oil Resistance:	Yes
Notes	
Note Derating:	* Notice derating

Variants

Item #	Item Description	Rated Current
935301004	PP12M-MSSV4A-0288-0500	4 A
935301003	PP12M-MSSV4A-0288-0300	4 A
935301002	PP12M-MSSV4A-0288-0200	4 A
935301001	PP12M-MSSV4A-0288-0100	4 A

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulators based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lumberg Automation:

PP12M-MSSV4A-0288-0500 PP12M-MSSV4A-0288-0100 PP12M-MSSV4A-0288-0200 PP12M-MSSV4A-0288-0300