

# Product: PP12M-MSSV5A-0253




M12 pigtail, Push Pull, CANopen/DevicerNet cable, PUR black cable, shielded, male, straight, D-coded, 4-Pin + Shield Pin, Data: 2x0.25 mm<sup>2</sup> + Power: 2x0.34 mm<sup>2</sup>

## **Product Description**

M12 pigtail, Push Pull, CANopen/DevicerNet cable, PUR black cable, shielded, male, straight, D-coded, 4-Pin + Shield Pin, Data: 2x0.25 mm<sup>2</sup> + Power: 2x0.34 mm<sup>2</sup>50 V AC / 60 V DC, 4 A, - 40 °C - + 80 °C (operating temp.), IP65, IP67, DIN EN 60332-1-2, VDE 0482-332-1-2, IEC 60332-1-2, UL VW-1, CSA FT-1, exclusion of dangerous materials, line construction acc. CAN-Bus and DeviceNET specification

## **Technical Drawing**



# **Technical Specifications**

#### **Technical Data**

Product Family:	Data Connectors
Product Sub Family:	M12 Standard push pull
Brand:	Lumberg Automation
Connector Type:	Cordset, single ended
Type of Contact / Gender:	Male
Connector Design:	Straight
Number of Pins:	5
Coding:	A
Shielding:	Shielded
Attachment Type:	Snap Ring
Rated Voltage:	60 V
Rated Impulse Voltage:	1.5 kV
Operating Voltage:	50 V AC / 60 V DC
Rated Current*:	4 A
Data Transmission:	CANopen / DeviceNet
Contact Resistance:	≤ 10 mOhm
Insulation Resistance:	> 10^9 Ohm
Mating Cycles:	≤ 100

Ambient Temperature (Operation)*:	- 40 °C - + 85 °C
Protection Degree / IP Rating**:	IP65, IP67
Pollution Degree:	3 acc. to DIN EN 60664-1 (VDE 0110-1)
Overvoltage Category:	III acc. to DIN EN 60664-1 (VDE 0110-1)

## **Materials**

Contact Base Material:	CuSn
Contact Plating:	Cu/Au
Contact Bearer Material:	РА
Contact Bearer Color:	Black
Flammability Class (Contact Bearer):	UL 94 V-0
Molded Body Material:	TPU
Molded Body Color:	Black
Flammability Class (Molded Body):	UL 94 HB
Attachment Material:	PA
Shielding Material:	GD-Zn, nickel-plated

# **Additional Technical Data**

Fastening Torque (Attachment):	PushPull

# Cable Data

Cable Number:	253
Conductor Size:	Data: 2x0.25 mm <sup>2</sup> + Power: 2x0.34 mm <sup>2</sup>
Number of Wires:	4
Minimal Bending Radius (Fixed Inst):	> 5 x D
Minimal Bending Radius (Flexible Inst):	> 10 x D
Conductor material:	Cu
Cable Jacket Material:	PUR
Cable Jacket Color:	black
Cable Diameter D:	ø 6.70 ± 0.20 mm
Wire Insulation Material:	Data: PE + Power: PE or PP
Insulated Wire Diameter:	Data: ø 2.05 ± 0.10 mm + Power: ø 1.40 ± 0.05 mm
Overall Shield (Cable):	Cu-ETP1 tinned
Ambient Temperature (Fixed Installation):	- 50 °C - + 80 °C
Ambient Temperature (Flex Installation):	- 25 °C - + 80 °C
Ambient Temperature (Drag Chain Inst):	- 25 °C - + 60 °C
UL Cable Type:	AWM: 20549 or 21198
Flammability Class (Cable Jacket):	DIN EN 60332-1-2, VDE 0482-332-1-2, IEC 60332-1-2, UL VW-1, CSA FT-1
Cable Characteristics:	Free of lacquer wetting disturbing substances, Exclusion of silicone, Coldness flexibility
Core Colors:	Data pair: blue, white; Power pair: red, black

# Safety & Environmental Compliance

RoHS Compliant:	yes
Resistances	
Halogenfree:	DIN EN 50267-2-1, IEC 60754-1, VDE 0482-267-2-1
Halogenfree: Oil Resistance:	DIN EN 50267-2-1, IEC 60754-1, VDE 0482-267-2-1 Yes

## Notes

Note Derating:	* Notice derating
Protection Degree / IP Rating Note:	** only if mounted and locked in combination with Hirschmann / Lumberg Automation connector.

#### Variants

Item #	Item Description
935301020	PP12M-MSSV5A-0253-0500
935301019	PP12M-MSSV5A-0253-0300
935301018	PP12M-MSSV5A-0253-0200
935301017	PP12M-MSSV5A-0253-0100

#### © 2024 Belden, Inc

#### All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulators based on their individual usage of the product.

# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lumberg Automation:

 PP12M-MSSV5A-0253-0010
 PP12M-MSSV5A-0253-0300
 PP12M-MSSV5A-0253-0100
 PP12M-MSSV5A-0253-0200

 PP12M-MSSV5A-0253-0500
 PP12M-MSSV5A-0253-0100
 PP12M-MSSV5A-0253-0200
 PP12M-MSSV5A-0253-0200