



Product: [R301601](#)

IND RUGG RJ45 T568A AWG22-24 IP20 CAT6A UTP/STP FIELD KIT

[Request Sample](#)

Product Description

DATATUFF ® INDUSTRIAL ETHERNET RUGGEDIZED RJ45 T568A PLUG CAT6A UTP/STP (FIELD KIT) SUITABLE FOR USE IN IP20 INSTALLATION

Technical Specifications

Product Overview

Suitable Applications:	noisy environment, harsh environment, IIoT, factory or process automation, IP cameras and devices, data communication, etc.
------------------------	---

Physical Characteristics (Overall)

Height:	0.62
Width:	0.54
Depth:	2.06
Wiring Scheme:	T568A
Packaging:	Individually packaged in a plastic bag.
Weight:	0.060 lbs

Connectors

Materials

Description	Material	Type
Front Connection	Copper Clad PCB, Gold plated contacts	RJ45
Rear Connection	Zinc diecast - Nickel plated	Ind DataTuff
Connector Body	Nickel plated zinc alloy diecast	

Electrical Characteristics

Dielectric Strength:	1,000V RMS @ 60 Hz for 1 minute (Signals to Ground)
Current Rating:	1.500 A
Insulation Resistance:	500 M-Ohm Minimum
Max Contact Resistance:	20 mOhm
Termination Resistance:	2.5 m-Ohm

Temperature Range

Installation Temperature Range:	-40°C To +85°C
Storage Temperature Range:	-40°C To +85°C
Operating Temperature Range:	-40°C To +85°C

Mechanical Characteristics

Footprint/Type:	Modular
Plug /Jack Compatibility:	RJ45
Termination Front Connection:	Mated Connection
Termination Front Connection Durability:	750 cycles
Termination Rear Connection:	Mated Connection

Termination Rear Connection Durability:	750 cycles
Connector/Hardware Retention:	20 lbs
Plug/Connector Retention:	11.250 lbs

Standards

UL Rating:	UL94V-0
TIA/EIA Compliance:	Category 6A - TIA 568.2-D, Category 6A - ISO/IEC 11801:2002 Ed.2
IEEE Compliance:	Power Over Ethernet (PoE) IEEE 802.3at type 1 and 2 (up to 30W), IEEE802.3bt/D1.7 type 3 and 4 (up to 100W), CISCO UPOE (up to 60W), Power over HDBaseTTM (up to 100W)
Other Standards:	IEC 60603-7, FCC Part 68-F

Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2002/95/EC (RoHS):	Yes
MII Order #39 (China RoHS):	EUP 50

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL2043 Air Handling Spaces
Safety Listing:	c(UL)us Listed

Related Part Numbers

Related Parts:	DataTuff Cables, Connectors and Accessories
----------------	---

Product Notes

Notes:	Please see Installation Guide PX105479. Suitable for use with cables 300V RMS and 600V AWM. Outer Jacket Diameter range: 0.197 to 0.354 in. Insulation Diameter range: 0.043 to 0.063 in. Parallel Pliers-Wrench recommended as per Installation Guide.
--------	---

History

Update and Revision:	Revision Number: 0.82 Revision Date: 02-24-2025
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[R301601 000S1](#)