

M12 Field Attachable Connectors (DUO)


RSC...DUO | RKC...DUO



Male, 4- and 5-Pole


Field attachable connector, M12 Duo male connector, 4- and 5-pole with threaded joint, for two cable connections, assembling with screw terminals.

RSC...DUO



*a O-Ring

RKC...DUO



*a O-Ring




Female, 4- and 5-Pole

Field attachable connector, M12 Duo female connector, 4- and 5-pole with threaded joint, for two cable connections, assembling with screw terminals.


Pin Assignments

Face Views / M12, Male / Female

4 pole



5 pole





Be Certain with Belden

M12 Field Attachable Connectors (DUO)

RSC...DUO | RKC...DUO

Technical Data

Environmental



Degree of protection IP 67 / NEMA 6P
Operating temperature range -25°C (-13°F) / +90°C (+194°F)

Mechanical

Housing / Molded body PBT
Insert PBT
Contact CuZn, pre-coppered, CuSnZn
Receptacle shell CuZn, nickel plated
O-ring FKM
Mode of connection Screw terminals
Connectable conductor max. 0.75 mm²

Electrical

Contact resistance ≤ 5 mΩ
Nominal current at 40°C 4 A
Nominal voltage 4 poles 240 V
5 poles 60 V
Rated voltage 4 poles 250 V
5 poles 63 V
Test voltage 4 poles 2.0 kV eff. / 60 s
5 poles 1.5 kV eff. / 60 s
Insulation resistance > 10⁹ Ω
Pollution degree 3

Part Number		Pins	Cable Diameter Range	Characteristics
Male	Female			
RSC 4/DUO	RKC 4/DUO	4	2 x 3 mm / 2 x 5 mm	
RSC 5/DUO	RKC 5/DUO	5	2 x 3 mm / 2 x 5 mm	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Lumberg Automation:](#)

[RKC 5/DUO single pk of 1](#) [RKC 4/DUO single pk of 1](#)