

RSRK 701B...801M




Mini, 1"-Round-Plug Connector, Double-Ended Cordsets, US Color Code

7- and 8-Poles

Mini, 1" double-ended cordsets, male straight to female straight connector, 7- and 8-poles with molded cable, US color code.


RSRK



Pin Assignments


Mini, 1" - Male / Female

7 poles



- 1 = white/black
- 2 = black
- 3 = white
- 4 = red
- 5 = orange
- 6 = blue
- 7 = green

8 poles



- 1 = orange
- 2 = blue
- 3 = white/black
- 4 = black
- 5 = white
- 6 = red
- 7 = green
- 8 = red/black

Be Certain with Belden

Cordsets Double-Ended



Mini, 1"-Round-Plug Connector, Double-Ended Cordsets, US Color Code RSRK 701M...801M

Technical Data

Environmental

Degree of protection	IP 67 / NEMA 6P
Operating temperature range	-40°C (-40°F) / +90°C (194°F)

Mechanical

Housing / Molded body	TPU, yellow
Insert	TPU, yellow
Contact	CuZn, gold over silver plated
Coupling nut	Aluminum, anodized black

Electrical

Current rating	7 pole: 8 A
	8 pole: 7 A

Voltage rating	300 V
----------------	-------

Cable Specifications - US Color Code

Cable No.	Outer Jacket	Gauge	Jacket Color	OD	Temperature Rating	Agency Approvals
649	PUR	18AWG	Yellow	.270" (6.9 mm)	-40°C (-40°F) to +80°C (176°F)	UL: AWM 20233 / CSA: AWM I/II A/B
650	PUR	18AWG	Yellow	.292" (7.4 mm)	-40°C (-40°F) to +80°C (176°F)	UL: AWM 20233 / CSA: AWM I/II A/B

Part Number	Pins	Outer Jacket	Standard Cable Lengths	Characteristics
RSRK 701M-649/...F	7	PUR	6 F / 12 F / 15 F / 20 F / 30 F	
RSRK 801M-650/...M	8	PUR	6 F / 12 F / 15 F / 20 F / 30 F	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lumberg Automation:

[RSRK 701M-649/6F](#) [RSRK 801M-650/12F](#) [RSRK 701M-649/15F](#) [RSRK 801M-650/20F](#) [RSRK 701M-649/30F](#)
[RSRK 801M-650/30F](#) [RSRK 70M-649/25M](#) [RSRK 70M-649/2.5M](#) [RSRK 801M-650/8F](#) [RSRK 70M-649/10M](#) [RSRK](#)
[701M-649/20F](#) [RSRK 801M-650/15F](#) [RSRK 701M-649/12F](#) [RSRK 701M-649/1F](#) [RSRK 801M-650/6F](#)