



Product: [3079E](#)

Profibus, 1 Pr #22 Str BC, PE Ins, OS+TC Brd, PVC Jkt, PLTC CMG Profibus DP

[Request Sample](#)

Product Description

Profibus, 1 Pair 22AWG (7x30) Bare Copper, PE Insulation, Overall Beldfoil®+Tinned Copper Braid(65%) Shield, PVC Outer Jacket, PLTC CMG SUN RES Profibus DP

Technical Specifications

Product Overview

Suitable Applications:	harsh environment, outdoors, data transmission applications such as Profibus DP or PA, Instrumentation and computer cable, etc. exposure to temperature extremes, humidity/moisture, dust, and oil.
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	1	22 AWG	7x30	BC - Bare Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code	Notes
Pair(s)	PE - Polyethylene (Foam)	0.035 in (0.89 mm)	0.102 in (2.59 mm)	Red & Green	Flame Retardant, Foam w/ skin

Outer Shield

Shield Type	Material	Coverage
Tape	Bi-Laminate (Alum+Poly)	100%
Braid	Tinned Copper (TC)	65%

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.043 in (1.1 mm)	0.314 in (7.98 mm)

Table Notes:	Jacket OD +/- 0.007
Overall Cable Diameter (Nominal):	0.314 in (7.98 mm)

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Characteristic Impedence	Nom. Velocity of Prop.	Max. Current
Pair(s)	17.6 Ohm/1000ft	150 Ohm	78%	6 Amps per Conductor at 30°C

Nom. Outer Shield DCR:	6.32 Ohm/1000ft (20.7 Ohm/km)
------------------------	-------------------------------

High Frequency (Nominal/Typical)

Element
Pair(s)

High Frequency

Max. Insertion Loss (Attenuation)
0.51 dB/100m
1.57 dB/100m

4.8 dB/100m
-------------

Voltage

UL Voltage Rating
300 V (CMG, PLTC)

Mechanical Characteristics

Temperature

UL Temperature	Operating
60°C	-20°C to +75°C

Bend Radius

Stationary Min.	Installation Min.
3.768 in (95.71 mm)	3.768 in (95.71 mm)

Max. Pull Tension:	41 lbs (19 kg)
Bulk Cable Weight:	39 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance
Flammability / Reaction to Fire:	UL 1685 FT4 Loading, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 725, Article 800, CMG, PLTC
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark

History

Update and Revision:	Revision Number: 0.563 Revision Date: 02-03-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
3079E B021000	Purple	Reel	1,000 ft	612825140412	C
3079E B025000	Purple	Reel	5,000 ft	612825140443	C Z

© 2025 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[3079E B023280](#) [3079E B021640](#) [3079E B021000](#) [3079E B025000](#)