



Product: [30800](#)

Lead Wire, #2/0 Str TC, Silicone Ins, Fiber Glass Jkt, AWM 3126

[Request Sample](#)

Product Description

Rubber Lead Wire, 2/0AWG (504x26) Tinned Copper, Silicone Insulation, Fiber Glass Outer Jacket, AWM 3126 CSA SEW-2 600V 200C

Technical Specifications

Product Overview

Suitable Applications:	Class 130(B), 155(F) or 180(H) insulation systems, internal wiring of lighting fixtures and appliances, high temperature applications
------------------------	---

Physical Characteristics (Overall)

Conductor			
AWG	Stranding	Material	No. of Conductors
2/0	504x26	TC - Tinned Copper	1
Conductor Count:			1

Insulation

Material	Nominal Wall Thickness
Silicone Rubber	0.08 in

Outer Jacket

Material	Nominal Diameter
Lacquered Glass Braid Covering	0.712 in

Electrical Characteristics

Voltage

UL Voltage Rating
600 V RMS

Temperature Range

UL Temp Rating:	200°C
Operating Temperature Range:	-70°C To +200°C

Mechanical Characteristics

Recommended Max Baking Cycles:	24 Hours @ 410°F (210°C)
Bulk Cable Weight:	576 lbs/1000ft
Min. Bend Radius/Minor Axis:	2.85 in

Standards

UL AWM Style Compliance:	AWM 3126
CSA Rating:	600 V, 200°C
CSA Type:	SEW-2

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
--------------------------------	-----

EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
CA Prop 65:	Yes
MII Order #39 (China RoHS):	Yes

Flammability, LS0H, Toxicity Testing

UL Flammability:	Horizontal
CSA Flammability:	FT1
UL voltage rating:	600 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	UPC
30800 009100	White	Reel	100 ft	612825140474
30800 009250	White	Reel	250 ft	612825140481

Footnote:	C - CRATE REEL PUT-UP., F - MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 50'.
-----------	--

Product Notes

Notes:	Exact strand count may vary.
--------	------------------------------

History

Update and Revision:	Revision Number: 0.368 Revision Date: 05-05-2023
----------------------	--

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[30800 009250](#) [30800 009100](#)