



Product: [3088CE](#)

Inst XLPE/PVC, 2+1G C #18 Str BC, XLPE Ins E1, OS, Blk PVC Jkt, 600V TC 150V NPLF 90C Dry

Product Description

UL Instrumentation XLPE/PVC, 2+1G Conductor 18AWG (7x26) Bare Copper, XLPE Insulation E1 Color Code, Overall Beldfoil® Shield, Black PVC Outer Jacket, 600V TC 150V NPLF 90C Dry 75C Wet SUN RES DIR BUR

Technical Specifications

Product Overview

Suitable Applications:	Instrumentation Applications in Plants, TC-ER, Exposed Run Applications
------------------------	---

Physical Characteristics (Overall)

Conductor					
Element	AWG	Stranding	Material	No. of Conductors	No. of Pairs
	18	7x26	BC - Bare Copper		1
Ground Wire	18	7x26	BC - Bare Copper	1	
Conductor Count:				3	
Total Number of Pairs:				1	

Material	Nominal Wall Thickness
XLP, XLPO, XLPE (Thermoset)	0.03 in

Color Chart	
Number	Color
1	Black & White
2	Green

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	20	7x28

Outer Shield

Material
No Shield

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	0.324 in	0.047 in	Yes

Electrical Characteristics

Conductor DCR	
Nominal Conductor DCR	Nominal Outer Shield DCR
5.86 Ohm/1000ft	7.46 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Other Conductor to Shield	Nom. Capacitance Conductor to Shield	Nom.Mutual Capacitance
30 pF/ft	54 pF/ft	30 pF/ft

Voltage

UL Voltage Rating
600 V RMS
150 V RMS (NPLF)

Temperature Range

UL Temp Rating:	90°C
Operating Temp Range:	-30°C To +90°C
Wet Temp Range:	-30°C To +90 °C
Dry Temp Range:	-30°C To +90 °C

Mechanical Characteristics

Bulk Cable Weight:	61 lbs/1000ft
Max. Pull Tension:	80 lbs
Min. Bend Radius/Minor Axis:	3.4 in

Standards

NEC/(UL) Compliance:	TC-ER
Other Specification:	ICEA S-73-532, S-66-524

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Burial:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1685 UL Loading
CSA Flammability:	FT4
ICEA Flammability:	T-29-520
IEEE Flammability:	1202
UL voltage rating:	600 V RMS (Type TC)

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

History

Update and Revision:	Revision Number: 0.202 Revision Date: 08-27-2021
----------------------	--

© 2021 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[3088CE 0101000](#) [3088CE 0105000](#)