



**Product:** SPIDER-PL-40-01T1O69999TX9HHHH

**Configurator:** SPIDER-PL-40-01T1O69999TX9HHHH



**Configurator Description**

Reliably transmit large amounts of data across any distance with the SPIDER III family of industrial Ethernet switches. These unmanaged switches have plug-and-play capabilities to allow for quick installation and startup - without any tools - to maximize uptime.

**Technical Specifications**

**Product description**

Description	Unmanaged, Industrial ETHERNET Rail Switch, fanless design, store and forward switching mode, USB interface for configuration , Full Gigabit Ethernet
Part Number	942141133
Port type and quantity	1 x 10/100/1000BASE-T, TP cable, RJ45 sockets, auto-crossing, auto-negotiation, auto-polarity , 1 x 100/1000Mbit/s SFP

**Product Life Cycle**

Availability	passiv
Last Order Date	2023-09-30

**Product Life Cycle**

Last Delivery Date	2023-12-31
Power supply/signaling contact	1 x plug-in terminal block, 6-pin

**Network size - length of cable**

Twisted pair (TP)	0 - 100 m
-------------------	-----------

**More Interfaces**

Single mode fiber (SM) 9/125 µm	0 - 20 km, 0 - 11 dB Link Budget (with M-SFP-LX/LC)
Multimode fiber (MM) 50/125 µm	0 - 550m, 0 - 7,5 dB link budget (with M-SFP-SX/LC)
Multimode fiber (MM) 62.5/125 µm	0 - 275 m, 0 - 7,5 dB Link Budget at 850 nm (with M-SFP-SX/LC)
Line - / star topology	any

**Power requirements**

Current consumption at 24 V DC	Max. 170 mA
--------------------------------	-------------

**Network size - cascading**

Operating Voltage	12/24 V DC (9.6 - 32 V DC), redundant
Power consumption	Max. 4.0 W

**Power requirements**

Power output in BTU (IT)/h	13.8
----------------------------	------

**Diagnostics features**

Diagnostic functions	LEDs (power, link status, data, data rate)
MTBF	1.530.211 h (Telcordia)

**Diagnostics features**

Operating temperature	-40-+70 °C
Storage/transport temperature	-40-+85 °C

Ambient conditions

Relative humidity (non-condensing)	10 - 95 %
Dimensions (WxHxD)	39 x 135 x 117 mm (w/o terminal block)
Weight	400 g
Mounting	DIN rail
Protection class	IP40 metal housing
IEC 60068-2-6 vibration	3.5 mm, 5–8.4 Hz, 10 cycles, 1 octave/min 1 g, 8.4–150 Hz, 10 cycles, 1 octave/min
IEC 60068-2-27 shock	15 g, 11 ms duration, 18 shocks
EN 61000-4-2 electrostatic discharge (ESD)	8 kV contact discharge, 15 kV air discharge
EN 61000-4-3 electromagnetic field	20V/m (80 – 3000 MHz)
EN 61000-4-4 fast transients (burst)	4kV power line; 4kV data line
EN 61000-4-5 surge voltage	power line: 2kV (line/earth), 1kV (line/line); 4kV data line
EN 61000-4-6 Conducted Immunity	10V (150 kHz - 80 MHz)

EMC emitted immunity

EN 55022	EN 55032 Class A
FCC CFR47 Part 15	FCC 47CFR Part 15, Class A
Basis Standard	CE, FCC, EN61131
Safety of industrial control equipment	cUL 61010-1/61010-2-201

EMC emitted immunity

Hazardous locations	ISA 12.12.01 Class 1 Div. 2
---------------------	-----------------------------

Reliability

Guarantee	60 months (please refer to the terms of guarantee for detailed information)
-----------	---

Scope of delivery and accessories

Accessories	Rail Power Supply RPS 30/80 EEC/120 EEC (CC), Wall mounting plate for DIN rail mounting (width 40/70 mm)
Scope of delivery	Device, terminal block, safety instruction

Further Instructions

Product Documentation	<a href="https://www.doc.hirschmann.com/index.html">https://www.doc.hirschmann.com/index.html</a>
Certificates	<a href="https://www.doc.hirschmann.com/certificates.html">https://www.doc.hirschmann.com/certificates.html</a>

© 2023 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirschmann:](#)

[SPIDER-PL-40-01T1O69999TX9HHHH](#)