



Product: [31514](#)

Lead Wire, #14 Str TC, Neoprene Ins, AWM 3046

Request Sample

Product Description

Low Temp Rubber Lead Wire, 14AWG (41x30) Tinned Copper, Neoprene Insulation, AWM 3046 CSA TYPE CL903600V 90C

Technical Specifications

Product Overview

Suitable Applications:	internal wiring of appliances, oil resistance applications, motor lead systems
------------------------	--

Construction Details

Conductor				
Element	No. of Elements	Size	Stranding	Material
Conductor(s)	1	14 AWG	41x30	TC - Tinned Copper

Insulation		
Material	Nom. Thickness	Nom. Insulation Diameter
Neoprene	0.047 in (1.2 mm)	0.169 in (4.29 mm)
Overall Cable Diameter (Nominal):		0.169 in (4.29 mm)

Electrical Characteristics

Electricals	
Nom. Conductor DCR	Max. Current
2.82 Ohm/1000ft	40 Amps per Conductor at 30°C

Voltage	
UL Voltage Rating	600 V (AWM 3046)

Mechanical Characteristics

Temperature	
UL Temperature	Operating
90°C	-30°C To +90°C

Bend Radius	
Stationary Min.	Installation Min.
1.69 in (42.9 mm)	1.69 in (42.9 mm)

Max. Pull Tension:	53.3 lbs (24.2 kg)
Recommended Max Baking Cycles:	24 Hours @ 300°F (149°C) ~ 8 Hours @ 325°F (163°C) ~ 15 Minutes @ 450°F (232°C)
Bulk Cable Weight:	26 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	Horizontal flame

AWM Compliance:	AWM 3046
CEC / C(UL) Compliance:	CL-903
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Recommended Maximum Baking Cycles: 24 Hours @ 300°F (149°C) ~ 8 Hours @ 325°F (163°C) ~ 15 Minutes @ 450°F (232°C)
--------	--

History

Update and Revision:	Revision Number: 0.479 Revision Date: 07-03-2024
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
31514 010500	Black	Reel	500 ft	612825142256	F
31514 0104000	Black	Reel	4,000 ft	612825142249	C I U
31514 005500	Green, Dark	Reel	500 ft	612825142225	F
31514 0024000	Red	Reel	4,000 ft	612825142201	C I U
31514 009500	White	Reel	500 ft	612825142232	F
31514 0044000	Yellow	Reel	4,000 ft	612825142218	C I U

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[31514 0104000](#) [31514 009500](#) [31514 010500](#) [31514 0044000](#) [31514 005500](#) [31514 0024000](#)