



Product: [FISM096A1](#)

Indoor Plenum OS2 Mini-Distribution 96F Armor 2mm SubUnits

Product Description

FX Indoor OS2 Mini-Distribution 96 Fibers OFCP Aluminum Interlocked Armor Sub-Units (2.0MM) Yellow Jacket

Technical Specifications

Part Number:	FISM096A1
Construction Type:	Mini Distribution

Product Overview

Environmental Space:	Indoor
Suitable Applications:	Indoor

Construction

Fiber Cable Construction

Fiber Type	Fiber Count
OS2	96

Central Strength Member:	GRP
--------------------------	-----

SubUnit Specifications

Number of Active Subunits:	8
Number of Subunit Positions:	8
Fibers Per Subunit:	12
SubUnit Diameter:	0.078 in (2.0 mm)

Jacket Specifications

Number of Jackets:	Double Jacket
Type of Armor:	Interlocked Aluminum
Number of Inner Jacket Ripcords:	2
Color@InnerJacket1:	Yellow
Material@InnerJacket1:	PVC

Outer Jacket Material

Material	Nominal Diameter
Thermoplastic	0.74 in (18.8 mm)

Outer Jacket Color:	Yellow
Number of Outer Jacket Ripcords:	2
OuterJacket1, Nominal Diameter:	0.675 (17.1)

Optical Characteristics

Mode Field Diameter:	9.2
Fiber Core Diameter:	8.2/125µm
Max Attenuation at 1310 nm:	0.4 dB/km
Max Attenuation at 1550 nm:	0.3 dB/km
Wavelength:	1310 nm / 1550 nm

10 Gigabit Ethernet Performance:	10,000 m / 40,000 m
1 Gigabit Ethernet Performance:	5,000 m / -

Mechanical Characteristics

Mechanical Tests

Description	Requirement/Value
Cable Min. Bend Radius Installation (Short Term)	20x Cable OD
Cable Min. Bend Radius Operation (Long Term)	15x Cable OD

Temperature Range

Operating Temp Range:	0C to +70C
Installation Temp Range:	0C to +60C
Storage Temp Range:	-40C to +70C

Standards

UL Rating/Flame Test:	OFCP
NEC/(UL) Specification:	N/A
C (UL) US:	FT4
Telecommunications Standards:	ANSI/CEA S-83-596
RoHS:	Yes

History

Variants

Item #	Color	UPC
FISM096A1	Yellow	612825287131

Update and Revision:	Revision Number: 0.54 Revision Date: 03-13-2019
----------------------	---

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[FISM096A1](#)